


[PRODUCTS](#)
[COMPANY](#)
[CONTACT US](#)
[SUPPORT](#)
[SITE MAP](#)
PRODUCT SEARCH

974-DS/16-20MM

ARTICLE NUMBER e.g.20.874.002

PRODUCTS

CROSS-REFERENCE

Screw Connectors for Printed Circuit Boards
TYPE 974 (-DS)
5 mm spacing - 2 to 26 poles

Distributor Stock Check

Series	Download PDF	3D Model	Can plug with	How to order	Color specifications	Print
--------	--------------	----------	---------------	--------------	----------------------	-------



RoHS WEEE Pb free surface compliant

Description


Can be installed anywhere on PCB without wires or screws interfering with the rest of PCB. Can be located next to each other back-to-back, front-to-front and front-to-back. The screws and wire entries are easily visible, accessible and usable, an ergonomic advantage.

- Solid version
- Wire entrance at 45° angle to PC Board
- End-to-end stackable while maintaining the 5 mm spacing.

Technical Data
Center to Center Spacing: 5 mm (0.197 in.)

Nominal Cross Section: 2.5 mm² (3874 mils²)

Wire Stripping Length: 6.5 mm (0.26 in.)

Recommended Hole Diameter in PC Board: 1.3 mm (0.051 in.)

Dimensions: mm (in.)

Length of Connector (L)

L = No. of Poles x Center to Center Spacing

When locating connector, allow 0.5 mm clearance around it for process-induced variations.
Approval Information

UL File No.E69841



CSA File No.LR24322



Rating	Current(A)	Voltage(V)	Application group	AWG
UL	20	300	B,D	26-12
CSA	15	300	B,D,E	22-10

* Version DS is CSA certified for 26-10 AWG.

UL: 24-26 AWG range for factory wiring only.

Screw Tightening Torque:

UL: 4.5 lbf·in

CSA: 0.51 Nm

International Approvals:

Rated Impulse Withstand Voltage: 2500 V

Material
Version: 2 to 8 poles

Molding: Polyamide, self extinguishing UL 94, V-0, color grey

Temperature limits:
Short Time: 140°C (284°F)

Continuous: RTI 105°C (221°F)

Low Limit: -40°C (-40°F)

Comparative Tracking Index: CTI≥600V

Oxygen Index Rating: 32%

Version: 9 to 26 poles

Molding: Polyamide (glass fiber reinforced), self extinguishing UL 94, V-0, color grey

Temperature limits:

Short Time: 200°C (392°F)
Continuous: RTI 105°C (221°F)
Low Limit: -40°C (-40°F)
Comparative Tracking Index: CTI > 175
Oxygen Index Rating: 33%

Terminal Body: Tin plated copper alloy
Wire Protector: Tin plated copper alloy
Screw: M3, Slotted head, zinc plated clear passivated, steel substrate
Solder Pin: Ø 1.0 mm (0.04 in.), Tin plated copper alloy

 [Top of page](#)

How to order

Item — **974 (-DS)**

Options

- ☐ CN: Consecutive Numbering (hot stamped numbers)
- ☐ SM: Special Marking (please provide sketch)
- ☐ G05: Gold Plating (5 micro inches)
- ☐ G30: Gold Plating (30 micro inches)
- ☐ S30: Silver Plating (30 micro inches)
- ☐ XXMM: Longer solder Pins up to 75 mm (3 in.)

Protruding length of pins, in millimeters: _____

Note: Plated component: terminal body

Ordering Note: Version with 10 mm spacing (975 (-DS)).

- ☒ **Request sample**
- ☐ **Request quote**

Quantity

Accessories

[BST Self Adhesive Marking Strips.](#)
[Consecutively numbered.](#)
[Jumper, Type 970-J1.](#)
[Jumper, Type 970-J2.](#)

974

WIRE PROTECTOR:
with: - DS

POLES:
02 to 26

/

[Add to shopping cart](#)

2008, WECO Electrical Connectors Inc.

ISO 9001 registered quality management system