





REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1876	A	RELEASED	EO	07/25/06	SA	07/25/06	HO	07/25/06


 RoHS
Compliant

P.C.B. LAYOUT

SPECIFICATIONS:

1. Shell: Steel, Tin-Plated
2. Contact: Brass, Gold-Plated
3. Insulator: PBT & Fiber-Glass Reinforced Black Color
4. Current Rating: 5 Amps
5. Dielectric Strength: 1000 V for One Minute
6. Insulator Resistance: 1000 Megohms Min. at 500 VDC
7. Temperature: -55°C to +105°C

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITHE.

TOLERANCES:
Unless Otherwise
Specified
.X ±0.35 [0.014]
.XX ±0.25 [0.010]

DRAWN BY:
EKLAS ODISH
DATE:
07/25/06
CHECKED BY:
SAMI ALNADI
DATE:
07/25/06
APPROVED BY:
HISHAM ODISH
DATE:
07/25/06

DRAWING TITLE:
25 Pin D-Sub R/A PCB Mount Plug 0.590" Footprint
SIZE DWG. NO. ELECTRONIC FILE REV
A SPC15197 79K4800.DWG A
SCALE: NTS U.O.M.: mm [INCHES] SHEET: 1 OF 1