




DATE	DESCRIPTION	REV.
10.1.03	CHANGE AS PER ECN 03-071	A



PC MOUSE CONTACT
(TYP. 2)

COLLECTOR PLATE BASE
COLLECTOR PLATE
FORMED THREAD FOR
#6-20 SCREW (TYPE B)
(TYP. 2)

BOTTOM VIEW



MOUNTING DETAIL
BOTTOM VIEW

NOTES:

1. TOP PLATE: COLOR - NATURAL
MAT'L - NYLON 6/6 UL 94V-2
COLLECTOR PLATE BASE:
MAT'L - .032 [0.81] THK PHENOLIC
- COLLECTOR PLATE:
MAT'L - .032 [0.81] THK STEEL
FINISH - TIN PLATE
PC MOUSE CONTACT:
MAT'L - .013 [0.33] THK BRASS
FINISH - TIN PLATE

THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.			
TOLERANCES	INCH	[MM]	CODE
DECIMAL	± .005	[± 0.15]	C
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED			

KEYSTONE ELECTRONICS CORP.			
ASTORIA, N.Y. 11105-2017			
PART NAME			
TO-3 POWER TRANSISTOR SOCKET			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		BOONE	3.18.91
		App'd	SCALE
		LN	1.5X
		DWG NO.	
		4600	