

Coaxial PCB Connector 92_MMBX-S50-0-12/111_N

Description

Edge mount PCB jack

Interface Standards
SUHNER-MMBX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 12.4 GHz

Mechanical Data

Board mounting type edge mount
Weight 0.0011 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	LCP (Liquid crystal polymer)	

Related Documents

Outline drawing DOU-00013388
Catalogue drawing DCA-00013390
Mounting hole DOU-00013391

Ordering Information

Tape and Reel package 92_MMBX-S50-0-12/111_NM
Single package 92_MMBX-S50-0-12/111_NE

Remarks

PCB connector without stand-offs