

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]					TOOLS
	ENGLISH	METRIC	L ± .03 [0,51]	W ± .01 [0,25]	C ± .02 [0,38]	M ± .03 [0,51]	H ± .01 [0,25]	
EV18-6FB	#6	M3	.86 [21,8]	.30 [7,6]	.21 [5,3]	.69 [17,5]	.15 [3,8]	**CT-100A *CT-160 *CT-260 *CT-400 CT-600-A (CT-500CH) CT-600-A (CT-550CH) CT-1550 CT-1551 CT-2500 (CT-2550CH)
EV18-8FB	#8	M4	.93 [23,6]	.32 [8,1]	.25 [6,4]	.73 [18,5]	.17 [4,3]	
EV18-10FB	#10	M5	.93 [23,6]	.35 [8,9]	.25 [6,4]	.75 [19,1]	.20 [5,1]	

**167°F [75°C] MAX. OPERATING TEMPERATURE WITH CT-100A
 *PANDUIT APPROVED TOOL

NOTES:


1. cULus LISTED FOR:
 A. 22-18 AWG [0,5-1,0 mm²] SOLID OR STRANDED COPPER WIRE
 B. 221°F [105°C] MAX. OPERATING TEMPERATURE
 C. 600V. MAX. BLDG WIRE
 (1000 V. MAX. IN SIGNS, FIXTURES & LUMINAIRES)

2. MATERIAL:
 A. STAMPING: .032" [0,8] THK COPPER, TIN PLATED
 B. HOUSING: VINYL, RED

3. WIRE STRIP LENGTH: 5/16" ^{+1/32}₋₀ [7,9mm ^{+0,8}₋₀]

4. SEE www.panduit.com FOR PACKAGE QUANTITIES

5. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



TITLE		STRONGHOLD FORK TERMINALS VINYL INSULATED, BUTTED SEAM #22-18 AWG	
ITEM REVISION NAME		CUSTOMER DRAWING	
00123SHP/00		PANDUIT ™	
DATASET FILE NAME		00123SHP_DC/00	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: SEE NOTES	
.X ± .XX ±		.XXX ± ANGLES ±	
THIRD ANGLE PROJECTION		DRAWING NUMBER: SH41194	
DRAWN BY FES	DATE -	CHK FS	SCALE N.T.S.
SHEET 1 OF 1		SIZE A	