


PART NO.
SEE CHART
DWG. NO.
SD-92321-001



90635 CONNECTOR
CIRCUIT SIZE
10
14
16
20
26
34
40
50

CABLE DETAILS:

28 AWG , 1.27 MM PITCH , 7 STRANDS WITH TINNED COPPER ,
GREY PVC INSULATION WITH A COLOURED POLARITY STRIPE
INDICATING CIRCUIT NO. 1 , UL 2651.

PLATING DETAILS:

15U" GOLD FLASH PLATING.

NOTES:

1. SEE PRODUCT SPECIFICATIONS PS-99020-0015.
2. SEE CABLE SPECIFICATION ES-99027-0006.
3. HARNESSES WILL BE 100% ELECTRICALLY TESTED FOR SHORTS AND DISCONTINUITIES.

ORDERING INFORMATION

92321-****

CIRCUIT SIZE
LENGTH L IN CENTIMETRES

LENGTHS AVAILABLE FROM 5 CM TO 50 CM, IN STEPS OF 5.
05, 10, 15, 20, 25, 30, 35, 40, 45 & 50CM

e.g. 92321-1410 = 14 CIRCUIT
WITH LENGTH L OF 10 CM.

ORIGINAL RELEASE EC NO. 2000-0896 DRWN: D.RYAN CHK: / / APPR: / / AI	DESCRIPTION MAJOR CRITICAL C	REV	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 2 : 1	DESIGN UNITS ☒ mm ☐ INCH	THIRD ANGLE PROJECTION	DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY		SHT	REV	
			4 PLACES ±0. ±.	mm	INCH	DRAWN BY & DATE D.RYAN 00/03/15		TITLE: QF50 TO QF50 STANDARD ASSEMBLIES	MATERIAL NO. SEE CHART	DRAWING NO. SD-92321-001	SHEET NO. 1 OF 1	
			3 PLACES ±0. ±.	mm	INCH	CHECKED BY & DATE BENRIGHT 00/03/15						
			2 PLACES ±0. ±.	mm	INCH	APPROVED BY & DATE MWILHITE 00/03/15						
			1 PLACE ±0. ±.		CAD FILENAME							
			ANGULAR: ± 1/2 °									
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.							