


LDC Series Triple Output —
15-60 Watts Open Frame, Universal Input AC 85~264

Designed for Low Profile and Low Cost.




- Low Profile Lightweight PC Board Construction, Low Cost
- High Quality — Field Failure Rate Less than 0.012%
- Universal Input: AC 85-264
- Inrush Current, Over-Voltage and Over-Current Protection Circuitry
- Fully Regulated, Fully Isolated Input/Output, V1 Isolated From V2 and V3
- Zero Minimum Load


- Available with Chassis and Cover Option (SN Option)
- Also Available with ±10% Voltage Adjustable Output Potentiometer (Y Option)
- Conductive Noise: FCC-B, VCCI-2 and VFG 243/91
- UL, CSA and TUV Safety Approvals, CE Marked
- Two Year Warranty
- Wiring Harnesses Available on Bottom of Page 696



| Stock No. | Mfr.'s Type | Watts Approx. | DC Output (V)/Current (A) | | | Dimensions W×H×D (In.) | Weight (Lbs.) | EACH | |
|-----------|-------------|---------------|---------------------------|----------------------|-----------------------|------------------------|---------------|--------|--------|
| | | | V1 | V2 | V3 | | | 1-4 | 5-24 |
| 800-9280 | LDC15F-1 | 16.0 | +5 V/2.0 A (Pk 3.0) | +12 V/0.3 A (Pk 0.6) | -12 V/0.2 A (Pk 0.30) | 1.97×1.02×5.00 | 0.33 | 50.76 | 46.90 |
| 800-0380 | LDC15F-1-SN | 16.0 | +5 V/2.0 A (Pk 3.0) | +12 V/0.3 A (Pk 0.6) | -15 V/0.2 A (Pk 0.30) | 2.25×1.50×5.79 | 0.66 | 57.14 | 55.30 |
| 800-9285 | LDC15F-2 | 17.5 | +5 V/2.0 A (Pk 3.0) | +15 V/0.3 A (Pk 0.6) | -15 V/0.2 A (Pk 0.30) | 1.97×1.02×5.00 | 0.33 | 50.76 | 46.90 |
| 800-0385 | LDC15F-2-SN | 17.5 | +5 V/2.0 A (Pk 3.0) | +15 V/0.3 A (Pk 0.6) | -15 V/0.2 A (Pk 0.30) | 2.25×1.50×5.79 | 0.66 | 57.14 | 55.30 |
| 800-9290 | LDC30F-1 | 3.3 | +5 V/3.0 A (Pk 4.5) | +12 V/1.2 A (Pk 2.0) | -12 V/0.3 A (Pk 0.45) | 2.56×1.02×5.51 | 0.48 | 71.86 | 66.40 |
| 800-0390 | LDC30F-1-SN | 3.3 | +5 V/3.0 A (Pk 4.5) | +12 V/1.2 A (Pk 2.0) | -12 V/0.3 A (Pk 0.45) | 2.84×1.50×6.30 | 0.88 | 75.71 | 73.27 |
| 800-9295 | LDC30F-2 | 34.5 | +5 V/3.0 A (Pk 4.5) | +15 V/1.0 A (Pk 2.0) | -15 V/0.3 A (Pk 0.45) | 2.56×1.02×5.51 | 0.48 | 71.86 | 66.40 |
| 800-0395 | LDC30F-2-SN | 34.5 | +5 V/3.0 A (Pk 4.5) | +15 V/1.0 A (Pk 2.0) | -15 V/0.3 A (Pk 0.45) | 2.84×1.50×6.30 | 0.88 | 75.71 | 73.27 |
| 800-4020 | LDC60F-1 | 61.0 | +5 V/5.0 A (Pk 7.0) | +12 V/2.5 A (Pk 3.5) | -12 V/0.5 A (Pk 0.70) | 3.27×1.02×7.28 | 0.66 | 111.09 | 102.64 |
| 800-0400 | LDC60F-1-SN | 61.0 | +5 V/5.0 A (Pk 7.0) | +12 V/2.5 A (Pk 3.5) | -12 V/0.5 A (Pk 0.70) | 3.62×1.50×8.27 | 1.21 | 114.29 | 110.60 |
| 800-4025 | LDC60F-2 | 62.5 | +5 V/5.0 A (Pk 7.0) | +15 V/2.0 A (Pk 3.5) | -15 V/0.5 A (Pk 0.70) | 3.27×1.02×7.28 | 0.66 | 111.09 | 102.64 |


PMC Series Triple Outputs —
15-100 Watts Metal Chassis Mount, Wide Range Input AC 85~264

Designed for High Reliability and Compact Footprint.



- Chassis Mount, Compact Footprint
- High Quality — Field Failure Rate Less than 0.012%
- Universal Input: AC 85-264
- User Selectable Input: AC 85-132, 170-264
- Inrush Current, Over-Voltage and Over-Current Protection Circuitry
- Fully Regulated, Fully Isolated Input/Output, V1 Isolated from V2 and V3
- Built-In ±10% Voltage Adjustable Potentiometer on V1
- Zero Minimum Load
- Available with Cover Option (N Option) PMC 50, 75 and 100
- Conductive Noise: FCC-B
- UL, CSA and TUV Safety Approvals, CE Marked
- Three Year Warranty
- Wiring Harnesses Available on Bottom of Page 696

| Stock No. | Mfr.'s Type | Watts Approx. | Output (V)/Current (A) | | | Dimensions W×H×D (In.) | Weight (Lbs.) | EACH | |
|-----------|-----------------|---------------|------------------------|-------------|--------------|------------------------|---------------|--------|--------|
| | | | V1 | V2 | V3 | | | 1-4 | 5-24 |
| 800-1160 | PMC15E-1 | 15 | 5 V/2 A | 12 V/0.30 A | -12 V/0.20 A | 1.46×2.36×4.33 | 0.55 | 73.00 | 67.00 |
| 800-1170 | PMC15E-2 | 15 | 5 V/2 A | 15 V/0.30 A | -15 V/0.20 A | 1.46×2.36×4.33 | 0.55 | 68.67 | 63.45 |
| 800-1180 | PMC15E-3 | 15 | 5 V/2 A | 12 V/0.30 A | -5 V/0.20 A | 1.46×2.36×4.33 | 0.55 | 68.67 | 63.45 |
| 800-1190 | PMC30E-1 | 30 | 5 V/3 A | 12 V/1.20 A | -12 V/0.30 A | 1.52×2.36×5.71 | 0.66 | 92.15 | 85.15 |
| 800-1200 | PMC30E-2 | 30 | 5 V/3 A | 15 V/0.70 A | -15 V/0.50 A | 1.52×2.36×5.71 | 0.66 | 92.15 | 85.15 |
| 800-1210 | PMC50E-1-XULA-N | 50 | 5 V/5 A | 12 V/1.25 A | -12 V/0.35 A | 1.34×3.66×7.28 | 0.88 | 131.53 | 121.53 |
| 800-1240 | PMC75E-1-N | 75 | 5 V/8 A | 12 V/2.50 A | -12 V/0.50 A | 1.65×3.66×8.07 | 1.32 | 181.00 | 167.25 |
| 800-1250 | PMC75E-2-N | 75 | 5 V/8 A | 15 V/1.80 A | -15 V/0.50 A | 1.65×3.66×8.07 | 1.32 | 181.01 | 167.25 |
| 800-1260 | PMC75E-4-N | 75 | 5 V/6 A | 12 V/3.20 A | -12 V/0.50 A | 1.65×3.66×8.07 | 1.32 | 181.01 | 160.38 |
| 800-1270 | PMC100E-1-N | 100 | 5 V/13 A | 12 V/2.00 A | -12 V/1.00 A | 1.89×3.66×8.66 | 1.65 | 211.05 | 195.01 |
| 800-1280 | PMC100E-2-N | 100 | 5 V/13 A | 15 V/1.50 A | -15 V/1.00 A | 1.89×3.66×8.66 | 1.65 | 211.05 | 195.01 |
| 800-1290 | PMC100E-4-N | 100 | 5 V/8 A | 12 V/4.00 A | -12 V/1.00 A | 1.89×3.66×8.66 | 1.65 | 211.05 | 195.01 |

12

RMC and MMC Series Triple Outputs —
8-100 Watts Metal Chassis Mount, Standard Input AC 85~132

Designed for High Reliability and Compact Footprint.



- Chassis Mount, Compact Footprint
- High Quality — Field Failure Rate Less than 0.012%
- Standard Input: AC 85-132
- Inrush Current, Over-Voltage and Over-Current Protection Circuitry
- Fully Regulated, Fully Isolated Input/Output, V1 Isolated from V2 and V3
- Built-In ±10% Output Voltage Adjustment Potentiometer on V1
- Zero Minimum Load
- Available with Cover Option (N Option)
- Conductive Noise: FCC-B, Some Models FCC-A
- UL and CSA Safety Approvals
- Two Year Warranty
- Wiring Harnesses Available on Bottom of Page 696

| Stock No. | Mfr.'s Type | Watts Approx. | Output (V)/Current (A) | | | Dimensions W×H×D (In.) | Weight (Lbs.) | EACH | |
|-----------|-------------|---------------|------------------------|-------------|-------------|------------------------|---------------|--------|--------|
| | | | V1 | V2 | V3 | | | 1-4 | 5-24 |
| 800-1801 | MMC8A-1-N | 8 | +5 V/1.2 A | +12 V/0.1 A | -12 V/0.1 A | 1.06×2.91×2.68 | 0.33 | 45.44 | 41.99 |
| 800-1806 | MMC8A-2-N | 8 | +5 V/1.1 A | +15 V/0.1 A | -10 V/0.1 A | 1.06×2.91×2.68 | 0.33 | 45.44 | 41.99 |
| 800-1811 | MMC8A-3-N | 8 | +5 V/1.2 A | +12 V/0.1 A | -5 V/0.1 A | 1.06×2.91×2.68 | 0.33 | 45.44 | 41.99 |
| 800-8061 | RMC15A-1-N | 15 | +5 V/2.0 A | +12 V/0.3 A | -12 V/0.2 A | 1.26×3.14×3.93 | 0.55 | 56.29 | 52.01 |
| 800-8066 | RMC15A-2-N | 15 | +5 V/2.0 A | +15 V/0.2 A | -15 V/0.2 A | 1.26×3.14×3.93 | 0.55 | 56.29 | 52.01 |
| 800-8071 | RMC30A-1-N | 30 | +5 V/3.0 A | +12 V/1.2 A | -12 V/1.2 A | 1.37×3.14×3.93 | 0.77 | 75.48 | 69.75 |
| 800-8076 | RMC30A-2-N | 30 | +5 V/3.0 A | +15 V/0.5 A | -15 V/0.5 A | 1.37×3.14×3.93 | 0.77 | 75.48 | 69.75 |
| 800-1836 | MMC50A-1-N | 50 | +5 V/5.0 A | +12 V/2.0 A | -12 V/0.5 A | 1.42×3.66×6.10 | 0.88 | 109.82 | 101.47 |
| 800-1841 | MMC50A-2-N | 50 | +5 V/5.0 A | +15 V/1.2 A | -15 V/0.5 A | 1.42×3.66×6.10 | 0.88 | 109.82 | 101.47 |
| 800-1846 | MMC50A-3-N | 50 | +5 V/5.0 A | +12 V/2.0 A | -5 V/0.5 A | 1.42×3.66×6.10 | 0.88 | 109.82 | 101.47 |
| 800-1851 | MMC50A-4-N | 50 | +5 V/7.0 A | +12 V/1.5 A | -12 V/0.3 A | 1.42×3.66×6.10 | 0.88 | 109.82 | 101.47 |
| 800-0006 | RMC50A-1-N | 50 | +5 V/5.0 A | +12 V/2.0 A | -12 V/0.5 A | 1.37×3.66×6.10 | 0.77 | | |