

HARTING




Han[®] R 23 Circular Connectors



Features

- Size R 23
- Outer diameter 26 mm
- High contact density
- Very robust hoods and housings
- Corrosion resistant
- Excellent EMC properties (with continuous shielding)
- Quick and easy assembly
- Vibration resistant screw locking system
- Up to 19 contacts, 25 V~ / 60 V-
- Ideal for applications such as measurement and automatic control

Description



1) is part of delivery range of bulkhead mounted housings
Part-number of spare part: 09 15 200 9901

General information

Fields of application:

HARTING Industrial Connectors are applicable in a wide variety of electronic and electrical applications.

The degree of protection of all hoods and housings is in accordance with International Standard IEC 60 529.

- | | |
|-------------------------|------------------------------|
| • Power Utilities | • Industrial Instrumentation |
| • Robotics | • Conveyor Equipment |
| • Chemical Plants | • Transportation |
| • Machine Tool Controls | • and many more |
| • Injection Moulding | |



Certified according to EN ISO 9001 in design/development, production, installation and servicing

Specifications

- | | |
|----------|---|
| VDE 0110 | table concerning clearance and creepage distances |
| VDE 0627 | Connectors and plug devices |

Standards DIN EN 61 984

Note

Connectors should not be coupled and decoupled under electrical load. Connectors of the same or different series being mounted side by side may be protected against incorrect mating by the use of coding options.

General information

It is the user's responsibility to check whether the components illustrated in this catalogue comply with different regulations from those stated in special fields of application which we are unable to foresee.

We reserve the right to modify designs in order to improve quality, keep pace with technological advancement or meet particular requirements in production.

No part of this catalogue may be reproduced in any form (print, photocopy, microfilm or any other process) or processed, duplicated or distributed by means of electronic systems without the prior written consent of HARTING Electric GmbH & Co. KG, Espelkamp. We are bound by the German version only.



Technical characteristics

Specifications

DIN VDE 0110
DIN EN 61 984

Hoods and Housings

Material	Copper zinc alloy
Surface	Nickel plated
Flat sealing	NBR
O-Ring sealing	FPM
Temperature range	-40 °C ... +115 °C
Protection degree in locked position	IP 67

Inserts

Number of contacts	6	9	12	17	19
Rated current					
- power contact	15A	1x15A			3 x 10A
- signal contact		8 x 7A	7A	7A	16 x 7A
(see Derating Diagram)					
Rated voltage ¹⁾	25 V~ / 60 V-				
Degree of pollution	3				
Test voltage U_{rms}	1.5 kV				
Insulation resistance	$\geq 10^{12} \Omega$				
Material	Thermoplastic polyester (PBT)				
Temperature range	-40 °C ... +115 °C				
Flammability accd. to UL 94	V 0				

Contacts

Material	Copper alloy
Surface	Gold plated

Contact resistance $\leq 5 \text{ m}\Omega$

Screw termination	
- power contact	0.14 - 1.0 mm ² / AWG 26 - 16
- signal contact	0.14 - 0.75 mm ² / AWG 26 - 18

Solder termination	
- power contact	0.14 - 2.5 mm ² / AWG 26 - 14
- signal contact	0.14 - 1.0 mm ² / AWG 26 - 16


Crimp termination	
- D-Sub contact	see catalogue Interface Connectors

PCB solder termination	
- power contact	$\varnothing 1.5 \text{ mm}$
- signal contact	$\varnothing 0.6 \text{ mm}$
- reference to bulkhead mounted housing	3.5 mm



1) Accd. to DIN VDE 0627 metallic parts which may be touched by a person and may have voltages present under fault conditions, must have integral protection. Therefore this R 23 connector is limited for use up to 25 V~/60 V-.


Derating Diagram













Insert: 12 pins





Wire gauge: 1 mm² (AWG 18)

Shielding of the EMC housings



Identification	Number of contacts	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Screw terminal 	6	09 15 206 2601	09 15 206 2701	Contact arrangement view: mating side 	
Solder terminal 	6	09 15 206 2603	09 15 206 2703		
PCB solder termination²⁾ 	6	09 15 206 2604	09 15 206 2704	PCB hole details: 	
2) Suitable only for bulkhead mounted housings No. 09 15 200 0311, 09 15 200 0313 and 09 15 200 0301					
Screw terminal 	9	09 15 209 2601	09 15 209 2701	Contact arrangement view: mating side (numbering in opposite direction on request) 	
Solder terminal 	9	09 15 209 2603	09 15 209 2703		

Identification	Number of contacts	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Solder terminal 	12	09 15 212 2603	09 15 212 2703	Contact arrangement view: mating side (numbering in opposite direction on request)  PCB hole details:  2) Suitable only for bulkhead mounted housings No. 09 15 200 0311, 09 15 200 0313 and 09 15 200 0301	
Crimp terminal for D-Sub contacts 	12	09 15 212 2602	09 15 212 2702		
PCB solder termination²⁾ 	12	09 15 212 2604	09 15 212 2704		
Solder terminal 	17	09 15 217 2601	09 15 217 2701	Contact arrangement view: mating side (numbering in opposite direction on request)  PCB hole details:  2) Suitable only for bulkhead mounted housings No. 09 15 200 0311, 09 15 200 0313 and 09 15 200 0301	
Crimp terminal for D-Sub contacts 	17	09 15 217 2602	09 15 217 2702		
PCB solder termination²⁾ 	17	09 15 217 2603	09 15 217 2703		
Solder terminal 	19	09 15 219 2603	09 15 219 2703	Contact arrangement view: mating side 	






Identification	Part-Number	Pg	Drawing	Dimensions in mm
Hood top-entry 	09 15 200 0402 09 15 200 0403	9 11		
Hood top-entry EMC version 	09 15 200 0451	—		
Hood right angle entry 	09 15 200 0603	11		
Identification	Part-Number	Drawing	Dimension in mm	
Screw cover for hoods with tether 	09 15 200 5421			

Order inserts separately see page 4 - 5

Corresponding hoods and housing see page 7 - 9






Order inserts separately see page 4 - 5

Corresponding hoods and housing see page 7 - 9

Identification	Part-Number	Drawing	Dimension in mm
Bulkhead mounted housing front wall assembly with central locking Pg 13.5 	09 15 200 0324	 Panel cut out Pg 13.5	
Bulkhead mounted housing front wall assembly with central locking M20 	09 15 200 0303	 Panel cut out Ø 20 ^{+0.1}	
Bulkhead mounted housing front wall assembly with flat sealing 	09 15 200 0301	 Panel cut out Ø 20 ^{+0.1}	
Bulkhead mounted housing front wall assembly with O-ring sealing 	09 15 200 0305	 Panel cut out Ø 20 ^{+0.1}	
Bulkhead mounted housing front wall assembly with O-ring sealing 	09 15 200 0901	 Panel cut out Ø 20 ^{+0.1}	





Order inserts separately, see page 4 - 5






Corresponding hoods and housings see page 6

Identification	Part-Number	Drawing	Dimension in mm
Bulkhead mounted housing back wall assembly with O-ring sealing 	09 15 200 0313	 Panel cut out $\varnothing 23^{+0,1}$ Panel thickness: 2.7 - 3.5 when using counter sunk screws	
Bulkhead mounted housing back wall assembly with O-ring sealing 	09 15 200 0311	 Panel cut out $\varnothing 23^{+0,1}$ Panel thickness: 2.7 - 3.5 when using counter sunk screws	
Bulkhead mounted housing back wall assembly with O-ring sealing 	09 15 200 0312	 Panel cut out $\varnothing 23^{+0,1}$ Panel thickness: 3.5 - 8.5 when using counter sunk screws	
Bulkhead mounted housing back wall assembly with central locking M25 	09 15 200 0314	 Panel cut out $\varnothing 25^{+0,1}$ Panel thickness: 6	
Cable to cable housing back wall assembly with central locking M25 	09 15 200 0351	 Panel cut out $\varnothing 25^{+0,1}$ Panel thickness: 6	

Order inserts separately, see page 4 - 5


Corresponding hoods and housings see page 6

Identification	Part-Number	Pg	Drawing	Dimensions in mm
Cable to cable housing top-entry 	09 15 200 0703	11		
Cable to cable housing top-entry EMC version 	09 15 200 0751	—		
Identification	Part-Number	Drawing	Dimension in mm	
Screw cover for bulkhead mounted and cable to cable housings 	09 15 200 5401			
Screw cover for bulkhead mounted and cable to cable housings with tether 	09 15 200 5411			


Identification	Part-Number	Pg	Drawing	Dimensions in mm
Cable clamp metal (IP 65) with normal seal 	09 00 000 5113	11	Suitable cable Ø 10 - 12	
with multiple seal 	09 00 000 5013	11	6.5 - 12	
Spacel cable clamp metal (IP 65) with strain relief and bell mouth 	09 00 000 5191	11	Suitable cable Ø 8 - 12	
with strain relief and bell mouth order separately 	09 00 000 5027	11	6.5 - 12	
Identification	Part-Number	Drawing	Dimension in mm	
Assembly tool for angled bulkhead mounted housings 	09 99 000 0324			
Assembly tool for bulkhead mounted and cable to cable housings 	09 99 000 0325	 As an alternative a screw driver can be used.		
Assembly tool for hoods 	09 99 000 0326	 Alternatively for the assembly of the EMC version a screw driver can be used.		

Assembly manuals


Hoods and Housings	Cable stripping length x
09 15 200 0351	26 mm
09 15 200 0403	20 mm
09 15 200 0451	26 mm
09 15 200 0603	30 mm
09 15 200 0703	20 mm
09 15 200 0751	26 mm
09 15 200 0901	30 mm




Standard hoods and housings



EMC housings



Right angled bulkhead mounted housing



Subsidiary companies – worldwide



Austria

HARTING Ges. m. b. H.
Deutschstraße 19, A-1230 Wien
Phone +43 1/6 16 21 21; Fax +43 1/6 16 21 21-21
E-Mail: at@HARTING.com

Belgium

HARTING N.V./S.A.
Z.3 Doornveld 23, B-1731 Zellik
Phone +32 2/4 66 01 90; Fax +32 2/4 66 78 55
E-Mail: be@HARTING.com; Internet: www.HARTING.be

Brazil

HARTING Ltda.
Av. Dr. Lino de Moraes, Pq. Jabaquara, 255
CEP 04360-001 - São Paulo - SP - Brazil
Phone +55 11/50 35-00 73; Fax +55 11/50 34-47 43
E-Mail: br@HARTING.com
Internet: www.HARTING.com.br

China

Zhuhai HARTING; Limited Shanghai branch
Room 5403, 300 Huaihai Zhong Road
Hong Kong New World Tower
Luwan District, P.R.C; Shanghai 200021, China
Phone +86 21 - 63 86 22 00; Fax +86 21 - 63 86 86 36
E-Mail: cn@HARTING.com

Czech Republic

HARTING spol. s.r.o.
Mlýnská 2, 160 00 Praha 6
Phone +420 220 380 460; Fax +420 220 380 461
E-Mail: cz@HARTING.com; Internet: www.HARTING.cz

Finland

HARTING Oy
Teknobulevardi 3-5, PL 35, FI-01530 Vantaa
Phone +358 9 350 87 300; Fax +358 9 350 87 320
E-Mail: fi@HARTING.com

France

HARTING France
181 avenue des Nations, Paris Nord 2
BP 66058 Tremblay en France
F-95972 Roissy Charles de Gaulle Cédex
Phone +33 1 49 38 34 00; Fax +33 1 48 63 23 06
E-Mail: fr@HARTING.com

Germany

HARTING Deutschland GmbH & Co. KG
Postfach 2451 - D-32381 Minden
Simeons carré 1 - D-32427 Minden
Phone (05 71) 88 96 - 0; Fax (05 71) 88 96 - 2 82
E-Mail: de@HARTING.com
Internet: www.HARTING.com

Office Germany

HARTING Deutschland GmbH & Co. KG
Blankenauer Straße 99; D-09113 Chemnitz
Phone +49 0371 429211; Fax +49 0371 429222
E-Mail: de@HARTING.com

Great Britain

HARTING Ltd.
Caswell Road; Brackmills Industrial Estate
GB-Northampton, NN4 7PW
Phone +44 16 04/76 66 86, 82 75 00
Fax +44 16 04/70 67 77
E-Mail: gb@HARTING.com
Internet: www.HARTING.co.uk

Hong Kong

HARTING (HK) Limited, Regional Office Asia Pacific
4208 Metroplaza Tower 1; 223 Hing Fong Road
Kwai Fong, N. T., Hong Kong
Phone +852/24 23-73 38; Fax +852/24 80-43 78
E-Mail: ap@HARTING.com
Internet: www.HARTING.com.hk

Hungary

HARTING Eastern Europe GmbH
Magyarországi Kereskedelmi Képviselete
1119 Budapest; Fehérvári út 89-95, II. emelet 217/A.
Phone +36-1-205 3464; Fax +36-1-205 3465
E-Mail: hu@HARTING.com; Internet: www.HARTING.hu

Indien

HARTING India Pvt. Ltd.
D4, Doshi Towers; 156 Poonamallee High Rd.
Kilpauk, Chennai - 600 010, INDIA
Tel. +91 44 43560415; Fax +91 44 4356 0417
pushpendra.singh@HARTING.com; www.HARTING.com

Italy

HARTING SpA
Via Dell' Industria 7; I-20090 Vimodrone (Milano)
Phone +39 02/25 08 01; Fax +39 02/2 65 05 97
E-Mail: it@HARTING.com

Japan

HARTING K. K.
Yusen Shin-Yokohama 1 Chome Bldg., 2F
1-7-9, Shin-Yokohama; Kohoku-ku, Yokohama
222-0033 Japan
Phone +81 45 476 3456; Fax: +81 45 476 3466
E-Mail: jp@HARTING.com
Internet: www.HARTING.co.jp

Korea

HARTING Korea Limited
#308 Leaders Bldg., 342-1, Yatap-dong, Bundang-gu,
Sungnam-City, Kyunggi-do, 463-828, Korea
Phone +82-31-781-4615; Fax +82-31-781-4616
E-Mail: kr@HARTING.com

Netherlands

HARTING B.V.
Larenweg 44; NL-5234 KA 's-Hertogenbosch
Postbus 3526; NL-5203 DM 's-Hertogenbosch
Phone +31 73/641 04 04
Fax +31 73/644 06 99
E-Mail: nl@HARTING.com

Norway

HARTING A/S,
Østensjøveien 36, N-0667 Oslo,
Phone +47 22/70 05 55
Fax +47 22/70 05 70
E-Mail: no@HARTING.com

Poland

HARTING Eastern Europe GmbH
Przedstawicielstwo w Polsce
ul. Kamieńskiego 201-219
51-126 Wrocław
Phone +48 71-352 81 71; Fax +48 71-320 74 44
E-Mail: pl@HARTING.com; Internet: www.HARTING.pl

Portugal

HARTING Iberia, S. A.
Avda. Josep Tarradellas, 20-30, 4º 6º
E-08029 Barcelona
Phone +351.219.673.177; Fax +351.219.678.457
E-Mail: es@HARTING.com

Russia

HARTING ZAO
ul. Tobolskaja 12, Saint Petersburg 194044 Russia
Phone +7/8 12/3 27 64 77; Fax +7/8 12/3 27 64 78
E-Mail: ru@HARTING.com
Internet: www.HARTING.ru

Singapore

HARTING Singapore Pte Ltd.
No. 1 Coleman Street; #B1-21 The Adelphi
Singapore 179803
Phone +656 2 25 52 85; Fax +656 2 25 99 47
E-Mail: sg@HARTING.com

Spain

HARTING Iberia S.A.
Josep Tarradellas 20-30 4º 6º; E-08029 Barcelona
Phone +34 933 638 475; Fax +34 934 199 585
E-Mail: es@HARTING.com

Sweden

HARTING AB
Gustavslundsvägen 141 B 4tr; 167 51 Bromma
Phone +46 8/4 45 71 71; Fax +46 8/4 45 71 70
E-Mail: se@HARTING.com

Switzerland

HARTING AG
Industriestrasse 26; CH-8604 Volketswil
Phone +41 44 908 20 60; Fax +41 44 908 20 69
E-Mail: ch@HARTING.com

Taiwan

HARTING R.O.C. Limited
Room 1, 5th Floor, No. 495, GuangFu South Road
Taipei, 110 Taiwan
Phone +886-2-2758-61 77
Fax +886-2-2758-71 77
E-Mail: tw@HARTING.com

USA

HARTING Inc. of North America
1370 Bowes Road; Elgin, Illinois 60123
Phone +1 (877) 741-1500 (toll free)
Fax +1 (866) 278-0307 (Inside Sales)
Fax +1 (847) 717-9430 (Sales and Marketing)
E-Mail: us@HARTING.com
Internet: www.HARTING-USA.com

Eastern-Europe

HARTING Eastern Europe GmbH
Bamberger Straße 7; D-01187 Dresden
Phone +49 351 / 4361760
Fax +49 351 / 4361770
E-Mail: Eastern.Europe@HARTING.com

Other countries

HARTING Electric GmbH & Co. KG
P.O. Box 14 73, D-32328 Espelkamp
Phone +49 57 72/47-97 100
Fax +49 57 72/47-4 95
E-Mail: electric@HARTING.com

Representatives – worldwide



Argentina

Condelectric S.A.
Hipólito Yrigoyen 2591
(B1640HFY) Martínez, Buenos Aires
Phone + Fax +54 11 4836-1053
E-Mail: info@condelectric.com.ar

Bulgaria COMET ELECTRONICS

16, Tsar Samuil Str., BG-1000 Sofia
Phone +359-2-9155800; Fax +359-2-9540384
E-Mail: office@comet.bg; Internet: www.comet.bg

Canada Chartwell Electronics Inc.

140 Duffield Drive; Markham; Ontario L6G 1B5
Phone +1 905-513-7100; Fax +1 905-513-7101
Toll Free +1 877-513-7769; www.chartwell.ca

Denmark Knud Wexøe A/S

Skaettekaeret 11, P.O. Box 152; DK-2840 Holte
Phone +45 45 46 58 00; Fax +45 45 46 58 01
E-Mail: wexoe@wexoe.dk
Internet: www.wexoe.dk

Estonia SKS-tehnika Oü

Mustamäe tee 55, EE-10621 Tallinn
Phone +372 6819 234; Fax +372 6819 235
E-Mail: peeter.kuus@sksf.fi

Finland SKS-automaatio OY

Martinkyläntie 50, FIN-01721 Vantaa
Phone +358 9 852 661; Fax +358 9 852 68 20
E-Mail: automaatio@sksf.fi

Hungary Mile Kft.

Mádi u. 52, H-1104 Budapest
Phone +36-1-431-9800; Fax +36-1-431-9817
E-Mail: milekft@mile-kft.hu
Internet: www.mile-kft.hu

Island Smith & Norland

Nóatún 4, IS - 105 Reykjavík
Phone +354 520 3000; Fax +354 520 3011
E-Mail: olaf@sminor.is; Internet: www.sminor.is

Israel MIGVAN

Technologies & Engineering Ltd.
13 Hashilo St., P.O.Box 7022
IL - Petach Tikva 49170
Phone +972 3 9240784; Fax +972 3 9240787
E-Mail: info@mte.co.il; Internet: www.mte.co.il

Poland Soyter Sp. z o. o.

ul. Warszawska 3, 05-082 Warszawa - Stare Babice
Phone +48 22 722 0 685; Fax +48 22 722 0 550
E-Mail: handlowy@soyter.com.pl
Internet: www.soyter.com

South-Africa HellermannTyton Pty Ltd.,

Private Bag X158 Rivonia 2128
34 Milky Way Avenue; Linbro Business Park 2065
Johannesburg, South Africa
Phone +27 (0)11 879-66 00; Fax +27 (0)11 879-66 06
E-Mail: sales.jhb@hellermann.co.za

Switzerland Distrelec AG

Grabenstrasse 6, CH-8606 Nänikon
Phone +41 1 944 99 11; Fax +41 1 944 99 88
E-Mail: info@distrelec.com
Internet: www.distrelec.com

Turkey Gökhan Elektrik San. Tic. Ltd. Sti.

Perpa Elektrikçiler Is Merkezi A Blok
Kat:7-8-9 No.694; TR - 80270 Okmeydanı/Istanbul
Phone +90 (212) 2 21 32 36 (pbx)
Fax +90 (212) 2 21 32 40
E-Mail: gokhan@gokhanelektrik.com
Internet: www.gokhanelektrik.com

Ukraine Incomtech Ltd.

4 Lermontovskaya St., UA-04050 Kiev
Phone +380-44-213-3641; Fax +380-44-213-3814
E-Mail: eletech@incomtech.com.ua
Internet: www.incomtech.com.ua

Distributors – worldwide



Farnell InOne

www.farnellinone.com;
in US: Newark InOne: www.newarkinone.com

RS Components

www.rs-components.com;
in US: Allied Electronics: www.alliedelec.com

Global Business Unit Electric



HARTING Electric GmbH & Co. KG

P.O. Box 14 73

D-32328 Espelkamp

Phone +49 57 72/47-97 100

Fax +49 57 72/47-4 95

E-Mail: HARTING.electric@HARTING.com

Internet: www.HARTING.com