

- A. QUANTITY: SINGLE PACK
B. BAG TO BE MARKED: AMPHENOL RF, 135104-02-XX.XX, AND DATE CODE

UNLESS OTHERWISE SPECIFIED, TOLERANCES ARE AS FOLLOWS: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES ±.015 (0,381 mm) ±.005 (0,127 mm) ± 1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	SEE NOTES	MATERIAL	DRAWN KARTHIK R	DATE 11-Mar-14	TITLE SMA RIGHT ANGLE CRIMP PLUG TO SMA RIGHT ANGLE CRIMP PLUG USING RG 174/U COAXIAL CABLE, VARIOUS LENGTHS			Amphenol Connex		
		REFERENCE	ENGINEER KARTHIK R	DATE 11-Mar-14						
			APPROVED B.C. GLEISSNER	DATE 25-Mar-14						
			CAD FILE			DWG SIZE B	DRAWING NO. 135104-02-XX.XX		REV B	
							SCALE: 2.5:1		SHEET 2 OF 2	