


Integrated Pressure Transducer IPT

Honeywell's Integrated Pressure Transducer (IPT) provides high accuracy pressure data in an industry standard SPI digital format. The core of the IPT is a proven Honeywell silicon piezoresistive pressure sensor with both pressure and temperature sensitive elements. The IPT is small and lightweight and can be easily integrated by the user into a wide variety of applications that require high performance in a small package. Applying the coefficients stored in the on-board EEPROM to the normalized IPT pressure and temperature output yields highly accurate and stable pressure readings over the -40 to 85°C compensated temperature range.

APPLICATIONS:

- Air Data Computers
- Altimeters
- Cabin Air Pressure
- Engine Test Systems
- Flight Test Systems
- Meteorology
- Flow and Pressure Calibrators
- Instrumentation and Analytical Equipment
- Research and Development





FEATURES AND BENEFITS

ISO-9001
ISO-14001

- | | |
|--|---|
| <ul style="list-style-type: none"> ▶ High Accuracy Over a Wide Temperature Range
From -40 to 85°C
±0.04% FS Total Error Band (absolute pressure),
to ±0.10% FS Total Error Band (gauge/ differential pressure) ⁽¹⁾ ▶ Digital SPI Output ▶ Small and Versatile | <ul style="list-style-type: none"> ▶ Stored Correction Coefficients in EEPROM – Ready to use; No additional pressure and temperature calibration necessary.
Simplifies System Design – No additional signal compensation needed to achieve a highly accurate pressure reading. ▶ Industry Standard Interface – Ready communication between a µController/µProcessor and the IPT. ▶ Volume ~ 1 in³ (16 cm³)
Lightweight – Less than 10 grams.
Media Interface – Handles most dry gas media. |
|--|---|

DIMENSIONS



SPECIFICATIONS

Performance Specifications⁽¹⁾

Total Error Band: (from -40 to 85°C)

±0.04%FS absolute

±0.10%FS gauge, differential

±0.20%FS 1 psi gauge

Temperature Range:

Operating: -40 to 85°C (-40 to 185°F)

Storage: -55 to 125°C (-67 to 257°F)

Pressure Sensor Temperature Error: ±1°C typ.

Long Term Stability⁽⁵⁾:

0.025% FS max per year

Mechanical Specifications

Pressure Ranges and Type:

See Ordering Information at right

Pressure Units: PSI⁽²⁾

Media Compatibility: Suitable for non-condensing, non-corrosive, and non-combustible gases.

Weight⁽³⁾: ~8.0 grams (absolute)

~9.7 grams (gauge, differential)

Electrical Specifications

Output:

24-bit pressure value

16-bit temperature value

256 x 8 EEPROM configuration

Power Requirements:

Supply Voltage: 4 to 12 VDC

Current Consumption:

6 mA typical, 7.5 mA max

Interface: 3.3V SPI (mode 1,1) SCLK ≤5 Mhz

Update Rate: 166 samples/second

Environmental Features

Overpressure: 3x FS

Burst Pressure: 3x FS

Mechanical Shock: DO-160E Section 7.0,

Category A, Figure 7.2, Operational Standard

Thermal Shock: Storage Temperature Cycling per JESD22-104, Section 5.0: -55°C to +125°C

Vibration: DO-160E Section 8, Category H,

Aircraft Type 2, Aircraft Zones 1 & 2


RoHS Compliant (2002/05/EC): Yes

ORDERING INFORMATION

IPT Integrated Pressure Transducer

IPT	FULL SCALE PRESSURE RANGE		
	Absolute	Gauge	Differential
0001	N/A	1 PSIG ⁽¹⁾	1 PSID
0002	N/A	2 PSIG	2 PSID
0005	N/A	5 PSIG	5 PSID
0010	N/A	10 PSIG	10 PSID
0020	20 PSIA	20 PSIG	20 PSID
0050	50 PSIA	N/A	N/A
Example:	TYPE		
	P1 Pressure		
	P2 Pressure		
	N/A		
	A	Absolute	0 (vacuum) to FS
	G	Gauge	Reference to FS
	D	Differential	+FS to -FS rel. to P2
			+FS to -FS rel. to P1
DIGITAL INTERFACE VOLTAGE			
	33	3.3 volts	
POWER SUPPLY			
	R	Regulated, 4-12VDC	
OPTIONS			
	A	Demonstration Kit ⁽⁴⁾	
IPT	0020	A	33 R -A

CONNECTOR



⁽¹⁾ Total Error is the sum of worst case linearity, repeatability, hysteresis, thermal effects, and calibration errors over the operating temperature range. Accuracy is only achieved after applying the correction coefficients and algorithm as shown in section 3.2. of Product Specification (FS = Full Scale). For total error calculations of differential units, "Full Scale" is the pressure difference between the minimum and maximum pressures. For example, full scale for a 1 psid PPT is 2 psi (-1 to +1 psi). Pressure range 1psi gauge has total error of ±0.20% FS. ⁽²⁾ After applying the correction coefficients stored in EEPROM, the resultant pressure reading is expressed in PSI (pounds per square inch). ⁽³⁾ Not including mounting hardware. ⁽⁴⁾ Demonstration kit includes RS-232 Cable, Demo Board, AC adapter, MS Windows Software, and User's Manual. ⁽⁵⁾ Beyond max. total error band when continuously powered at 25±10°C, <90%RH and 28 to 32 inHg atmospheric pressure.

Find out more

For more information on Honeywell's Precision Pressure Transducers visit us online at www.pressuresensing.com or contact us at 1-800-601-3099 (International: 1-602-365-3099). Customer Service Email: D&Sorders@honeywell.com.

Honeywell reserves the right to make changes to improve reliability, function or design. Honeywell does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights nor the rights of others.

Honeywell
12001 Highway 55
Plymouth, MN 55441
www.pressuresensing.com

ADS-14184
July 2014
©2012 Honeywell International Inc.

Honeywell