


CONNETTORE TIPO B (CON MOLLA DI RITEGNO INTERNA)
CONNECTOR TYPE B (WITH INTERNAL SPRING)

SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



CAVITA' ADATTA PER TERMINALI JUNIOR POWER TIMER:

CONTATTO P/N 929939-1 0 -3 CON GOMMINO P/N 828904-1
CAVO ISOLANTE RIDOTTO Ø1.5-2.1mm; SEZIONE 0.5-1.0mm²


CONTATTO P/N 929937-1 0 -3 CON GOMMINO P/N 828905-1
(O GOMMINO P/N 282536-1 SOLO PER CAVI SEZIONE 2.5mm²)
CAVO ISOLANTE RIDOTTO Ø2.2-3.0mm; SEZIONE 1.5-2.5mm²

CAVITY SUITABLE FOR JUNIOR POWER TIMER CONTACT:

CNT. P/N 929939-1 OR -3 PLUS WIRE SEAL P/N 828904-1
REDUCED INS. CABLE Ø1.5-2.1mm; WIRE RANGE 0.5-1.0mm²

CNT. P/N 929937-1 OR -3 PLUS WIRE SEAL P/N 828905-1
(OR WIRE SEAL P/N 282536-1 ONLY FOR WIRE SECT. 2.5 mm²)
REDUCED INS. CABLE Ø2.2-3.0mm; WIRE RANGE 1.5-2.5mm²

- PER DIMENSIONI CONTROPARTE VEDERE FOGLIO 2 DI 2.
(- FOR PIN HEADER DIMENSIONS SEE SHEET 2 OF 2).



ROSSO (RED)	282788-8
GIALLO (YELLOW)	282788-7
MARRONE (BROWN)	282788-6
BLU (BLUE)	282788-5
VERDE (GREEN)	282788-4
NATURALE (NATUR)	282788-3
GRIGIO (GREY)	282788-2
NERO (BLACK)	282788-1

3	\\\\\\\\\\\\\\	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)
2	NATURALE (NATURAL)	GOMMA (RUBBER)	GUARNIZIONE (RUBBER GASKET)
1	\\\\\\\\\\\\\\	PA 6.6	BLOCCHETTO (HOUSING)
N° (ITEM)	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)




CUSTOMER DWG. FOR REFERENCE ONLY
DISEGNO PER CLIENTE SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED - RELEASE FOR PUBLICATION 19			
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING			
TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)	DIAM. ISOLANTE (INS. DIA. RANGE) 1.5-3.0 (REDUCED INS. CABLE)	RANGO FILO (WIRE RANGE) 0.5-2.5 mm ²	SCALA (SCALE) ***

C	ECR-14-003472	MP	24 MAR 2014
B	IN PRODUZIONE (RELEASED FOR PRODUCTION) EC ET00-0325-96	A.F.	26 JUL '96
A1	REVISED PER EC ET00-0096	A.F.	26 FEB '96
A	FIRST ISSUE PER EC ET00-0004-96 (PROP. NO. WAS 95-51276)	R.M.	03-01 '96
REV. (REV. LTR.)	REVISIONI (REVISION RECORD)	DIS. DATA (DR. DATE)	APP. DATA (APP. DATE)

ANGOLI (ANGLES) ± 0.3 ± 2°			
DIS. 22 DEC 95 (DR.) R. MARTINI			
CONT. 22 DEC 95 (CHK) C. TARTARI			
LOC.	SIZE	NUMERO (CONG NO)	REV.
I	A3	C-282788	C
DESCRIZIONE (DESCRIPTION) 2 POS. SPLASH PROOF CONN. ASS'Y with SECONDARY LOCK			FOGLIO (SHEET) 1 DI 2 (1 OF 2)

DISTRIBUZIONE
(PRINT DIST.)



DETT. CONTATTO SC. 5:1
(TAB DETAIL SC. 5:1)

NOTE (NOTES):

- QUOTE APPLICABILI PER SFORMATURA PEZZO
(RIGHT DIMENSIONS FOR EXTRACTION ITEM
FROM THE MOULD)
- MATERIALE CONTATTI: LEGA DI RAME STAGNATA,
ES. OTTONE STAGNATO.
(TAB MATERIAL: TINNED CU ALLOY,
E.G. TINNED BRASS)
- MATERIALE BLOCCHETTO: TERMOPLASTICO CARICATO
FIBRA VETRO.
(HOUSING MATERIAL: THERMOPLASTIC
GLASS FIBER FILLED).

FORMA ALTERNATIVA PERMESSA CON RAGGIO
(ALLOWED ALTERNATIVE PROFILE WITH RADIUS)

FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO		19	
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION		19	
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)	
± 0.3		RANGO FILO (WIRE RANGE)		SCALA (SCALE)	
ANGOLI (ANGLES)		SEE SHEET 1		SEE SHEET 1 ***	
DIS. (DR.)		DESCRIZIONE (DESCRIPTION)		2 POS. SPLASH PROOF CONN. ASS'Y with SECONDARY LOCK	
CONT. (CHK.)		LOC. SIZE NUMERO (DWG NO)		REV. FOGLIO (SHEET)	
SEE SHEET 1 OF 2		I A3 C-282788		- 2 (OF) 2	
REV. (REV. DATE)		REVISIONI (REVISION RECORD)		DIS. DATA (DR. DATE)	
APP. (APP.)		APP. (APP.)		APP. (APP.)	