



Home: Crimp Housings &gt;

**Part Number: 48103-1512**

2.50mm Pitch, Wire-to-Board, 15 Circuits, Crimp Housing, Red

Image not available

**Status:** OBSOLETE  
**Replacement:** Contact Molex  
**Series:** 48103  
**Category:** Crimp Housings

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)  
[Email this page](#)
Go to [Part Detail](#) ▾

Series image - Reference only

**Mates With Part(s):**  
[48104](#), [48147](#)

**Use With Part(s):**  
[48102](#)

**Application Tooling****FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**[Check our list of old tooling that used to be available for this part](#)**Product Environmental Compliance**[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, &amp; Low-Halogen

Multiple Part Industry Compliance Documents

\*IPC 1752A Class C

\*IPC 1752A Class D

\*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? Email [ProductCompliance@molex.com](mailto:ProductCompliance@molex.com)Request Molex's CMRT from [conflictminerals@molex.com](mailto:conflictminerals@molex.com)**Part Detail****COLLAPSE ALL****General**

Status	Obsolete
Category	Crimp Housings
Series	<a href="#">48103</a>
Application	Signal
Product Name	N/A
UPC	822348527267

**Physical**

Circuits (maximum)	15
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-25°C to +85°C

**Agency Certification**

Please find UL Certificates by searching the UL Database using the Molex Series Number.  
[Click here to visit the UL Database](#)

CSA	LR19980
UL	E29179

**Agency Certifications****Product Categories****Resources****Stay Connected****Support****Feedback****Help****Feedback**