

# UNO-2170

## Intel® Celeron® M Automation Computer with 2 x LAN, 4 x COM, PC/104



### Features

- Onboard Celeron® M 600 MHz or Celeron M 1.0 GHz
- Onboard 512 KB battery-backup SRAM
- Two RS-232 and two RS-232/422/485 ports with automatic flow control
- Two 10/100Base-T RJ-45 ports
- Two USB and one type I/II PC card
- PC/104 expansion slots
- Windows® CE 5.0 & 6.0, Windows XP Embedded, and Linux ready solution
- Onboard system status LED indicators
- Supports Boot from LAN function
- Fanless design with no internal cabling
- Isolation between chassis and power ground

### Introduction

The UNO-2170 is an Automation Computer that supports PC/104 expansion, serial communication ports and several other networking interfaces. UNO-2170 supports Windows XP Embedded OS and Windows CE 5.0 & 6.0, which offers a pre-configured image with optimized onboard device drivers. Windows XP Embedded delivers the power of the Windows operating system in componentized form. You can seamlessly integrate your applications into Windows XP Embedded and speed up your system development with an application ready platform that can provide a rich networking interface to fulfill diverse requirements.

### Specifications

#### General

- **Certification** CE, FCC class A, UL, CCC
- **Dimensions (W x D x H)** 255 x 152 x 50 mm (10" x 6.0" x 2.0")
- **Enclosure** Aluminum
- **Mounting** Wallmount
- **Industrial Grounding** Isolation between chassis and power ground
- **Power Consumption** 24 W (Typical)
- **Power Requirements** 9 ~ 36 V<sub>DC</sub> (e.g. +24 V @ 2 A) (Min. 48 W), AT
- **Weight** 1.6 kg
- **OS Support** WES Windows XP Embedded, Windows 2000/XP, Windows CE 5.0 & 6.0, Linux, QNX
- **System Design** Fanless with no internal cabling
- **Remote Management** Built-in Advantech DiagAnywhere agent on Windows CE / XPe

#### System Hardware

- **CPU** Celeron M 600 MHz, Celeron M 1.0 GHz
- **Memory** 256 MB/512 MB DDR SDRAM built-in
- **Battery Backup SRAM** 512 KB
- **Indicators** LEDs for Power, IDE, Alarm for battery backup SRAM, LAN (Active, Status) and Serial (Tx, Rx)
- **Keyboard/Mouse** 1 x PS/2
- **PC Card** 1 x PC Card slot, supports CardBus (Card-32) Card and 16-bit (PCMCIA 2.1/JEIDA4.2) card Supports +5, +3.3 and +12 V @ 120 mA working power
- **PC/104 Slot** 2 x PC/104 slots (optional). Supports +5 V power
- **Printer Port** 1 x printer port
- **Storage** SSD: 1 x internal type I/II CompactFlash® slot  
HDD: Built-in one 2.5" SATA HDD bracket
- **Display** DB15 VGA connector, 1600 x 1200 @ 85 Hz

- **Watchdog Timer** Programmable 256 levels timer interval, from 1 to 255 sec

#### I/O Interface

- **Serial Ports** 2 x RS-232, 2 x RS-232/422/485 with DB9 connectors  
Automatic RS-485 data flow control
- **Serial Port Speed** RS-232: 50 ~ 115.2 kbps  
RS-422/485: 50 ~ 921.6 kbps (Max.)
- **LAN** 2 x 10/100 Base-T RJ-45 ports (Built-in boot ROM in flash BIOS)
- **USB Ports** 2 x USB, EHCI, Rev. 2.0 compliant

#### Environment

- **Humidity** 95% @ 40°C (non-condensing)
- **Operating Temperature** (IEC 60068-2-2, 100% CPU/ I/O loading)  
-20 ~ 50°C (-4 ~ 122°F) @ 5 ~ 85% RH.
- **Shock Protection** IEC 68 2-27  
CompactFlash: 50 G @ wall mount, half sine, 11 ms  
HDD: 20 G @ wall mount, half sine, 11 ms
- **Vibration Protection** IEC 68 2-64 (Random 1 Oct./min, 1hr/axis.)  
CompactFlash: 2 Grms @ 5 ~ 500 Hz,  
HDD: 0.5 Grms @ 5 ~ 500 Hz

### Ordering Information

- **UNO-2170-C00BE** Celeron M 600 MHz Automation Computer
- **UNO-2170-C11BE** Celeron M 1 GHz Automation Computer

#### Accessories

- **UNO-PCM21-AE** 2 x PC/104 expansion kit for UNO-2170
- **UNO-FPM21-AE** UNO-2000 series VESA mount kit
- **PCLS-DIAGAW10** Advantech Remote Monitoring & Diagnosis Utility