

D

C

B

A







D

C

B

A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		B1	Released as per ECR-08-012339	15-May-08	SP	TS



PN 0-1 AS SHOWN

NOTES:

- SUITABLE CRIMP CONTACTS: HSS SERIES
DRAWING NUMBER : 1105151
- SUITABLE HOODS / HOUSINGS :
SERIES HA3 SIZE 1
CUSTOMER DRAWING: 1106405/1102105
- SUITABLE EXTRACTION TOOL: 0-1102855-5
- STANDARDS:
DIN EN 61984; DIN EN 60664-1
- PACKAGING QTY: 10 PCS IN A BOX

		6		7	
1	0-1110998-1	CONTACT SCREW	CuZn40Pb3	NICKEL PLATED	1
1	0-1245634-1	BRAKE SYSTEM CONNECTOR INSERT	PBT GF-10%	LIGHT GREY	2
1	0-1245636-1	BRAKE SYSTEM CONNECTOR COVER	PBT GF-10%	LIGHT GREY	3
1	0-1245638-2	SOCKET CONTACT SCREW STYLE	CuZn39Pb3F44	1-2 μm Cu/2-4 μm Ag+Passivation	4
1	1-1110027-1	SCREW	STEEL	ZINC PLATED	5
1	1-1110121-7	WASHER, SERRATED LOCK	STEEL	ZINC PLATED	6
0-1	PART NO	DESCRIPTION	MATERIAL	SURFACE/COLOR	ITEM
REVISION OF EACH ASSEMBLY NO (WHEN BLANK,USE DRG. REVISION)					
PART LIST					
HG-Q.1Bu.C. 63A 300V 4kV 3					

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN S.Prakash 30-Aug-2007	Tyco Electronics AMP GmbH D-53819, Neunkirchen, Germany		
DIMENSIONS: mm		CHK T.Schnurfeit 30-Aug-2007	NAME Brake System Connector Socket Housing Assembly,HG-Q.1Bu.C		
TOLERANCES UNLESS OTHERWISE SPECIFIED: mm ISO 8015 m, ISO 2768 - m, -f m, DIN 9137 - 00		APVD T.Schnurfeit 30-Aug-2007	SIZE A2		
0 PLC ± 1 PLC ±0.5 2 PLC ±0.33 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ± FINISH		PRODUCT SPEC 108-74016 APPLICATION SPEC 114-74013 WEIGHT -	DRAWING NO C=1108840		
MATERIAL 6		CUSTOMER DRAWING			RESTRICTED TO -
		SCALE 3:1			SHEET 1 OF 1
					REV B1