



© COPYRIGHT 1988 BY SPC TECHNOLOGY. ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


REVISIONS				DOC. NO. SPC-FD05, Total Pages: 2			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKED	DATE	APPROVD
129	A	RELEASED	DJC	3/10/98	JC	3/13/98	JWM
							7/7/98



SPECIFICATIONS:

IMPEDANCE: 50 OHMS
WORKING VOLTAGE: 335 VRMS @ SEA LEVEL
FREQUENCY RANGE: 0-6 GHz
INSERTION LOSS: ≤ .1 dB MAX/1 GHz
VSWR: 1.5 MAX @ 6 GHz
FOR R3-174, 188, 188A, 316/U, ALPHA 9174, 9316,
BELDEN 8216, 83269, 83284, 84316 & TIMES LMR-100 CABLE

7	COVER	1	BRASS	GOLD
6	FERRULE	1	COPPER	GOLD
5	HOUSING	1	BRASS	GOLD
4	DIELECTRIC	1	DELTRIN	NONE
3	DIELECTRIC	1	TEFLON	NONE
2	PIN	1	BRASS	GOLD
1	BODY	1	BrCu	GOLD
ITEM	DESCRIPTION	QTY	MATERIAL	FINISH



SUGGESTED STRIPPING INSTRUCTIONS
SUGGESTED CRIMP DIES: .130
PIN TO BE SOLDERED

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SPACE CONDITIONS OF USE ARE BEYOND OUR CONTROL. THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.				DRAWING TITLE: MCX R/A CRIMP PLUG			
DRAWN BY: DANIEL CAREY		DATE: 3/10/98		SIZE: 1514		ELECTRONIC FILE: 92N3360.DWG	
CHECKED BY: JOHN COLE		DATE: 3/13/98		SCALE: NTS		SHEET: 1 OF 1	
APPROVED BY: JEFF MCVICKER		DATE: 7/7/98					