



## Film Capacitors

### Metallized Polypropylene Film Capacitors (MFP)

**Series/Type:** B32632 ... B32634

**Date:** August 2004

© EPCOS AG 2004. Reproduction, publication and dissemination of this data sheet, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.

**High pulse (wound)**

**Typical applications**

- Smoothing
- High-frequency AC loads
- TV (flyback)

**Climatic**

- Max. operating temperature: 110 °C
- Climatic category (IEC 60068-1): 55/100/56

**Construction**

- Dielectric: polypropylene (PP)
- Film metallized on one side and metal foils internally connected in series
- Contact layer of sprayed metal
- Wound capacitor technology
- Epoxy resin coating (UL 94 V-0)

**Features**

- Highest possible contact reliability
- Very high pulse strength
- Self-healing properties

**Terminals**


- Crimped wire leads, lead-free tinned, lead length (6 – 1 mm) or min. 20 mm
- Double crimped wire leads, lead-free tinned
- Straight wire leads, lead-free tinned, lead length (17 ±3 mm)
- Different lead spacings (reduced and enlarged) available, lead length (6 – 1 mm)

**Marking**

Manufacturer's logo, style and type (P6xx),  
rated capacitance (coded),  
capacitance tolerance (code letter),  
rated DC voltage, date of manufacture (coded)


**Delivery mode**

Bulk (untaped)  
Taped (Ammo pack or reel)  
For notes on taping, refer to chapter "Taping and packing".




## Dimensional drawings


Crimped leads




Double crimped leads



Straight leads




Detail of double crimped version



## Dimensions in mm

| Lead spacing | Lead diameter | Type   |
|--------------|---------------|--------|
| $e \pm 0.8$  | $d_1$         |        |
| 15.0         | 0.8           | B32632 |
| 22.5         | 0.8           | B32633 |
| 27.5         | 0.8           | B32634 |



**B32632 ... B32634**

**High pulse (wound)**

### Overview of available types

| Lead spacing    | 15.0 mm |      |      |      |      | 22.5 mm |      |      |      |      |      |
|-----------------|---------|------|------|------|------|---------|------|------|------|------|------|
| Type            | B32632  |      |      |      |      | B32633  |      |      |      |      |      |
| $V_R$ (VDC)     | 630     | 1250 | 1600 | 2000 | 3000 | 630     | 1250 | 1600 | 2000 | 2500 | 3000 |
| $V_{rms}$ (VAC) | 300     | 450  | 450  | 500  | 800  | 300     | 450  | 450  | 500  | 750  | 800  |
| $C_R$ (nF)      |         |      |      |      |      |         |      |      |      |      |      |
| 0.47            |         |      |      |      |      |         |      |      |      |      |      |
| 0.68            |         |      |      |      |      |         |      |      |      |      |      |
| 1.0             |         |      |      |      |      |         |      |      |      |      |      |
| 1.5             |         |      |      |      |      |         |      |      |      |      |      |
| 2.2             |         |      |      |      |      |         |      |      |      |      |      |
| 3.3             |         |      |      |      |      |         |      |      |      |      |      |
| 4.7             |         |      |      |      |      |         |      |      |      |      |      |
| 6.8             |         |      |      |      |      |         |      |      |      |      |      |
| 10              |         |      |      |      |      |         |      |      |      |      |      |
| 15              |         |      |      |      |      |         |      |      |      |      |      |
| 22              |         |      |      |      |      |         |      |      |      |      |      |
| 33              |         |      |      |      |      |         |      |      |      |      |      |
| 47              |         |      |      |      |      |         |      |      |      |      |      |
| 68              |         |      |      |      |      |         |      |      |      |      |      |
| 100             |         |      |      |      |      |         |      |      |      |      |      |

### Lead configurations


| Series | Standard                                                                            | Reduced                                                                             | Enlarged                                                                            | Straight                                                                            | Double crimped                                                                      |
|--------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|        |  |  |  |  |  |
| B32632 | 15 mm                                                                               | 7.5 / 10 / 12.5 mm                                                                  | 17.5 mm                                                                             | 15 mm                                                                               | 15 mm                                                                               |
| B32633 | 22.5 mm                                                                             | 15 / 17.5 / 20 mm                                                                   | 25 mm                                                                               | 22.5 mm                                                                             | 22.5 mm                                                                             |
| B32634 | 27.5 mm                                                                             | 25 mm                                                                               | —                                                                                   | 27.5 mm                                                                             | 27.5 mm                                                                             |

## Overview of available types

|                 |         |      |      |      |
|-----------------|---------|------|------|------|
| Lead spacing    | 27.5 mm |      |      |      |
| Type            | B32634  |      |      |      |
| $V_R$ (VDC)     | 630     | 1250 | 1600 | 2000 |
| $V_{rms}$ (VAC) | 300     | 450  | 450  | 500  |
| $C_R$ (nF)      |         |      |      |      |
| 10              |         |      |      |      |
| 15              |         |      |      |      |
| 22              |         |      |      |      |
| 33              |         |      |      |      |
| 47              |         |      |      |      |
| 68              |         |      |      |      |
| 100             |         |      |      |      |
| 150             |         |      |      |      |
| 220             |         |      |      |      |
| 330             |         |      |      |      |

## Lead configurations

| Series | Standard                                                                          | Reduced                                                                           | Enlarged                                                                          | Straight                                                                          | Double crimped                                                                    |
|--------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|
|        |  |  |  |  |  |
| B32632 | 15 mm                                                                             | 7.5 / 10 / 12.5 mm                                                                | 17.5 mm                                                                           | 15 mm                                                                             | 15 mm                                                                             |
| B32633 | 22.5 mm                                                                           | 15 / 17.5 / 20 mm                                                                 | 25 mm                                                                             | 22.5 mm                                                                           | 22.5 mm                                                                           |
| B32634 | 27.5 mm                                                                           | 25 mm                                                                             | —                                                                                 | 27.5 mm                                                                           | 27.5 mm                                                                           |


**B32632**
**High pulse (wound)**
**Ordering codes and packing units (lead spacing 15 mm)**

| $V_R$ | $V_{rms}$<br>$f \leq 1 \text{ kHz}$<br>VDC | $C_R$<br>nF | Max. dimensions<br>$w \times h \times l$<br>mm | Ordering code<br>(composition see<br>below) | Ammo<br>pack<br>pcs./unit | Reel<br>pcs./unit | Untaped<br>pcs./unit |
|-------|--------------------------------------------|-------------|------------------------------------------------|---------------------------------------------|---------------------------|-------------------|----------------------|
| 630   | 300                                        | 2.2         | $6.0 \times 11.5 \times 19.0$                  | B32632A6222+***                             | 900                       | 1200              | 1000                 |
|       |                                            | 3.3         | $6.0 \times 11.5 \times 19.0$                  | B32632A6332+***                             | 900                       | 1200              | 1000                 |
|       |                                            | 4.7         | $6.0 \times 11.5 \times 19.0$                  | B32632A6472+***                             | 900                       | 1200              | 1000                 |
|       |                                            | 6.8         | $6.0 \times 11.5 \times 19.0$                  | B32632A6682+***                             | 900                       | 1200              | 1000                 |
|       |                                            | 10          | $6.0 \times 11.5 \times 19.0$                  | B32632A6103+***                             | 900                       | 1200              | 1000                 |
|       |                                            | 15          | $7.0 \times 12.0 \times 19.0$                  | B32632A6153+***                             | 800                       | 1000              | 1000                 |
|       |                                            | 22          | $8.0 \times 13.5 \times 19.0$                  | B32632A6223+***                             | 700                       | 900               | 1000                 |
|       |                                            | 33          | $9.5 \times 15.5 \times 19.0$                  | B32632A6333+***                             | 600                       | 800               | 500                  |
| 1250  | 450                                        | 47          | $12.0 \times 17.0 \times 19.0$                 | B32632A6473+***                             | 450                       | 600               | 500                  |
|       |                                            | 1.0         | $6.5 \times 11.5 \times 19.0$                  | B32632A7102+***                             | 850                       | 1100              | 1000                 |
|       |                                            | 1.5         | $6.5 \times 11.5 \times 19.0$                  | B32632A7152+***                             | 850                       | 1100              | 1000                 |
|       |                                            | 2.2         | $6.5 \times 12.0 \times 19.0$                  | B32632A7222+***                             | 850                       | 1100              | 1000                 |
|       |                                            | 3.3         | $7.0 \times 12.5 \times 19.0$                  | B32632A7332+***                             | 800                       | 1000              | 1000                 |
|       |                                            | 4.7         | $7.0 \times 12.5 \times 19.0$                  | B32632A7472+***                             | 800                       | 1000              | 1000                 |
|       |                                            | 6.8         | $7.5 \times 14.0 \times 19.0$                  | B32632A7682+***                             | 750                       | 1000              | 1000                 |
|       |                                            | 10          | $9.0 \times 15.5 \times 19.0$                  | B32632A7103+***                             | 600                       | 800               | 500                  |
| 1600  | 450                                        | 15          | $12.0 \times 16.5 \times 19.0$                 | B32632A7153+***                             | 450                       | 600               | 500                  |
|       |                                            | 1.0         | $6.0 \times 11.5 \times 19.0$                  | B32632A1102+***                             | 900                       | 1200              | 1000                 |
|       |                                            | 1.5         | $6.0 \times 11.5 \times 19.0$                  | B32632A1152+***                             | 900                       | 1200              | 1000                 |
|       |                                            | 2.2         | $7.0 \times 12.0 \times 19.0$                  | B32632A1222+***                             | 800                       | 1000              | 1000                 |
|       |                                            | 3.3         | $8.0 \times 13.5 \times 19.0$                  | B32632A1332+***                             | 700                       | 900               | 1000                 |
|       |                                            | 4.7         | $9.5 \times 15.5 \times 19.0$                  | B32632A1472+***                             | 600                       | 800               | 1000                 |
|       |                                            | 6.8         | $10.5 \times 16.0 \times 19.0$                 | B32632A1682+***                             | 500                       | 700               | 500                  |
|       |                                            | 10          | $12.5 \times 17.5 \times 19.0$                 | B32632A1103+***                             | 450                       | 600               | 500                  |

Further E series and intermediate capacitance values on request.

**Composition of ordering code**

+ = Capacitance tolerance code:

K =  $\pm 10\%$

J =  $\pm 5\%$

A =  $\pm 3.5\%$

on request =  $\pm 2.5\%$

\*\*\* = Packaging code:

289 = Ammo pack

189 = Reel

010 = Untaped crimped (lead length 6 – 1 mm)


011 = Untaped crimped (lead length min. 20 mm)

008 = Untaped (straight, lead length  $17 \pm 3$  mm)

020 = Double crimped (lead length 6 – 1 mm)

Packaging codes for further lead configurations (untaped):

| Lead configuration (lead length 6 – 1 mm) | Reduced | Reduced | Reduced | Enlarged |
|-------------------------------------------|---------|---------|---------|----------|
| Lead spacing (mm)                         | 7.5 mm  | 10 mm   | 12.5 mm | 17.5 mm  |
| Packaging code                            | 030     | 040     | 050     | 060      |



### Ordering codes and packing units (lead spacing 15 mm)

| $V_R$ | $V_{rms}$<br>$f \leq 1 \text{ kHz}$ | $C_R$ | Max. dimensions<br>$w \times h \times l$<br>mm | Ordering code<br>(composition see<br>below) | Ammo<br>pack<br>pcs./unit | Reel<br>pcs./unit | Untaped<br>pcs./unit |
|-------|-------------------------------------|-------|------------------------------------------------|---------------------------------------------|---------------------------|-------------------|----------------------|
| VDC   | VAC                                 | nF    |                                                |                                             |                           |                   |                      |
| 2000  | 500                                 | 0.47  | $6.5 \times 11.5 \times 19.0$                  | B32632A2471M***                             | 850                       | 1100              | 1000                 |
|       |                                     | 0.47  | $6.5 \times 11.5 \times 19.0$                  | B32632A2471K***                             | 850                       | 1100              | 1000                 |
|       |                                     | 0.68  | $6.5 \times 12.5 \times 19.0$                  | B32632A2681M***                             | 850                       | 1100              | 1000                 |
|       |                                     | 0.68  | $6.5 \times 12.5 \times 19.0$                  | B32632A2681K***                             | 850                       | 1100              | 1000                 |
|       |                                     | 1.0   | $6.5 \times 12.5 \times 19.0$                  | B32632A2102+***                             | 850                       | 1100              | 1000                 |
|       |                                     | 1.5   | $6.5 \times 12.5 \times 19.0$                  | B32632A2152+***                             | 850                       | 1100              | 1000                 |
|       |                                     | 2.2   | $7.0 \times 13.5 \times 19.0$                  | B32632A2222+***                             | 800                       | 1000              | 500                  |
|       |                                     | 3.3   | $8.5 \times 15.0 \times 19.0$                  | B32632A2332+***                             | 650                       | 850               | 500                  |
|       |                                     | 4.7   | $10.5 \times 16.0 \times 19.0$                 | B32632A2472+***                             | 500                       | 700               | 500                  |
|       |                                     | 6.8   | $12.5 \times 17.5 \times 19.0$                 | B32632A2682+***                             | 450                       | 600               | 500                  |
| 3000  | 800                                 | 0.47  | $5.5 \times 11.0 \times 19.0$                  | B32632S4471+***                             | 1000                      | 1300              | 1000                 |
|       |                                     | 0.68  | $6.0 \times 12.0 \times 19.0$                  | B32632S4681+***                             | 900                       | 1200              | 1000                 |
|       |                                     | 1.0   | $7.5 \times 13.0 \times 19.0$                  | B32632S4102+***                             | 750                       | 1000              | 500                  |
|       |                                     | 1.5   | $8.5 \times 14.5 \times 19.0$                  | B32632S4152+***                             | 650                       | 850               | 500                  |
|       |                                     | 2.2   | $10.5 \times 16.0 \times 19.0$                 | B32632S4222+***                             | 500                       | 700               | 500                  |
|       |                                     | 3.3   | $12.5 \times 18.0 \times 19.0$                 | B32632S4332+***                             | 450                       | 600               | 500                  |

Further E series and intermediate capacitance values on request.

### Composition of ordering code

+ = Capacitance tolerance code:


K =  $\pm 10\%$   
J =  $\pm 5\%$   
A =  $\pm 3.5\%$   
on request =  $\pm 2.5\%$

\*\*\* = Packaging code:

289 = Ammo pack  
189 = Reel  
010 = Untaped crimped (lead length 6 – 1 mm)  
011 = Untaped crimped (lead length min. 20 mm)  
008 = Untaped (straight, lead length  $17 \pm 3$  mm)  
020 = Double crimped (lead length 6 – 1 mm)

Packaging codes for further lead configurations (untaped):

| Lead configuration (lead length 6 – 1 mm) | Reduced | Reduced | Reduced | Enlarged |
|-------------------------------------------|---------|---------|---------|----------|
| Lead spacing (mm)                         | 7.5 mm  | 10 mm   | 12.5 mm | 17.5 mm  |
| Packaging code                            | 030     | 040     | 050     | 060      |


**B32633**
**High pulse (wound)**
**Ordering codes and packing units (lead spacing 22.5 mm)**

| $V_R$ | $V_{rms}$<br>$f \leq 1$ kHz<br>VAC | $C_R$<br>nF | Max. dimensions<br>$w \times h \times l$<br>mm | Ordering code<br>(composition see<br>below) | Ammo<br>pack<br>pcs./unit | Reel<br>pcs./unit | Untaped<br>pcs./unit |
|-------|------------------------------------|-------------|------------------------------------------------|---------------------------------------------|---------------------------|-------------------|----------------------|
| 630   | 300                                | 22          | $6.5 \times 12.5 \times 27.5$                  | B32633A6223+***                             | 550                       | 750               | 1000                 |
|       |                                    | 33          | $7.0 \times 15.0 \times 27.5$                  | B32633A6333+***                             | 500                       | 700               | 500                  |
|       |                                    | 47          | $8.0 \times 17.0 \times 27.5$                  | B32633A6473+***                             | 450                       | 600               | 500                  |
|       |                                    | 68          | $9.5 \times 17.5 \times 27.5$                  | B32633A6683+***                             | 350                       | 500               | 500                  |
|       |                                    | 100         | $11.5 \times 19.5 \times 27.5$                 | B32633A6104+***                             | 300                       | 400               | 250                  |
| 1250  | 450                                | 10          | $7.0 \times 15.0 \times 27.5$                  | B32633A7103+***                             | 500                       | 700               | 500                  |
|       |                                    | 15          | $8.0 \times 16.0 \times 27.5$                  | B32633A7153+***                             | 450                       | 600               | 500                  |
|       |                                    | 22          | $10.0 \times 17.5 \times 27.5$                 | B32633A7223+***                             | 350                       | 500               | 500                  |
|       |                                    | 33          | $12.0 \times 19.5 \times 27.5$                 | B32633A7333+***                             | 300                       | 400               | 250                  |
|       |                                    | 47          | $14.0 \times 21.0 \times 27.5$                 | B32633A7473+***                             | 250                       | 350               | 250                  |
| 1600  | 450                                | 3.3         | $7.0 \times 13.0 \times 27.5$                  | B32633A1332+***                             | 500                       | 700               | 1000                 |
|       |                                    | 4.7         | $7.0 \times 13.0 \times 27.5$                  | B32633A1472+***                             | 500                       | 700               | 1000                 |
|       |                                    | 6.8         | $7.0 \times 16.0 \times 27.5$                  | B32633A1682+***                             | 500                       | 700               | 500                  |
|       |                                    | 10          | $8.0 \times 17.0 \times 27.5$                  | B32633A1103+***                             | 450                       | 650               | 500                  |
|       |                                    | 15          | $9.5 \times 17.5 \times 27.5$                  | B32633A1153+***                             | 350                       | 500               | 250                  |
|       |                                    | 22          | $11.5 \times 19.5 \times 27.5$                 | B32633A1223+***                             | 300                       | 400               | 250                  |
|       |                                    | 33          | $15.5 \times 22.5 \times 27.5$                 | B32633A1333+***                             | 250                       | 300               | 250                  |
| 2000  | 500                                | 2.2         | $7.0 \times 14.0 \times 27.5$                  | B32633A2222+***                             | 500                       | 700               | 1000                 |
|       |                                    | 3.3         | $7.0 \times 14.0 \times 27.5$                  | B32633A2332+***                             | 500                       | 700               | 1000                 |
|       |                                    | 4.7         | $7.0 \times 15.5 \times 27.5$                  | B32633A2472+***                             | 500                       | 700               | 500                  |
|       |                                    | 6.8         | $9.0 \times 16.5 \times 27.5$                  | B32633A2682+***                             | 400                       | 550               | 500                  |
|       |                                    | 10          | $10.5 \times 17.5 \times 27.5$                 | B32633A2103+***                             | 350                       | 450               | 250                  |
|       |                                    | 15          | $13.0 \times 20.5 \times 27.5$                 | B32633A2153+***                             | 250                       | 350               | 250                  |
|       |                                    | 22          | $15.5 \times 22.5 \times 27.5$                 | B32633A2223+***                             | 200                       | 300               | 250                  |

Further E series and intermediate capacitance values on request.

**Composition of ordering code**

+ = Capacitance tolerance code:

K =  $\pm 10\%$

J =  $\pm 5\%$

A =  $\pm 3.5\%$

on request =  $\pm 2.5\%$

\*\*\* = Packaging code:

289 = Ammo pack

189 = Reel

010 = Untaped crimped (lead length 6 – 1 mm)

011 = Untaped crimped (lead length min. 20 mm)


008 = Untaped (straight, lead length  $17 \pm 3$  mm)

020 = Double crimped (lead length 6 – 1 mm)

Packaging codes for further lead configurations (untaped):

| Lead configuration (lead length 6 – 1 mm) | Reduced | Reduced | Reduced | Enlarged |
|-------------------------------------------|---------|---------|---------|----------|
| Lead spacing (mm)                         | 15 mm   | 17.5 mm | 20 mm   | 25 mm    |
| Packaging code                            | 055     | 060     | 070     | 080      |





### Ordering codes and packing units (lead spacing 22.5 mm)

| $V_R$ | $V_{rms}$<br>$f \leq 1 \text{ kHz}$ | $C_R$ | Max. dimensions<br>$w \times h \times l$<br>mm | Ordering code<br>(composition see<br>below) | Ammo<br>pack<br>pcs./unit | Reel<br>pcs./unit | Untaped<br>pcs./unit |
|-------|-------------------------------------|-------|------------------------------------------------|---------------------------------------------|---------------------------|-------------------|----------------------|
| VDC   | VAC                                 | nF    |                                                |                                             |                           |                   |                      |
| 2500  | 750                                 | 1.0   | $7.5 \times 14.0 \times 27.5$                  | B32633A3102+***                             | 450                       | 650               | 1000                 |
|       |                                     | 1.5   | $7.5 \times 15.0 \times 27.5$                  | B32633A3152+***                             | 450                       | 650               | 1000                 |
|       |                                     | 2.2   | $8.0 \times 16.0 \times 27.5$                  | B32633A3222+***                             | 450                       | 600               | 500                  |
|       |                                     | 3.3   | $9.5 \times 16.0 \times 27.5$                  | B32633A3332+***                             | 350                       | 500               | 500                  |
|       |                                     | 4.7   | $10.0 \times 18.5 \times 27.5$                 | B32633A3472+***                             | 350                       | 500               | 500                  |
|       |                                     | 6.8   | $12.0 \times 20.5 \times 27.5$                 | B32633A3682+***                             | 300                       | 400               | 250                  |
|       |                                     | 10    | $14.0 \times 23.0 \times 27.5$                 | B32633A3103+***                             | 250                       | 350               | 250                  |
| 3000  | 800                                 | 15    | $17.0 \times 26.0 \times 27.5$                 | B32633A3153+***                             | 200                       | 300               | 200                  |
|       |                                     | 1.0   | $5.5 \times 12.0 \times 27.5$                  | B32633S4102+***                             | 650                       | 900               | 500                  |
|       |                                     | 1.5   | $6.5 \times 12.5 \times 27.5$                  | B32633S4152+***                             | 550                       | 750               | 500                  |
|       |                                     | 2.2   | $7.5 \times 14.0 \times 27.5$                  | B32633S4222+***                             | 450                       | 650               | 500                  |
|       |                                     | 3.3   | $9.0 \times 15.5 \times 27.5$                  | B32633S4332+***                             | 400                       | 550               | 500                  |
|       |                                     | 4.7   | $11.0 \times 17.0 \times 27.5$                 | B32633S4472+***                             | 300                       | 450               | 500                  |
|       |                                     | 6.8   | $13.0 \times 19.0 \times 27.5$                 | B32633S4682+***                             | 250                       | 350               | 200                  |

Further E series and intermediate capacitance values on request.

### Composition of ordering code

+ = Capacitance tolerance code:

K =  $\pm 10\%$

J =  $\pm 5\%$

A =  $\pm 3.5\%$

on request =  $\pm 2.5\%$

\*\*\* = Packaging code:

289 = Ammo pack

189 = Reel

010 = Untaped crimped (lead length 6 – 1 mm)


011 = Untaped crimped (lead length min. 20 mm)

008 = Untaped (straight, lead length  $17 \pm 3$  mm)

020 = Double crimped (lead length 6 – 1 mm)

Packaging codes for further lead configurations (untaped):

| Lead configuration (lead length 6 – 1 mm) | Reduced | Reduced | Reduced | Enlarged |
|-------------------------------------------|---------|---------|---------|----------|
| Lead spacing (mm)                         | 15 mm   | 17.5 mm | 20 mm   | 25 mm    |
| Packaging code                            | 055     | 060     | 070     | 080      |


**B32634**
**High pulse (wound)**
**Ordering codes and packing units (lead spacing 27.5 mm)**

| $V_R$ | $V_{rms}$<br>$f \leq 1 \text{ kHz}$ | $C_R$ | Max. dimensions<br>$w \times h \times l$<br>mm | Ordering code<br>(composition see<br>below) | Untaped<br>pcs./unit |
|-------|-------------------------------------|-------|------------------------------------------------|---------------------------------------------|----------------------|
| VDC   | VAC                                 | nF    |                                                |                                             |                      |
| 630   | 300                                 | 100   | $9.5 \times 18.0 \times 32.5$                  | B32634A6104+***                             | 250                  |
|       |                                     | 150   | $12.0 \times 22.0 \times 32.5$                 | B32634A6154+***                             | 200                  |
|       |                                     | 220   | $13.5 \times 22.5 \times 32.5$                 | B32634A6224+***                             | 200                  |
|       |                                     | 330   | $16.0 \times 25.5 \times 32.5$                 | B32634A6334+***                             | 150                  |
| 1250  | 450                                 | 33    | $9.5 \times 18.0 \times 32.5$                  | B32634A7333+***                             | 250                  |
|       |                                     | 47    | $11.5 \times 20.0 \times 32.5$                 | B32634A7473+***                             | 250                  |
|       |                                     | 68    | $13.0 \times 23.0 \times 32.5$                 | B32634A7683+***                             | 200                  |
|       |                                     | 100   | $16.0 \times 26.0 \times 32.5$                 | B32634A7104+***                             | 150                  |
| 1600  | 450                                 | 15    | $8.5 \times 17.0 \times 32.5$                  | B32634A1153+***                             | 500                  |
|       |                                     | 22    | $10.0 \times 18.5 \times 32.5$                 | B32634A1223+***                             | 250                  |
|       |                                     | 33    | $12.0 \times 22.0 \times 32.5$                 | B32634A1333+***                             | 250                  |
|       |                                     | 47    | $14.0 \times 22.5 \times 32.5$                 | B32634A1473+***                             | 200                  |
|       |                                     | 68    | $16.0 \times 25.5 \times 32.5$                 | B32634A1683+***                             | 150                  |
| 2000  | 500                                 | 10    | $8.5 \times 17.0 \times 32.5$                  | B32634A2103+***                             | 500                  |
|       |                                     | 15    | $10.0 \times 20.0 \times 32.5$                 | B32634A2153+***                             | 250                  |
|       |                                     | 22    | $12.0 \times 22.0 \times 32.5$                 | B32634A2223+***                             | 250                  |
|       |                                     | 33    | $15.0 \times 25.0 \times 32.5$                 | B32634A2333+***                             | 200                  |

Further E series and intermediate capacitance values on request.

**Composition of ordering code**

+ = Capacitance tolerance code:

K =  $\pm 10\%$

J =  $\pm 5\%$

A =  $\pm 3.5\%$

on request =  $\pm 2.5\%$

\*\*\* = Packaging code:

010 = Untaped crimped (lead length 6 – 1 mm)


011 = Untaped crimped (lead length min. 20 mm)

008 = Untaped (straight, lead length  $17 \pm 3$  mm)

020 = Double crimped (lead length 6 – 1 mm)


Packaging codes for further lead configurations (untaped):

|                                           |         |
|-------------------------------------------|---------|
| Lead configuration (lead length 6 – 1 mm) | Reduced |
| Lead spacing (mm)                         | 25 mm   |
| Packaging code                            | 090     |



## Technical data

|                                                                                                         |                                                                                                                                                                                                                                                             |                                                                        |                                                                                  |
|---------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------|----------------------------------------------------------------------------------|
| Operating temperature range                                                                             | Max. operating temperature $T_{op,max}$ +110 °C<br>Upper category temperature $T_{max}$ +100 °C<br>Lower category temperature $T_{min}$ -55 °C<br>Rated temperature $T_R$ +85 °C                                                                            |                                                                        |                                                                                  |
| Dissipation factor $\tan \delta$<br>at 20 °C<br>(upper limit values)                                    | $1.0 \cdot 10^{-3}$ (at 10 kHz)<br>$2.0 \cdot 10^{-3}$ (at 100 kHz)                                                                                                                                                                                         |                                                                        |                                                                                  |
| Insulation resistance $R_{ins}$<br>at 20 °C, rel. humidity $\leq 65\%$<br>(minimum as-delivered values) | 100 GΩ                                                                                                                                                                                                                                                      |                                                                        |                                                                                  |
| DC test voltage                                                                                         | $2.0 \cdot V_R$ , 2 s                                                                                                                                                                                                                                       |                                                                        |                                                                                  |
| Category voltage $V_C$<br>(continuous operation with $V_{DC}$<br>or $V_{AC}$ at $f \leq 1$ kHz)         | $T_A$ (°C)                                                                                                                                                                                                                                                  | DC voltage derating                                                    | AC voltage derating                                                              |
|                                                                                                         | $T_A \leq 85$<br>$85 < T_A \leq 100$                                                                                                                                                                                                                        | $V_C = V_R$<br>$V_C = V_R \cdot (165 - T_A)/80$                        | $V_{C,rms} = V_{rms}$<br>$V_{C,rms} = V_{rms} \cdot (165 - T_A)/80$              |
| Operating voltage $V_{op}$ for<br>short operating periods<br>( $V_{DC}$ or $V_{AC}$ at $f \leq 1$ kHz)  | $T_A$ (°C)                                                                                                                                                                                                                                                  | DC voltage (max. hours)                                                | AC voltage (max. hours)                                                          |
|                                                                                                         | $T_A \leq 85$<br>$85 < T_A \leq 100$                                                                                                                                                                                                                        | $V_{op} = 1.25 \cdot V_C$ (2000h)<br>$V_{op} = 1.25 \cdot V_C$ (1000h) | $V_{op} = 1.0 \cdot V_{C,rms}$ (2000h)<br>$V_{op} = 1.0 \cdot V_{C,rms}$ (1000h) |
| Damp heat test<br>Limit values after damp<br>heat test                                                  | 56 days/40 °C/93% relative humidity<br>Capacitance change $ \Delta C/C $ $\leq 2\%$<br>Dissipation factor change $\Delta \tan \delta$ $\leq 1.0 \cdot 10^{-3}$ (at 10 kHz)<br>Insulation resistance $R_{ins}$ $\geq 50\%$ of minimum<br>as-delivered values |                                                                        |                                                                                  |
| Reliability:<br>Failure rate $\lambda$<br>Service life $t_{SL}$                                         | 2 fit ( $\leq 2 \cdot 10^{-9}/h$ ) at $0.5 \cdot V_R$ , 40 °C<br>200 000 h at $1.0 \cdot V_R$ , 40 °C<br>For conversion to other operating conditions and temperatures,<br>refer to chapter "Quality assurance", page .                                     |                                                                        |                                                                                  |
| Failure criteria:<br>Total failure<br>Failure due to variation<br>of parameters                         | Short circuit or open circuit<br>Capacitance change $ \Delta C/C $ $> 10\%$<br>Dissipation factor $\tan \delta$ $> 4 \cdot$ upper limit value<br>Insulation resistance $R_{ins}$ $< 1500$ MΩ                                                                |                                                                        |                                                                                  |




**B32632 ... B32634**

**High pulse (wound)**

**Characteristic voltages  $V_{DC}$ ,  $V_{AC}$ ,  $V_{pp}$**

| $V_{DC}$<br>V | $V_{AC}$<br>V | $V_{pp}$<br>V |
|---------------|---------------|---------------|
| 630           | 300           | 560           |
| 1250          | 450           | 1000          |
| 1600          | 450           | 1200          |
| 2000          | 500           | 1400          |
| 2500          | 750           | 1750          |
| 3000          | 800           | 1800          |



### Pulse handling capability

"dV/dt" represents the maximum permissible voltage change per unit of time for non-sinusoidal voltages, expressed in V/ $\mu$ s.

"k<sub>0</sub>" represents the maximum permissible pulse characteristic of the waveform applied to the capacitor, expressed in V<sup>2</sup>/ $\mu$ s.

Note:


The values of dV/dt and k<sub>0</sub> provided below must not be exceeded in order to avoid damaging the capacitor.

### dV/dt values

| Lead spacing          |                         | 15 mm               | 22.5 mm | 27.5 mm |
|-----------------------|-------------------------|---------------------|---------|---------|
| V <sub>R</sub><br>VDC | V <sub>rms</sub><br>VAC | dV/dt in V/ $\mu$ s |         |         |
| 630                   | 300                     | 5 000               | 3 000   | 2 000   |
| 1250                  | 450                     | 12 000              | 7 000   | 4 500   |
| 1600                  | 450                     | 14 000              | 9 000   | 5 500   |
| 2000                  | 500                     | 17 000              | 12 000  | 7 000   |
| 2500                  | 750                     | —                   | 14 000  | —       |
| 3000                  | 800                     | 18 000              | 15 000  | —       |

### k<sub>0</sub> values


| Lead spacing          |                         | 15 mm                                      | 22.5 mm    | 27.5 mm    |
|-----------------------|-------------------------|--------------------------------------------|------------|------------|
| V <sub>R</sub><br>VDC | V <sub>rms</sub><br>VAC | k <sub>0</sub> in V <sup>2</sup> / $\mu$ s |            |            |
| 630                   | 300                     | 6 300 000                                  | 3 800 000  | 2 500 000  |
| 1250                  | 450                     | 30 000 000                                 | 17 500 000 | 11 000 000 |
| 1600                  | 450                     | 45 000 000                                 | 29 000 000 | 17 500 000 |
| 2000                  | 500                     | 68 000 000                                 | 48 000 000 | 28 000 000 |
| 2500                  | 750                     | —                                          | 59 000 000 | —          |
| 3000                  | 800                     | 108 000 000                                | 90 000 000 | —          |




B32632 ... B32634

High pulse (wound)

# Impedance $Z$ versus frequency $f$ (typical values)






Permissible AC voltage  $V_{rms}$  versus frequency  $f$  (for sinusoidal waveforms,  $T_A \leq 90^\circ\text{C}$ )


For  $T_A > 90^\circ\text{C}$ , please refer to "General technical information", section 3.2.3.

Lead spacing 15 mm


630 VDC/300 VAC




1250 VDC/450 VAC




1600 VDC/450 VAC



2000 VDC/500 VAC





**B32632**


**High pulse (wound)**

**Permissible AC voltage  $V_{rms}$  versus frequency  $f$  (for sinusoidal waveforms,  $T_A \leq 90^\circ\text{C}$ )**

For  $T_A > 90^\circ\text{C}$ , please refer to "General technical information", section 3.2.3.

**Lead spacing 15 mm**

**3000 VDC/800 VAC**






Permissible AC voltage  $V_{rms}$  versus frequency  $f$  (for sinusoidal waveforms,  $T_A \leq 90^\circ\text{C}$ )


For  $T_A > 90^\circ\text{C}$ , please refer to "General technical information", section 3.2.3.

Lead spacing 22.5 mm


630 VDC/300 VAC




1250 VDC/450 VAC




1600 VDC/450 VAC



2000 VDC/500 VAC





**B32633**


**High pulse (wound)**

**Permissible AC voltage  $V_{rms}$  versus frequency  $f$  (for sinusoidal waveforms,  $T_A \leq 90^\circ\text{C}$ )**


For  $T_A > 90^\circ\text{C}$ , please refer to "General technical information", section 3.2.3.


**Lead spacing 22.5 mm**

**2500 VDC/750 VAC**



**3000 VDC/800 VAC**






Permissible AC voltage  $V_{rms}$  versus frequency  $f$  (for sinusoidal waveforms,  $T_A \leq 90^\circ\text{C}$ )


For  $T_A > 90^\circ\text{C}$ , please refer to "General technical information", section 3.2.3.

Lead spacing 27.5 mm


630 VDC/300 VAC




1250 VDC/450 VAC




1600 VDC/450 VAC



2000 VDC/500 VAC






B32632 ... B32634

High pulse (wound)

### Flyback application

#### Permissible voltage and current / waveform


Permissible current  $I_{pp}$  versus frequency for a duty cycle of 20% ( $t_0/t = 0.2$ ):



KMK0720-5

Approximation formular for duty cycle higher than 20%:


$$I'_{pp} = I_{pp} \cdot \sqrt{\frac{t_0^3}{t^3}}$$




# Flyback application

Permissible current  $I_{pp}$  versus rated capacitance  $C_R$


Frequency = 15.75 kHz



Frequency = 31.5 kHz



Frequency = 95 kHz



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## EPCOS:

[B32632A1103J10](#) [B32632A1222J10](#) [B32632A1472K10](#) [B32632A2102J10](#) [B32633A1103J10](#) [B32633A1223J10](#)  
[B32633A1333J10](#) [B32633A2103J10](#) [B32633A2153J10](#) [B32633A2153K10](#) [B32633A2223J10](#) [B32632A1272K20](#)  
[B32632A2182J20](#) [B32633A1123J20](#) [B32633A1822J20](#) [B32632A1102J11](#) [B32632A1113J20](#) [B32632A1152J](#)  
[B32632A1332J20](#) [B32632A1471J](#) [B32632A1471K](#) [B32632A1682J20](#) [B32632A2102J](#) [B32632A2102K](#)  
[B32632A2221K](#) [B32632A6333J20](#) [B32632A6473J](#) [B32632A7103J20](#) [B32632A7113J20](#) [B32632A7123J20](#)  
[B32632A7472K](#) [B32632A7822J20](#) [B32632A7912J20](#) [B32633A1103J](#) [B32633A1103J20](#) [B32633A1133J20](#)  
[B32633A1153J](#) [B32633A1153J20](#) [B32633A1472J20](#) [B32633A1682J20](#) [B32633A1912J20](#) [B32633A2103J20](#)  
[B32633A3332K](#) [B32633A3472K](#) [B32633A7153K](#) [B32634A2103K](#) [B32634A6334J](#) [B32634A7104J](#) [B32634A7683J](#)  
[B32632A6153K289](#) [B32632A2471K289](#) [B32632A2102K289](#) [B32632A1332J289](#) [B32632A2102J289](#)  
[B32632A7472K189](#) [B32632A7103K189](#) [B32632A1332K189](#) [B32632A2471K189](#) [B32632A7332J189](#)  
[B32632A7472J189](#) [B32632A7153J189](#) [B32633A1472J189](#) [B32633A2332J189](#) [B32632A1472K20](#) [B32632A7102K](#)  
[B32633A1103K20](#) [B32633A2682J20](#) [B32634A6224K](#)