



## MOJAVE2A

**DryLine® Dehydrator, Low-pressure membrane, 19 in rack mountable, 2.0–5.0 psig, with discrete alarm, 240 Vac, 50/60 Hz**

- See related products for dc options, sold separately

### **OBSOLETE**

This product was discontinued on: **October 27, 2016**

#### **Replaced By**

MT050C


DryLine® Dehydrator, Low-pressure membrane, 19 in rack mountable, Wall mountable, 3.0 psig (2-6 adjustable), with summary and discrete alarms, 115/230 Vac, 50/60 Hz

# Product Specifications

COMMSCOPE®

MOJAVE2A

## Outline Drawing-Front



**MOJAVE FRONT VIEW**


DIMENSIONS ARE AS FOLLOWS: [ ] MILLIMETERS, INCHES

# Product Specifications

COMMSCOPE®

MOJAVE2A

## Outline Drawing-Side




MOJAVE SIDE VIEW

# Product Specifications

COMMSCOPE®

MOJAVE2A

## Outline Drawing-Back




MOJAVE BACK VIEW

# Product Specifications

COMMSCOPE®

MOJAVE2A

## Outline Drawing-Top



MOJAVE TOP VIEW

## Alarm

Alarm Type	Discrete
Excess-Run Alarm	10 minutes, factory set
High-Humidity Alarm	7.5% RH, factory set
Low-Pressure Alarm	68 mbar   7 kPa   1 psig
Power-Fail Alarm	Loss of input power

## Dimensions

Net Weight	11.8 kg   26.0 lb
Product Depth	254.0 mm   10.0 in
Product Height	222.5 mm   8.8 in
Product Width	431.8 mm   17.0 in
Product Depth, Packed	431.8 mm   17.0 in
Product Height, Packed	426.7 mm   16.8 in
Product Width, Packed	584.2 mm   23.0 in

## Electrical Specifications

Power Cord	Europe power cord with stripped leads
Voltage	240 Vac $\pm 10\%$
Alarm Contact Rating	Form C dry contacts, 2 amps at 30 Vdc
Operating Temperature	-10 °C to +50 °C (+14 °F to +122 °F)
Power Consumption, average	180.0 W
Power Frequency	60/50 Hz
Power Phase	Single
Suggested Circuit Breaker Size	15 A
Circuit Breaker Requirement	Electrical connections require separate circuits for dehydrator installation

# Product Specifications



MOJAVE2A

## General Specifications

Dehydrator Type	Automatic Membrane
Voltage Type	ac
Volume Capacity, minimum	42.5 L   1.5 ft <sup>3</sup>
Volume Capacity, maximum	1699.0 L   60.0 ft <sup>3</sup>
Brand	DryLine®
Cut In/Out Pressure Type	Factory set
Cut In Pressure	13.8 kPa   2.0 psig
Cut Out Pressure	34.5 kPa   5.0 psig
Dew Point	Better than -45 °C (-50 °F) at 95% RH at +40 °C (+104 °F)
Flow Rate, nominal	4.20 SLPM   0.15 SCFM
Includes	3/8 in polyethylene tubing   90° elbow fitting   Male connector fitting   Needle valve   Power cord   Power cord connector lock   PTFE tape   Screws
Mount Type	Floor   Rack   Shelf   Wall
Port Count	1
Port Type	3/8 in PE tube
Rack Type	EIA 19 in
Rack Units	5