

4

3

2




1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		A1	REVISED PER ECO-11-005033	01APR11	RK	HMR
			B	REVISED PER ECO-11-011073	27MAY11	TITAN	MARTIN

NOTES:

- 1 SINGLE PACK IN ACCORDANCE WITH SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH SPEC 107-3275
- 3 0.08μm Au PLATING OVER 1.27μm Ni PLATING
- 4 0.08μm Au PLATING OVER 1.27μm Ni PLATING OVER 0.76μm Cu PLATING
- 5 0.76μm Au PLATING OVER 1.27μm Ni PLATING

- 6 FOR TECHNICAL DATA REFER TO YOUR LOCAL TE CONNECTIVITY SALES OFFICE
- 7 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



RECOMMENDED
PCB LAYOUT

				1	1	1	1	BERYLLIUM COPPER 5	CENTER CONTACT	3
				1	1	1	1	PTFE	INSULATOR	2
				1	1	-	-	BRASS 4	BODY	1
				-	-	1	1	STAINLESS STEEL 3	BODY	1
				3--1	3--0	1--1	1--0	MATERIAL	DESCRIPTION	ITEM
				2	1	2	1			
QUANTITY PER ASSY									PARTS LIST	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.2

2 PLC ± 0.1

3 PLC ± 0.05

4 PLC ± -

ANGLES ± 0.5°

FINISH -

DWN
R.SMITH
10FEB04

CHK
S.PARLOW
10FEB04

APVD
F.WHEELER-KING
10FEB04

PRODUCT SPEC
108-3461

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SMA STRAIGHT PCB SOCKET RECEPTACLE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1478979

RESTRICTED TO
-

SCALE
1:1

SHEET
1 OF 1

REV
B