











- | LOC | DIST | REVISIONS | | | | | |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
| AA | 22 | P | LYR | DESCRIPTION | DATE | DWN | APVD |
| | | | C2 | REVISED PER ECO-11-005033 | 04MAY11 | RK | HMR |
1. HOUSING: PBT POLYESTER, BLACK, UL 94V-0.
TERMINALS: 0.30 THICK PHOS BRONZE PLATED WITH 1.27µm MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 2µm MINIMUM THICK MATTE TIN IN ACTION PIN COMPLIANT PIN TERMINAL AREA OVER 1.27µm MINIMUM THICK NICKEL UNDERPLATE.
SHIELD: 0.25 THICK COPPER ALLOY PLATED WITH 2.03µm MINIMUM BRIGHT TIN OVER 1.27µm MINIMUM NICKEL.
GROUND CLIPS: 0.25 THICK COPPER ALLOY PLATED WITH 2.03µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
LIGHT EMITTING DIODE (LED): DIFFUSED EPOXY LENS, 12.95 CARBON STEEL WIREFRAME LEADS PLATED WITH 8.89µm TIN/COPPER OVER 2.03µm SILVER OVER 1.02µm COPPER OVER 3.56µm NICKEL OVER 1.02µm COPPER UNDERPLATE.
LED ACTION PIN COMPLIANT PIN CONTACTS: 0.30 THICK BRASS PLATED WITH 2µm MINIMUM MATTE TIN.
2. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. ALL DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
4. TWO LEDS PER PORT, SIZE .079 X .118, SEE TABLE.
5. DRILLED HOLE DIA = .040±.001.
COPPER THICKNESS = .001-.003.
TIN THICKNESS = .0003 MIN.
6. DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
7. DATE CODE LOCATED ON REAR OF PART APPROXIMATELY AS SHOWN.
8. THESE FOUR SIDE PCB ACTION PIN GROUNDS AND CORRESPONDING PCB HOLES ARE REQUIRED ONLY ON 6116317-2, 6116317-3, 6116317-5, 6116317-6, 6116317-7, -9 AND 1--0.
9. SUGGESTED OPERATING CURRENT FOR LEDS IS 20 mA.



RED/GREEN	RED/GREEN	RED/GREEN	RED/GREEN	1-6116317-0
GREEN/YELLOW	GREEN/YELLOW	RED/GREEN	RED/GREEN	6116317-9
GREEN/YELLOW	GREEN/YELLOW	RED/GREEN	RED/GREEN	6116317-8
GREEN	GREEN	YELLOW	YELLOW	6116317-7
YELLOW	YELLOW	GREEN	GREEN	6116317-6
GREEN/YELLOW	GREEN/YELLOW	GREEN/YELLOW	GREEN/YELLOW	6116317-5
GREEN	GREEN	GREEN	GREEN	6116317-4
GREEN	GREEN	GREEN	GREEN	6116317-3
GREEN	GREEN	GREEN	GREEN	6116317-2
GREEN	GREEN	GREEN	GREEN	6116317-1
LED #4 (LOWER-RIGHT)	LED #3 (UPPER-RIGHT)	LED #2 (UPPER-LEFT)	LED #1 (LOWER-LEFT)	PART NO.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES[mm]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

9 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

5 PLC ±

6 PLC ±

7 PLC ±

8 PLC ±

9 ANGLES ±

MATERIAL

FINISH

DWN: L. VARELA - DOCKS 23JUN2005

CHK: J. WESTMAN 23JUN2005

APVD: S. FLICKINGER 23JUN2005

PRODUCT SPEC: 108-1854

APPLICATION SPEC: 114-2160

WEIGHT: 1 = 77.2 grams

CUSTOMER DRAWING

NAME: STACKED MODULAR JACK ASSEMBLY, 2X8 WITH LEDS, 8 POSITION, SHIELDED PANEL GROUND, OFFSET, CAT 5

SIZE: A1

CAGE CODE: 00779

DRAWING NO: C=6116317

RESTRICTED TO: -


SCALE: 3:1

SHEET: 1 OF 3



REV: C2


TE Connectivity

TE



LOC		DIST		REVISIONS					
AA		22		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	L. VARELA	23JUN2005	 TE Connectivity			
				CHK	J. WESTMAN	23JUN2005				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	S. FLICKINGER	23JUN2005	NAME			
INCHES[mm]				PRODUCT SPEC		STACKED MODULAR JACK ASSEMBLY, 2X8 WITH LEDS, 8 POSITION, SHIELDED PANEL GROUND, OFFSET, CAT 5				
		9 PLC ±		108-1854		SIZE				
		2 PLC ±		APPLICATION SPEC						
		3 PLC ±.005 [0.13]		114-2160						
		4 PLC ±.005 [0.13]		WEIGHT						
MATERIAL		FINISH		77.2 grams		A1 00779		DRAWING NO		
				CUSTOMER DRAWING		SCALE		RESTRICTED TO		
						3:1		-		
						SHEET				
						3				
						OF				
						3				
						REV		C2		