


Features and Benefits

- Thermal impedance:
0.48°C-in²/W (@50 psi)
- Withstands high voltages
- High dielectric strength
- Very durable



Sil-Pad K-4 uses a specially developed film which has high thermal conductivity, high dielectric strength and is very durable. Sil-Pad K-4 combines the thermal transfer properties of well-known Sil-Pad rubber with the physical properties of a film.

Sil-Pad K-4 is a durable insulator that withstands high voltages and requires no thermal grease to transfer heat. Sil-Pad K-4 is available in customized shapes and sizes.

TYPICAL PROPERTIES OF SIL-PAD K-4						
PROPERTY		IMPERIAL VALUE		METRIC VALUE		TEST METHOD
Color		Gray		Gray		Visual
Reinforcement Carrier		Kapton		Kapton		—
Thickness (inch) / (mm)		0.006		0.152		ASTM D374
Hardness (Shore A)		90		90		ASTM D2240
Breaking Strength (lbs/inch) / (kN/m)		30		5		ASTM D1458
Elongation (%)		40		40		ASTM D412
Tensile Strength (psi) / (MPa)		5000		34		ASTM D412
Continuous Use Temp (°F) / (°C)		-76 to 356		-60 to 180		—
ELECTRICAL						
Dielectric Breakdown Voltage (Vac)		6000		6000		ASTM D149
Dielectric Constant (1000 Hz)		5.0		5.0		ASTM D150
Volume Resistivity (Ohm-meter)		10 ¹²		10 ¹²		ASTM D257
Flame Rating		VTM-O		VTM-O		U.L.94
THERMAL						
Thermal Conductivity (W/m-K)		0.9		0.9		ASTM D5470
THERMAL PERFORMANCE vs PRESSURE						
Pressure (psi)		10	25	50	100	200
TO-220 Thermal Performance (°C/W)		3.66	3.43	3.13	2.74	2.42
Thermal Impedance (°C-in²/W) (1)		1.07	0.68	0.48	0.42	0.38
1) The ASTM D5470 test fixture was used. The recorded value includes interfacial thermal resistance. These values are provided for reference only. Actual application performance is directly related to the surface roughness, flatness and pressure applied.						


Typical Applications Include:

- Power supplies
- Power semiconductors
- Motor controls

Configurations Available:

- Sheet form, die-cut parts and roll form
- With or without pressure sensitive adhesive

Building a Part Number



Standard Options

NA = Selected standard option. If not selecting a standard option, insert company name, drawing number, and revision level.

1212 = Standard configuration dash number.
1212 = 12" x 12" sheets, 12/250 = 12" x 250' rolls, or 00 = custom configuration

AC = Adhesive, one side
00 = No adhesive

Standard thicknesses available: 0.006"

SPK4 = Sil-Pad K4 Material

Note: To build a part number, visit our website at www.bergquistcompany.com.

Sil-Pad®: U.S. Patents 4,574,879; 4,602,125; 4,602,678; 4,685,987; 4,842,911 and others.
Kapton® is a registered trademark of DuPont.