


FEED-THROUGH FLAT BASE EUROSTRIPS® 300V - Panel Mount

For wire-to-wire connections in HVAC, appliance, equipment, power distribution and other industrial applications with strict budget and space requirements.

Easy to use double row terminal strips are a cost-effective alternative to barrier strips or other types of terminal blocks. Simply strip the wire, insert, and tighten the screw.^a Eurostrips® feature tubular screw clamps, with or without wire protectors, and recessed metal parts for finger protection. The wire protectors include an integral wire stop in the center of the terminal. The stainless steel wire protectors exhibit excellent memory and the wire stop insures the most effective connection.


Eurostrips® described on this and the following page are available with a flat base for minimum clearance applications. They can be panel mounted or left to free float. Offered in easy to cut standard 12 pole strips, they can also be ordered precut with the required number of poles.

- Tubular Screw Clamp
- With or Without Wire Protectors
- Panel Mount or Free Float
- Housing Material: Polyamide 6.6
- Color: Opaque White
- Marking Plates or Factory Imprinted



TS1.5

Flat Base
Pole Spacing 8mm (.315)
Mounting Hole Diameter 2.8mm (.110)
Stripping Length 5mm (.197)



TS2.5

Flat Base
Pole Spacing 10mm (.394)
Mounting Hole Diameter 3.5mm (.138)
Stripping Length 6mm (.236)

Ratings

IEC/VDE

UL (File No. E148805)

CSA (File No. LR38962)

Wire Range

1.5mm²

22-12 AWG

22-16 AWG

Current

18A

20A

15A

Voltage

380V

300V

300V

Wire Range

2.5mm²

22-10 AWG

18-12 AWG

Current

26A

30A

30A

Voltage

380V

300V

300V

Ordering Information		No. of Poles	Type	Cat. No.	Length (L) mm (in.)	Std. Pk.
Eurostrip®, Flat Base with Wire Protector	2	2	TS1.5/2wp	40.002	13.6 (.53)	100
	3	3	TS1.5/3wp	40.003	21.5 (.85)	100
	4	4	TS1.5/4wp	40.004	29.5 (1.16)	100
	5	5	TS1.5/5wp	40.005	37.4 (1.47)	100
	6	6	TS1.5/6wp	40.006	45.4 (1.79)	50
	7	7	TS1.5/7wp	40.007	53.3 (2.10)	50
	8	8	TS1.5/8wp	40.008	61.3 (2.41)	50
	9	9	TS1.5/9wp	40.009	69.2 (2.72)	50
	10	10	TS1.5/10wp	40.010	77.2 (3.04)	50
	11	11	TS1.5/11wp	40.011	85.1 (3.35)	50
	12	12	TS1.5/12wp	40.012	93.0 (3.66)	50
Eurostrip®, Flat Base without Wire Protector ^b	2	2	TS1.5/2	40.052	13.6 (.53)	100
	3	3	TS1.5/3	40.053	21.5 (.85)	100
	4	4	TS1.5/4	40.054	29.5 (1.16)	100
	5	5	TS1.5/5	40.055	37.4 (1.47)	100
	6	6	TS1.5/6	40.056	45.4 (1.79)	50
	7	7	TS1.5/7	40.057	53.3 (2.10)	50
	8	8	TS1.5/8	40.058	61.3 (2.41)	50
	9	9	TS1.5/9	40.059	69.2 (2.72)	50
	10	10	TS1.5/10	40.060	77.2 (3.04)	50
	11	11	TS1.5/11	40.061	85.1 (3.35)	50
	12	12	TS1.5/12	40.062	93.0 (3.66)	50
	2	2	TS2.5/2	40.252	17.0 (.67)	100
	3	3	TS2.5/3	40.253	27.0 (1.06)	100
	4	4	TS2.5/4	40.254	37.0 (1.46)	100
	5	5	TS2.5/5	40.255	47.0 (1.85)	100
	6	6	TS2.5/6	40.256	57.0 (2.24)	50
	7	7	TS2.5/7	40.257	67.0 (2.64)	50
	8	8	TS2.5/8	40.258	77.0 (3.03)	50
	9	9	TS2.5/9	40.259	87.0 (3.43)	50
	10	10	TS2.5/10	40.260	97.0 (3.82)	50
	11	11	TS2.5/11	40.261	107.0 (4.21)	50
	12	12	TS2.5/12	40.262	117.0 (4.61)	50

For Accessories, please refer to pages 50, 51

Dimensions mm (in.)


A = 8.0 (.315) E = Ø2.8 (.110) I = 2.5 (.099)
B = M2.5 x 4.3 F = Ø5.35 (.211) J = 7.5 (.296)
C = 5.6 (.221) G = 8.0 (.315) K = 6.7 (.264)
D = 2.4 (.095) H = Ø3.0 (.118) M = 13.7 (.540)
N = 18.2 (.716)

Dimensions mm (in.)

A = 10.0 (.394) E = Ø3.5 (.137) I = 3.0 (.118)
B = M3 x 5.8 F = Ø5.7 (.225) J = 9.5 (.374)
C = 6.4 (.252) G = 10.0 (.394) K = 8.0 (.315)
D = 3.5 (.138) H = Ø3.6 (.142) M = 15.5 (.611)
N = 21.8 (.858)

^a Clamp screws are zinc chromated steel. Stainless steel or nickel plated brass screws are available, consult Altech for ordering information.

^b Use for solid wire or wire with a ferrule.



TS6

Flat Base
Pole Spacing 12mm (.472)
Mounting Hole Diameter 4.2mm (.165)
Stripping Length 7mm (.276)

Wire Range	Current	Voltage
6mm ²	44A	380V
20-8 AWG	40A	300V
18-10 AWG	40A	300V

Type	Cat. No.	Length (L) mm (in.)	Std. Pk.
TS6/2wp	40.402	20.0 (.79)	100
TS6/3wp	40.403	32.0 (1.26)	100
TS6/4wp	40.404	44.0 (1.73)	100
TS6/5wp	40.405	56.0 (2.21)	100
TS6/6wp	40.406	68.0 (2.68)	50
TS6/7wp	40.407	80.0 (3.15)	50
TS6/8wp	40.408	92.0 (3.62)	50
TS6/9wp	40.409	104.0 (4.10)	50
TS6/10wp	40.410	116.0 (4.57)	25
TS6/11wp	40.411	128.0 (5.03)	25
TS6/12wp	40.412	140.0 (5.51)	25
TS6/2	40.452	20.0 (.79)	100
TS6/3	40.453	32.0 (1.26)	100
TS6/4	40.454	44.0 (1.73)	100
TS6/5	40.455	56.0 (2.21)	100
TS6/6	40.456	68.0 (2.68)	50
TS6/7	40.457	80.0 (3.15)	50
TS6/8	40.458	92.0 (3.62)	50
TS6/9	40.459	104.0 (4.10)	50
TS6/10	40.460	116.0 (4.57)	25
TS6/11	40.461	128.0 (5.03)	25
TS6/12	40.462	140.0 (5.51)	25

Dimensions mm (in.)

A = 12.0 (.472)	E = Ø4.4 (.173)	I = 4.3 (.169)
B = M3.5 x 7	F = Ø6.8 (.268)	J = 9.5 (.374)
C = 7.6 (.299)	G = 12.0 (.472)	K = 9.0 (.354)
D = 4.3 (.169)	H = Ø4.2 (.165)	M = 17.7 (.697)
		N = 23.0 (.906)