


Number of contacts

72 +




Inserts

Han
D/DD


Identification	Series	Part No.		Drawing	Dimensions in mm
Crimp terminal	Han DD	Male insert (M)	Female insert (F)		
Order crimp contacts separately					

09 16 072 3001 09 16 072 3101




1) Distance for contacts max. 21 mm

Contact arrangement View from termination side



Panel cut out for inserts
for use without hoods/housings



Identification	Wire gauge (mm²)	Male contacts	Female contacts	Drawing	Dimensions in mm
Crimp contacts					
silver plated	0.14-0.37	09 15 000 6104	09 15 000 6204		
	0.5	09 15 000 6103	09 15 000 6203		
	0.75	09 15 000 6105	09 15 000 6205		
	1.0	09 15 000 6102	09 15 000 6202		
	1.5	09 15 000 6101	09 15 000 6201		
	2.5	09 15 000 6106	09 15 000 6206		
gold plated	0.14-0.37	09 15 000 6124	09 15 000 6224		
	0.5	09 15 000 6123	09 15 000 6223		
	0.75	09 15 000 6125	09 15 000 6225		
	1.0	09 15 000 6122	09 15 000 6222		
	1.5	09 15 000 6121	09 15 000 6221		
	2.5	09 15 000 6126	09 15 000 6226		

Wire gauge		Ø	Stripping length
0.14-0.37 mm²	AWG 26-22	0.90 mm	8 mm
0.5 mm²	AWG 20	1.10 mm	8 mm
0.75 mm²	AWG 18	1.30 mm	8 mm
1 mm²	AWG 18	1.45 mm	8 mm
1.5 mm²	AWG 16	1.75 mm	8 mm
2.5 mm²	AWG 14	2.25 mm	6 mm

Stock items in bold type