


Absolute maximum ratings

(T_a=25°C)






Symbol	Ratings		Unit
	FET 1	FET 2	
V _{DS}	150		V
V _{GS}	+20, -10		V
I _D	±5	±7	A
I _D (pulse)*1	±10	±15	A
P _T	5 (T _a =25°C, with all circuits operating, without heatsink)		W
	43 (T _c =25°C, with all circuits operating, with infinite heatsink)		W
θ _{j-a}	25 (Junction-Air, T _a =25°C, with all circuits operating)		°C/W
θ _{j-c}	2.91 (Junction-Case, T _c =25°C, with all circuits operating)		°C/W
V _{ISO}	1000 (Between fin and lead pin, AC)		Vrms
T _{ch}	150		°C
T _{stg}	-40 to +150		°C

* : PW≤100μs, duty≤50%

Equivalent circuit diagram



Characteristic curves




Electrical characteristics

(Ta=25°C)


Symbol	FET 1					FET 2				
	Specification			Unit	Conditions	Specification			Unit	Conditions
	min	typ	max			min	typ	max		
$V_{(BR)DSS}$	150			V	$I_D=100\mu A$, $V_{GS}=0V$	150			V	$I_D=100\mu A$, $V_{GS}=0V$
I_{GSS}			100	nA	$V_{GS}=20V$			100	nA	$V_{GS}=20V$
I_{DSS}			100	μA	$V_{DS}=150V$, $V_{GS}=0V$			100	μA	$V_{DS}=150V$, $V_{GS}=0V$
V_{TH}	1.0		2.0	V	$V_{DS}=10V$, $I_D=250\mu A$	1.0		2.0	V	$V_{DS}=10V$, $I_D=250\mu A$
$R_{e(yfs)}$	3	5.5		S	$V_{DS}=10V$, $I_D=2.5A$	4	9		S	$V_{DS}=10V$, $I_D=3.5A$
$R_{DS(ON)}$		330	440	m Ω	$V_{GS}=10V$, $I_D=2.5A$		150	200	m Ω	$V_{GS}=10V$, $I_D=3.5A$
		370	480	m Ω	$V_{GS}=4V$, $I_D=2.5A$		170	230	m Ω	$V_{GS}=4V$, $I_D=3.5A$
C_{iss}		380		pF	$V_{DS}=10V$,		870		pF	$V_{DS}=10V$,
C_{oss}		95		pF	$f=1.0MHz$,		320		pF	$f=1.0MHz$,
C_{rss}		25		pF	$V_{GS}=0V$		210		pF	$V_{GS}=0V$
$t_d(on)$		25		ns	$I_D=2.5A$,		25		ns	$I_D=3.5A$,
t_r		50		ns	$V_{DD}\div 70V$,		55		ns	$V_{DD}\div 70V$,
$t_d(off)$		55		ns	$R_L=28\Omega$,		80		ns	$R_L=20\Omega$,
t_f		40		ns	$V_{GS}=5V$, see Fig.3 on page 16.		50		ns	$V_{GS}=5V$, see Fig.3 on page 16.
V_{SD}		1.1	1.5	V	$I_{SD}=5A$, $V_{GS}=0V$		1.0	1.5	V	$I_{SD}=7A$, $V_{GS}=0V$
t_{rr}		180		ns	$I_F=\pm 100mA$		500		ns	$I_F=\pm 100mA$

Characteristic curves



Re(yfs)-Id Characteristics (Typical)




Safe Operating Area (SOA)



Capacitance-Vds Characteristics (Typical)



IDR-VSD Characteristics (Typical)



Pr-Ta Characteristics

