7WB3306

2-Bit Bus Switch

The 7WB3306 is an advanced high−speed low−power 2−bit bus switch in ultra−small footprints.

Features

- High Speed: t_{PD} = 0.25 ns (Max) @ V_{CC} = 4.5 V
- 3 Ω Switch Connection Between 2 Ports
- Power Down Protection Provided on Inputs
- Zero Bounce
- TTL−Compatible Control Inputs
- Ultra−Small Pb−Free Packages
- These are Pb−Free Devices

ON Semiconductor®

http://onsemi.com

MARKING DIAGRAMS

UDFN8
MU SUFFIX
CASE 517AJ





Micro8™
DM SUFFIX
CASE 846A





TSSOP8
DT SUFFIX
CASE 948AL



UDFN8
1.95 x 1.0
CASE 517CA



A	= Assembly Location
Y	= Year
W	= Work Week
M	= Date Code
▪	= Pb−Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 7 of this data sheet.



Figure 1. UDFN8
(Top Thru−View)



Figure 2. Micro8/TSSOP8
(Top View)



Figure 3. Logic Diagram

FUNCTION TABLE

Input $\overline{OEn}$	Function
L	Bn = An
H	Disconnect

MAXIMUM RATINGS

Symbol	Parameter		Value	Unit
V_{CC}	DC Supply Voltage		−0.5 to +7.0	V
V_{IN}	Control Pin Input Voltage		−0.5 to +7.0	V
$V_{I/O}$	Switch Input / Output Voltage		−0.5 to +7.0	V
I_{IK}	Control Pin DC Input Diode Current	V_{IN} < GND	−50	mA
I_{OK}	Switch I/O Port DC Diode Current	$V_{I/O}$ < GND	−50	mA
I_O	ON−State Switch Current		±128	mA
	Continuous Current Through V_{CC} or GND		±150	mA
I_{CC}	DC Supply Current Per Supply Pin		±150	mA
I_{GND}	DC Ground Current per Ground Pin		±150	mA
T_{STG}	Storage Temperature Range		−65 to +150	°C
T_L	Lead Temperature, 1 mm from Case for 10 Seconds		260	°C
T_J	Junction Temperature Under Bias		150	°C
θ_{JA}	Thermal Resistance	UDFN8 (Note 1) Micro8 TSSOP8	111 392 150	°C/W
P_D	Power Dissipation in Still Air at 85°C	UDFN8 Micro8 TSSOP8	1127 319 833	mW
MSL	Moisture Sensitivity		Level 1	
F_R	Flammability Rating Oxygen Index: 28 to 34		UL 94 V−0 @ 0.125 in	
V_{ESD}	ESD Withstand Voltage (Note 2)	Human Body Model, all pins Human Body Model, A_n/B_n to Ground Human Body Model, A_n/B_n to V_{CC}	> 1.5 > 4 > 4	kV kV kV
$I_{LATCHUP}$	Latchup Performance Above V_{CC} and Below GND at 125°C (Note 3)		±100	mA

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Measured with minimum pad spacing on an FR4 board, using 10 mm−by−1 inch, 2 ounce copper trace no air flow.
2. Tested to EIA / JESD22−A114−A.
3. Tested to EIA / JESD78.

RECOMMENDED OPERATING CONDITIONS

Symbol	Parameter		Min	Max	Unit
V_{CC}	Positive DC Supply Voltage		4.0	5.5	V
V_{IN}	Control Pin Input Voltage		0	5.5	V
$V_{I/O}$	Switch Input / Output Voltage		0	5.5	V
T_A	Operating Free−Air Temperature		−55	+125	°C
$\Delta t/\Delta V$	Input Transition Rise or Fall Rate	Control Input Switch I/O	0 0	5 DC	nS/V

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

DC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Conditions	V_{CC} (V)	T_A = 25°C			T_A = −55°C to +125°C		Unit
				Min	Typ	Max	Min	Max	
V_{IK}	Clamp Diode Voltage	$I_{I/O}$ = −18 mA	4.5			−1.2		−1.2	V
V_{IH}	High−Level Input Voltage (Control)		4.0 to 5.5	2.0			2.0		V
V_{IL}	Low−Level Input Voltage (Control)		4.0 to 5.5			0.8		0.8	V
V_{OH}	Output Voltage High	See Figure 4							
I_{IN}	Input Leakage Current	0 ≤ V_{IN} ≤ 5.5 V	5.5			±0.1		±1.0	μA
I_{OFF}	Power Off Leakage Current	$V_{I/O}$ = 0 to 5.5 V	0			±0.1		±1.0	μA
I_{CC}	Quiescent Supply Current	I_O = 0, V_{IN} = V_{CC} or 0 V	5.5			±0.1		±1.0	μA
ΔI_{CC}	Increase in Supply Current (Control Pin)	One input at 3.4 V; Other inputs at V_{CC} or GND	5.5					2.5	mA
R_{ON}	Switch ON Resistance	$V_{I/O}$ = 0, $I_{I/O}$ = 64 mA $I_{I/O}$ = 30 mA	4.5		3 3	7 7		7 7	Ω
		$V_{I/O}$ = 2.4, $I_{I/O}$ = 15 mA			6	15		15	
		$V_{I/O}$ = 2.4, $I_{I/O}$ = 15 mA	4.0		10	20		20	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

AC ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Test Condition	V_{CC} (V)	T_A = 25 °C			T_A = −55°C to +125°C		Unit
				Min	Typ	Max	Min	Max	
t_{PD}	Propagation Delay, Bus to Bus	See Figure 5	4.0 to 5.5			0.25		0.25	ns
t_{EN}	Output Enable Time	See Figure 5	4.5 to 5.5	0.8	2.5	4.2	0.8	4.2	ns
			4.0	0.8	3.0	4.6	0.8	4.6	
t_{DIS}	Output Disable Time		4.5 to 5.5	0.8	3.0	4.8	0.8	4.8	ns
			4.0	0.8	2.9	4.4	0.8	4.4	
C_{IN}	Control Input Capacitance	V_{IN} = 5 or 0 V	5.0		2.5				pF
$C_{IO(ON)}$	Switch On Capacitance	Switch ON	5.0		10				pF
$C_{IO(OFF)}$	Switch Off Capacitance	Switch OFF	5.0		5				pF

TYPICAL DC CHARACTERISTICS







Figure 4. Output Voltage High vs Supply Voltage

AC LOADING AND WAVEFORMS

Parameter Measurement Information



Test	S1
t_{PD}	Open
t_{PLZ}/t_{PZL}	7 V
t_{PHZ}/t_{PZH}	Open

*C_L includes probes and jig capacitance.



Voltage Waveforms
Propagation Delay Times



Voltage Waveforms
Enable and Disable Times

4. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control
5. All input pulses are supplied by generators having the following characteristics: PRR ≤ 10 MHz, Z_O = 50 Ω, t_r ≤ 2.5 ns, t_f ≤ 2.5 ns.
6. The outputs are measured one at a time, with one transition per measurement.
7. t_{PLZ} and t_{PHZ} are the same as t_{DIS}.
8. t_{PZL} and t_{PZH} are the same as t_{EN}.
9. t_{PHL} and t_{PLH} are the same as t_{PD}.

Figure 5. t_{PD}, t_{EN}, t_{DIS} Loading and Waveforms

ORDERING INFORMATION

Device	Package	Shipping†
7WB3306MUTAG	UDFN8 (Pb−Free)	3000 / Tape & Reel
7WB3306DMR2G	Micro8 (Pb−Free)	4000 / Tape & Reel (In Developmant)
7WB3306DTR2G	TSSOP8 (Pb−Free)	5000 / Tape & Reel
7WB3306DMUTCG	UDFN8, 1.95 x 1.0, 0.5 mm Pitch (Pb−Free)	3000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS

UDFN8 1.8 x 1.2, 0.4P
CASE 517AJ
ISSUE O









NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30 mm FROM TERMINAL TIP.
4. MOLD FLASH ALLOWED ON TERMINALS ALONG EDGE OF PACKAGE. FLASH MAY NOT EXCEED 0.03 ONTO BOTTOM SURFACE OF TERMINALS.
5. DETAIL A SHOWS OPTIONAL CONSTRUCTION FOR TERMINALS.

	MILLIMETERS	
DIM	MIN	MAX
A	0.45	0.55
A1	0.00	0.05
A3	0.127 REF	
b	0.15	0.25
b2	0.30 REF	
D	1.80 BSC	
E	1.20 BSC	
e	0.40 BSC	
L	0.45	0.55
L1	0.00	0.03
L2	0.40 REF	

MOUNTING FOOTPRINT*
SOLDERMASK DEFINED



DIMENSIONS: MILLIMETERS

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

UDFN8 1.95x1.0, 0.5P
CASE 517CA
ISSUE O



NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.20 MM FROM TERMINAL TIP.
4. PACKAGE DIMENSIONS EXCLUSIVE OF BURRS AND MOLD FLASH.

	MILLIMETERS	
DIM	MIN	MAX
A	0.45	0.55
A1	0.00	0.05
A3	0.13 REF	
b	0.15	0.25
D	1.95 BSC	
E	1.00 BSC	
e	0.50 BSC	
L	0.25	0.35
L1	0.30	0.40

RECOMMENDED SOLDERING FOOTPRINT*



DIMENSIONS: MILLIMETERS

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

Micro8™
CASE 846A
ISSUE H



NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSION A DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS. MOLD FLASH, PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.15 (0.006) PER SIDE.
4. DIMENSION B DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION. INTERLEAD FLASH OR PROTRUSION SHALL NOT EXCEED 0.25 (0.010) PER SIDE.
5. 846A–01 OBSOLETE, NEW STANDARD 846A–02.

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
A	––	––	1.10	––	––	0.043
A1	0.05	0.08	0.15	0.002	0.003	0.006
b	0.25	0.33	0.40	0.010	0.013	0.016
c	0.13	0.18	0.23	0.005	0.007	0.009
D	2.90	3.00	3.10	0.114	0.118	0.122
E	2.90	3.00	3.10	0.114	0.118	0.122
e	0.65 BSC			0.026 BSC		
L	0.40	0.55	0.70	0.016	0.021	0.028
H_E	4.75	4.90	5.05	0.187	0.193	0.199

SOLDERING FOOTPRINT*



*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

TSSOP8, 4.4x3
CASE 948AL
ISSUE O



TOP VIEW

SYMBOL	MIN	NOM	MAX
A			1.20
A1	0.05		0.15
A2	0.80	0.90	1.05
b	0.19		0.30
c	0.09		0.20
D	2.90	3.00	3.10
E	6.30	6.40	6.50
E1	4.30	4.40	4.50
e	0.65 BSC		
L	1.00 REF		
L1	0.50	0.60	0.75
θ	0°		8°



SIDE VIEW



END VIEW

Notes:

(1) All dimensions are in millimeters. Angles in degrees.
(2) Complies with JEDEC MO-153.

Micro8 is a trademark of International Rectifier.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5817−1050

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative