

Light Bars

Shape	Part Number	Emitting Color	Emitting Material	Lens-Color	Wave Length (nm)	Luminous Intensity 10mA *20mA(mcd) Min. Max.	Viewing Angle	Figure No.
7.5x14mm	EUR22DX	Red	GaAsP/GaP	Red Diffused	625	3 - 18	120°	9
	EMR22DX	Red	GaAlAs	Red Diffused	660	*40 - 100	120°	
	EUG22DX	Green	GaP	Green Diffused	565	3 - 18	120°	
	EMG22DX	Green	GaP	Green Diffused	565	*21 - 31	120°	
	EUY22DX	Yellow	GaAsP/GaP	Yellow Diffused	590	3 - 18	120°	
6.8x19.9mm	EUR30D	Red	GaAsP/GaP	Red Diffused	625	3.5 - 15	120°	10
	EMR30D	Red	GaAlAs	Red Diffused	660	*40 - 100	120°	
	EUG30D	Green	GaP	Green Diffused	565	3.5 - 15	120°	
	EMG30D	Green	GaP	Green Diffused	565	*21 - 31	120°	
	EUY30D	Yellow	GaAsP/GaP	Yellow Diffused	590	3.5 - 15	120°	
15x15mm	EUR29DX	Red	GaAsP/GaP	Red Diffused	625	4.5 - 22	120°	11
	EMR29DX	Red	GaAlAs	Red Diffused	660	*70 - 110	120°	
	EUG29DX	Green	GaP	Green Diffused	565	3 - 15	120°	
	EMG29DX	Green	GaP	Green Diffused	565	*30 - 55	120°	
	EUY29DX	Yellow	GaAsP/GaP	Yellow Diffused	590	3.5 - 22	120°	
3.65x6.15mm	EUR21D	Red	GaAsP/GaP	Red Diffused	625	5 - 20	100°	12
	EMR21D	Red	GaAlAs	Red Diffused	660	*32- 100	100°	
	EUG21D	Green	GaP	Green Diffused	565	2 - 8	100°	
	EMG21D	Green	GaP	Green Diffused	565	*5 - 20	100°	
	EUY21D	Yellow	GaAsP/GaP	Yellow Diffused	590	2 - 8	100°	

