


(2,00mm) .0787"

MMS SERIES



BOX CONTACT SOCKET

SPECIFICATIONS

For complete specifications see www.samtec.com?MMS

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating:

Sn or Au over 50µ" (1,27µm) Ni

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ max

Current Rating:

2A @ 80°C ambient

Insertion Depth:

DH = (2,13mm) .084" to (2,79mm) .110", SH = (2,13mm)

.084" minimum or pass-through

Top Entry DV/SV = (2,13mm)

.084" to (4,32mm) .170"

Bottom Entry DV/SV = (4,27)

.168" minimum (Plus board)

Insertion Force:

(Single contact only)

3.7oz (1,03N) avg.

Withdrawal Force:

(Single contact only)

2.2oz (0,61N) avg.

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,15mm) .006" max



MMS - **1** **NO. PINS PER ROW** - **01** **PLATING OPTION** - **ROW OPTION** - **OTHER OPTION**

Mates with:
TMMH, TMM, MTMM,
MMT, TW, LTMM,
ZLTMM, TCMD

02 thru 40

-L
= 10µ" (0,25µm) Gold contact,
Matte Tin on tail

-T
= Matte Tin

-SV
= Single Vertical

-SH
= Single Horizontal

-DV
= Double Vertical

-DH
= Double Horizontal

-“XX”
= Polarized Position

Row Option	X
-SH & -SV	(0,254) .010
-DH & -DV	(0,559) .022

APPLICATION SPECIFIC OPTIONS

Alignment Pin (-DV only),
Locking clips and Through-hole
pass-through options available.
Call Samtec.

MMS - **1** **NO. PINS PER ROW** - **02** **PLATING OPTION** - **ROW OPTION** - **OTHER OPTION**

02 thru 40

-L
= 10µ" (0,25µm) Gold
contact, Matte Tin
on tail

-T
= Matte Tin

-SV
= Single Vertical

-SH
= Single Horizontal

-DV
= Double Vertical

-DH
= Double Horizontal

-“XX”
= Polarized Position

-K
= (5,50mm) .217" DIA
Polyimide Film
Pick & Place Pad
(-SV & -DV only)
(-SV = 3 pos. min.)
(-DV = 4 pos. min.)

-M
= Metal Pick & Place Pad
(4 positions min.)
(-DV only)

-P
= Plastic Pick & Place Pad
(4 pos. min., -SV only)
(5 pos. min., -DV only)

-TR
= Tape & Reel Packaging

Note: Some lengths, styles
and options are non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292 SAMTEC ISRAEL • Tel: 972-3-7526600
SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-61103766 SAMTEC TAIWAN • Tel: 886-2-2735-6109
SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9512 7747 SAMTEC SOUTH AFRICA • Tel: 27 11 452 8112