


BB-CD-103-02

PLATING: ELECTRO-TIN (.0003 MIN.)

$\frac{.081}{2.06} \text{ MIN.}$

"UL" LISTING #E32244
"CSA" LISTING #18689

WIRE SIZE: 16 - 14 AWG
1.0 - 2.5 MM²




PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	AVAILABLE STUD SIZES
BB-107-	$\frac{.245}{6.22}$	$\frac{.209}{5.31}$	$\frac{.565}{14.35}$	04, 06
BB-124-	$\frac{.295}{7.49}$	$\frac{.211}{5.36}$	$\frac{.564}{14.33}$	04, 06, 08
BB-127-	$\frac{.362}{9.19}$	$\frac{.269}{6.83}$	$\frac{.687}{17.45}$	06, 08, 10


DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		REFERENCE	SCALE: NTS	DATE	TITLE:
FRAC.	DEC.	ANG.	DRWN. BY: <i>h</i>	10-18-84	SPADE TONGUE TERMINAL KRIMPITITE 100-SERIES
±	±	±	CHKD. BY: <i>GT</i>	11-2-84	
			APPRD. BY:		

DWG. NO.	A	CUSTOMER DWG.
----------	---	---------------

	10	9	8	7	6	5	4	3	2	19141
	MATERIAL NUMBER	ALTERNATE NUMBER	STUD SIZE	"S" ±.005/(0.13)	"W" ±.010/(0.25)	"C" MIN (A1)	"L" MAX (A1)	PACKAGING		
F	I91410050	BB-I07-04	4	.119/(3.02)	.245/(6.22)	.209/(5.31)	.565/(14.35)	LOOSE PIECE		
	I91410052	BB-I07-06	6	.146/(3.71)	.245/(6.22)	.209/(5.31)	.565/(14.35)			
	I91410054	BB-I24-04	4	.119/(3.02)	.295/(7.49)	.211/(5.36)	.564/(14.33)			
	I91410056	BB-I24-06	6	.146/(3.71)	.295/(7.49)	.211/(5.36)	.564/(14.33)			
	I91410058	BB-I24-08	8	.173/(4.39)	.295/(7.49)	.211/(5.36)	.564/(14.33)			
	I91410061	BB-I27-06	6	.146/(3.71)	.362/(9.19)	.269/(6.83)	.687/(17.45)			
E	I91410063	BB-I27-08	8	.173/(4.39)	.388/(9.85)	.269/(6.83)	.687/(17.45)	TAPE MOUNTED		
	I91410065	BB-I27-10	10	.198/(5.03)	.388/(9.85)	.269/(6.83)	.687/(17.45)			
	I91410051	BB-I07-04T	4	.119/(3.02)	.245/(6.22)	.209/(5.31)	.565/(14.35)			
	I91410053	BB-I07-06T	6	.146/(3.71)	.245/(6.22)	.209/(5.31)	.565/(14.35)			
	I91410055	BB-I24-04T	4	.119/(3.02)	.295/(7.49)	.211/(5.36)	.564/(14.33)			
	I91410057	BB-I24-06T	6	.146/(3.71)	.295/(7.49)	.211/(5.36)	.564/(14.33)			
D	I91410059	BB-I24-08T	8	.173/(4.39)	.295/(7.49)	.211/(5.36)	.564/(14.33)			
	I91410062	BB-I27-06T	6	.146/(3.71)	.362/(9.19)	.269/(6.83)	.687/(17.45)			
	I91410064	BB-I27-08T	8	.173/(4.39)	.388/(9.85)	.269/(6.83)	.687/(17.45)			
	I91410066	BB-I27-10T	10	.198/(5.03)	.388/(9.85)	.269/(6.83)	.687/(17.45)			



PARTS ON TAPE



CUSTOMER DRAWING

NOTES:
1. MATERIAL: COPPER .031/(.79) THICK.
2. PLATING: ELECTRO-TIN.
3. PARTS ARE ROHS COMPLIANT. (A1)

ADD MISSING TOLRNC				QUALITY SYMBOLS				GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE				SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION			
EC NO: WNA2010-0362				2009/12/21				DRAWN BY				DATE				TITLE		SPADE TONGUE TERMINAL					
DRWNET:THRODAHL				2009/12/21				HEB				1999/11/12						16-14 AWG					
CHKD:JMACNEIL				2009/12/21				CHECKED BY				DATE						KRIMPTITE SERIES					
APPR:JMACNEIL				2009/12/21				RWD				1999/11/12						MOLEX INCORPORATED					
								APPROVED BY				DATE				MOLEX							
								RWD				1999/11/12											
								MATERIAL NO.				DOCUMENT NO.						SHEET NO.					
								SEE CHART				SD-19141-001						1 OF 1					
								SIZE				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
A1				REV				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS															