


Product Catalog

For Web Assistance: (800) 323-0198



Company Profile
and History



Product
Quote Form



Find a
Distributor



Contact Us

Product Index



Hookup Wire

Braided Stranded Copper Wire

Multiconductor

Tubing

Coaxial Cable

Check the Items You'd Like to Add to Your Quote or Order

Braidless Silicone Wire

HIGH-VOLTAGE HIGH-TEMPERATURE ELECTRONIC WIRE

*ABRASION RESISTANT SILICONE UL STYLE 3239

| Standard Putups: • 100ft. • 500ft. • 1000ft. • bulk. | DESCRIPTION | | | | FEATURES & APPLICATIONS | | | |
|---|---|-----|-----------|----------------------------|--|---------------|------------|----------|
| | <ul style="list-style-type: none"> Conductors: Fully annealed tinned copper per ASTM B-33. Also available - nickel plated or pure nickel conductor. Insulation: Specially formulated abrasion resistant extruded silicone rubber. | | | | <ul style="list-style-type: none"> Superior chemical resistance. *Corona radiation and ozone resistant. *Recommended for stoves, heaters, furnaces, dryers, motors, therapeutic devices, signs, lighting fixtures, power supplies, radar installations, Xenon flash tubes, and special electronic devices where high temperatures are incurred. | | | |
| See color chart 8 in Technical Section. Consult factory for availability of other colors. | CHARACTERISTICS | | | | APPROVALS | | | |
| | <ul style="list-style-type: none"> Temperature: 150C. Voltage Rating: Excellent dielectric strength. See chart below. | | | | <ul style="list-style-type: none"> Recognized under the components program of Underwriters' Laboratories, Inc. UL Style 3239 (see chart below for UL recognized items), 150C. | | | |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 392240 | 22 | 7/30 | .030 | .040 | .114 | 10KV | 3239 |
| <input type="checkbox"/> | 392245 | 22 | 7/30 | .030 | .045 | .124 | 15KV | 3239 |
| <input type="checkbox"/> | 392250 | 22 | 7/30 | .030 | .050 | .134 | 20KV | 3239 |
| <input type="checkbox"/> | 392262 | 22 | 7/30 | .030 | .062 | .158 | 25KV | 3239 |
| <input type="checkbox"/> | 392275 | 22 | 7/30 | .030 | .075 | .185 | 30KV | 3239 |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 392297 | 22 | 7/30 | .030 | .097 | .230 | 40KV | 3239 |
| <input type="checkbox"/> | 392299 | 22 | 7/30 | .030 | .150 | .330 | 50KV | None |
| <input type="checkbox"/> | 392040 | 20 | 10/30 | .038 | .040 | .120 | 10KV | 3239 |
| <input type="checkbox"/> | 392045 | 20 | 10/30 | .038 | .045 | .131 | 15KV | 3239 |
| <input type="checkbox"/> | 392050 | 20 | 10/30 | .038 | .050 | .140 | 20KV | 3239 |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 392062 | 20 | 10/30 | .038 | .062 | .165 | 25KV | 3239 |
| <input type="checkbox"/> | 392075 | 20 | 10/30 | .038 | .075 | .191 | 30KV | 3239 |
| <input type="checkbox"/> | 392097 | 20 | 10/30 | .038 | .097 | .235 | 40KV | 3239 |
| <input type="checkbox"/> | 392099 | 20 | 10/30 | .038 | .150 | .338 | 50KV | None |
| <input type="checkbox"/> | 391840 | 18 | 16/30 | .047 | .040 | .131 | 10KV | 3239 |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 391845 | 18 | 16/30 | .047 | .045 | .140 | 15KV | 3239 |
| <input type="checkbox"/> | 391850 | 18 | 16/30 | .047 | .050 | .146 | 20KV | 3239 |
| <input type="checkbox"/> | 391862 | 18 | 16/30 | .047 | .062 | .175 | 25KV | 3239 |
| <input type="checkbox"/> | 391875 | 18 | 16/30 | .047 | .075 | .200 | 30KV | 3239 |
| <input type="checkbox"/> | 391897 | 18 | 16/30 | .047 | .097 | .245 | 40KV | 3239 |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 391899 | 18 | 16/30 | .047 | .150 | .350 | 50KV | None |
| <input type="checkbox"/> | 391640 | 16 | 26/30 | .058 | .040 | .141 | 10KV | 3239 |
| <input type="checkbox"/> | 391645 | 16 | 26/30 | .058 | .045 | .150 | 15KV | 3239 |

| | | | | | | | | |
|--------------------------|--------------------|------------|------------------|-----------------------------------|--------------------------------------|----------------------|-------------------|-----------------|
| <input type="checkbox"/> | 391650 | 16 | 26/30 | .058 | .050 | .161 | 20KV | 3239 |
| <input type="checkbox"/> | 391662 | 16 | 26/30 | .058 | .062 | .185 | 25KV | 3239 |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 391675 | 16 | 26/30 | .058 | .075 | .212 | 30KV | 3239 |
| <input type="checkbox"/> | 391697 | 16 | 26/30 | .058 | .097 | .255 | 40KV | 3239 |
| <input type="checkbox"/> | 391699 | 16 | 26/30 | .058 | .150 | .376 | 50KV | None |
| <input type="checkbox"/> | 391440 | 14 | 41/30 | .074 | .040 | .155 | 10KV | 3239 |
| <input type="checkbox"/> | 391445 | 14 | 41/30 | .074 | .045 | .165 | 15KV | 3239 |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 391450 | 14 | 41/30 | .074 | .050 | .175 | 20KV | 3239 |
| <input type="checkbox"/> | 391462 | 14 | 41/30 | .074 | .062 | .204 | 25KV | 3239 |
| <input type="checkbox"/> | 391475 | 14 | 41/30 | .074 | .075 | .225 | 30KV | 3239 |
| <input type="checkbox"/> | 391497 | 14 | 41/30 | .074 | .097 | .272 | 40KV | 3239 |
| <input type="checkbox"/> | 391499 | 14 | 41/30 | .074 | .150 | .380 | 50KV | None |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 391240 | 12 | 65/30 | .092 | .040 | .170 | 10KV | 3239 |
| <input type="checkbox"/> | 391245 | 12 | 65/30 | .092 | .045 | .184 | 15KV | 3239 |
| <input type="checkbox"/> | 391250 | 12 | 65/30 | .092 | .050 | .196 | 20KV | 3239 |
| <input type="checkbox"/> | 391262 | 12 | 65/30 | .092 | .062 | .218 | 25KV | 3239 |
| <input type="checkbox"/> | 391275 | 12 | 65/30 | .092 | .075 | .246 | 30KV | 3239 |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 391297 | 12 | 65/30 | .092 | .097 | .289 | 40KV | 3239 |
| <input type="checkbox"/> | 391299 | 12 | 65/30 | .092 | .150 | .396 | 50KV | None |
| <input type="checkbox"/> | 391040 | 10 | 105/30 | .112 | .040 | .200 | 10KV | 3239 |
| <input type="checkbox"/> | 391045 | 10 | 105/30 | .112 | .045 | .206 | 15KV | 3239 |
| <input type="checkbox"/> | 391050 | 10 | 105/30 | .112 | .050 | .220 | 20KV | 3239 |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 391062 | 10 | 105/30 | .112 | .062 | .244 | 25KV | 3239 |
| <input type="checkbox"/> | 391075 | 10 | 105/30 | .112 | .075 | .270 | 30KV | 3239 |
| <input type="checkbox"/> | 391097 | 10 | 105/30 | .112 | .097 | .312 | 40KV | 3239 |
| <input type="checkbox"/> | 391099 | 10 | 105/30 | .112 | .150 | .420 | 50KV | None |
| <input type="checkbox"/> | 390845 | 8 | 133/29 | .166 | .045 | .256 | 15KV | None |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 390862 | 8 | 133/29 | .166 | .062 | .290 | 25KV | None |
| <input type="checkbox"/> | 390897 | 8 | 133/29 | .166 | .097 | .360 | 40KV | None |
| <input type="checkbox"/> | 390645 | 6 | 133/27 | .210 | .045 | .300 | 15KV | None |
| <input type="checkbox"/> | 390662 | 6 | 133/27 | .210 | .062 | .340 | 25KV | None |
| <input type="checkbox"/> | 390462 | 4 | 133/25 | .268 | .062 | .392 | 25KV | None |
| | Part Number | AWG | Stranding | Nom. Dia. of Conductor in. | Nom. Insulation Thickness in. | Nom. O.D. in. | DC Voltage | UL Style |
| <input type="checkbox"/> | 390262 | 2 | 259/26 | .336 | .062 | .460 | 25KV | None |

50KV ratings are theoretical. 200C constructions available upon request. Standard color: White.

If you wish to add the products to your quote or complete your quote check one of these buttons

[Add Items and Continue](#)

[Add Items and Generate Quote](#)

[Generate Quote](#)

[Home](#) | [Profile](#) | [Catalog](#) | [Quote Form](#) | [Representatives](#) | [Contact](#)
 Copyright 1997-2001, Dearborn Wire and Cable, Inc.