

Low Noise Amplifier 1.575 GHz

Rev. V1

Features

- Low Noise Figure: 1.15 dB
- High Gain: 27 dB
- Low Power Consumption: 5V, 20 mA
- High Dynamic Range
- Lead-Free SOIC-8 Package
- 100% Matte Tin Plating over Copper
- Halogen-Free "Green" Mold Compound
- 260°C Reflow Compatible
- RoHS* Compliant Version of AM50-0002

Description

M/A-COM's MAALSS0042 is a high performance GaAs MMIC low noise amplifier in a lead-free SOIC 8-lead surface mount plastic package. The MAALSS0042 employs a monolithic 3-stage self-bias design and a simple external matching network to obtain minimum noise figure.

The MAALSS0042 is ideally suited for use where low noise figure, high gain, high dynamic range and low power consumption are required. Typical applications include receiver front ends in the Global Positioning System (GPS) market, as well as standard gain blocks, buffer amps, driver amps, and IF amps in both fixed and portable systems.


M/A-COM'S MAALSS0042 is fabricated using a mature 0.5-micron gate length GaAs process. The process features full passivation for increased performance reliability.

Ordering Information ^{1,2}

Part Number	Package
MAALSS0042	Bulk Packaging
MAALSS0042TR-3000	3000 piece reel
MAALSS0042SMB	Sample Test Board

1. Reference Application Note M513 for reel size information.
2. Die quantity varies.

Functional Diagram



Pin Configuration ^{3,4,5}

Pin No.	Pin Name	Description
1	GND	Ground
2	RF IN	RF Input
3	GND	Ground
4	GND	Ground
5	GND	Ground
6	RF OUT	RF Output, V _{DD}
7	GND	Ground
8	GND	Ground

3. Pins 1, 3, 4, 5, 7, and 8 must be RF and DC grounded (see Recommended PCB Configuration).
4. Pin 2 is the RF input and must be connected to the simple matching network shown in the Application Schematic.
5. Pin 6 is the RF output. V_{DD} is also applied on Pin 6.

Absolute Maximum Ratings ^{6,7}

Parameter	Absolute Maximum
V _{DD}	+10 VDC
Input Power	17 dBm
Channel Temperature ⁸	+150 °C
Operating Temperature	-40 °C to +85 °C
Storage Temperature	-65 °C to +150 °C

6. Exceeding any one or combination of these limits may cause permanent damage to this device.
7. M/A-COM does not recommend sustained operation near these survivability limits.
8. Typical thermal resistance (θ_{JC}) = +165 °C/W

* Restrictions on Hazardous Substances, European Union Directive 2002/95/EC.

Rev. V1

Parameter	Test Conditions	Units	Min.	Typ.	Max.
Gain	F = 1.575 GHz, P _{IN} = -35 dBm	dB	25	27	29
Noise Figure	F = 1.575 GHz, P _{IN} = -35 dBm	dB	-	1.15	1.4
Input VSWR	F = 1.575 GHz, P _{IN} = -35 dBm	Ratio	-	2.0:1	-
Output VSWR	F = 1.575 GHz, P _{IN} = -35 dBm	Ratio	-	1.5:1	-
Output P1dB	F = 1.575 GHz	dBm	-	1	-
Input IP ₃	F = 1.575 GHz, P _{IN} = -35 dBm	dBm	-	-14	-
Reverse Isolation	F = 1.575 GHz, P _{IN} = -35 dBm	dB	-	48	-
Bias Current	—	mA	15	20	25

FR-4 circuit board, thickness = 0.016 inches (0.41)
 Dimensions in inches (mm).

	Frequency = 1.575 GHz	
	Impedance	Electrical Length
T1	57.2 Ω	36.0°
T2	82.7 Ω	16.2°

Figure 1: Dimensions of the MACOM M538-012-AA package. The figure includes three views: a top view, a side view, and a bottom view. The top view shows a rectangular package with 8 pins on each long side. Dimensions include: overall length 1.990/1.968 (50.03/50.00), overall width 0.075/0.098 (1.91/2.51), pin pitch 0.050 (1.27), and pin width 0.013/0.020 (0.33/0.51). The side view shows a height of 0.197/0.1574 (5.00/4.00). The bottom view shows a footprint with a central area of 0.532/0.688 (1.35/1.75) and a central pad diameter of 0.050 (1.27).

2


M/A-COM Technology Solutions Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Low Noise Amplifier 1.575 GHz


Rev. V1

Typical Performance


Gain, $T_A = +25^\circ\text{C}$




Gain over Temperature




Noise Figure, $T_A = +25^\circ\text{C}$




Noise Figure over Temperature



Input IP_3 , $T_A = +25^\circ\text{C}$



VSWR, $T_A = +25^\circ\text{C}$



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[M/A-COM Technology Solutions:](#)

[MAALSS0042TR-3000](#)