

PAR6-59-PXB/B

1.8 m | 6 ft Parabolic Unshielded Antenna for Relocation-Category A, single-polarized, 5.725-5.850GHz and 5.925-6.425 GHz, CPR137G, gray antenna, molded gray radome with flash, non-standard pack—one-piece reflector

POWERED BY



General Specifications

Antenna Type	PAR - Parabolic Unshielded Antenna for Relocation-Category A, single-polarized
Diameter, nominal	1.8 m 6 ft
Packing	Non-standard pack
Radome Color	Gray
Radome Material	Molded
Reflector Construction	One-piece reflector
Antenna Input	CPR137G
Antenna Color	Gray
Antenna Type	PAR - Parabolic Unshielded Antenna for Relocation-Category A, single-polarized
Diameter, nominal	1.8 m 6 ft
Flash Included	Yes
Polarization	Single

Electrical Specifications

Operating Frequency Band	5.925 – 6.425 GHz
Beamwidth, Horizontal	2.0 °
Beamwidth, Vertical	2.0 °
Cross Polarization Discrimination (XPD)	30 dB
Front-to-Back Ratio	55 dB
Gain, Low Band	37.7 dBi
Gain, Mid Band	37.8 dBi
Gain, Top Band	37.9 dBi
Operating Frequency Band	5.725 – 5.850 GHz
Radiation Pattern Envelope Reference (RPE)	4327A
Return Loss	19.1 dB
VSWR	1.25

Electrical Specifications (Band 2)

Beamwidth, Horizontal	1.9 °
Beamwidth, Vertical	1.9 °
Cross Polarization Discrimination (XPD)	30 dB
Electrical Compliance	ETSI Class 1 US FCC Part 101A
Front-to-Back Ratio	55 dB

Product Specifications

COMMSCOPE®

PAR6-59-PXB/B

POWERED BY



Gain, Low Band	38.0 dBi
Gain, Mid Band	38.2 dBi
Gain, Top Band	38.4 dBi
Operating Frequency Band	5.925 – 6.425 GHz
Radiation Pattern Envelope Reference (RPE)	2472A
Return Loss	30.7 dB
VSWR	1.06

Mechanical Specifications

Fine Azimuth Adjustment	±15°
Fine Elevation Adjustment	±20°
Mounting Pipe Diameter	115 mm 4.5 in
Net Weight	70 kg 154 lb
Side Struts, Included	1 inboard
Side Struts, Optional	1 inboard
Wind Velocity Operational	110 km/h 68 mph
Wind Velocity Survival Rating	200 km/h 124 mph

Wind Forces At Wind Velocity Survival Rating

Angle a for MT Max	-130 °
Axial Force (FA)	8779 N 1974 lbf
Side Force (FS)	1946 N 437 lbf
Twisting Moment (MT)	3826 N•m
Weight with 1/2 in (12 mm) Radial Ice	122 kg 269 lb
Zcg with 1/2 in (12 mm) Radial Ice	347 mm 14 in
Zcg without Ice	278 mm 11 in

Product Specifications


COMMSCOPE®

PAR6-59-PXB/B

POWERED BY

 ANDREW®

Wind Forces At Wind Velocity Survival Rating Image



Packed Dimensions

Gross Weight, Packed Antenna

142.0 kg | 313.1 lb

Note

Non-standard packing option—contact 1-800-255-1479 (North America), 1-800-873-2307 (International), or an Andrew representative

Product Specifications


COMMSCOPE®

PAR6-59-PXB/B

POWERED BY

ANDREW®

Antenna Dimensions And Mounting Information



Dimensions in Inches (mm)					
Antenna Size, ft (m)	A	B	C	D	E
6 (1.8)	76.3 (1939)	17.1 (435)	17.9 (455)	19.3 (490)	14.3 (362)

Regulatory Compliance/Certifications

Agency ISO 9001:2008 **Classification** Designed, manufactured and/or distributed under this quality management system

* Footnotes

Axial Force (FA)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Cross Polarization Discrimination (XPD)

The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.

Front-to-Back Ratio

Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.

Gain, Mid Band

For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.

Product Specifications

COMMSCOPE®

PAR6-59-PXB/B

Operating Frequency Band

Packing

Radiation Pattern Envelope Reference (RPE)

Return Loss

Side Force (FS)

Twisting Moment (MT)

VSWR

Wind Velocity Operational

Wind Velocity Survival Rating

Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.

Andrew standard packing is suitable for export. Antennas are shipped as standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.

Radiation patterns determine an antenna's ability to discriminate against unwanted signals under conditions of radio congestion. Radiation patterns are dependent on antenna series, size, and frequency.

The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.

Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.

The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of 0.3 x the 3 dB beam width of the antenna.

The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.

POWERED BY

