

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1040460417

Status:


Active

Overview:

IllumiMate™ Connector System

Description:

IllumiMate 2.00mm Pitch Wire-to-Board Header, Surface Mount, Single Row, Right Angle, 4 Circuits



Documents:

3D Model

Drawing (PDF)

Product Specification PS-104046-001-001 (PDF)

Packaging Specification PK-104046-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	104046
Application	Signal, Wire-to-Board
Comments	for LED module
Overview	IllumiMate™ Connector System
Product Name	IllumiMate
UPC	884982033139
Physical	
Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	4.05mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.191/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-25°C to +130°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	250V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-104046-001-001
Product Specification	PS-104046-001-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

104046 Series

Mates With

104047 Crimp Housing, 104466 Crimp Terminal

This document was generated on 12/07/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION