





3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS





NOTES:


1. MATERIALS:
- | | | |
|--------------|---------------|---------------|
| SPRINGS | SS | PLATING : Au |
| CONTACTS | Be Cu | COLOR : BLACK |
| IC GUIDES | PES | COLOR : BLACK |
| PRESSURE PAD | PES | COLOR : BLACK |
| COVER | PPS or equiv. | COLOR : BLACK |
| BASE | PES | COLOR : BLACK |
2. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "RoHS COMPLIANCE" SECTION WWW.3MCONNECTOR.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY).
3. FOR PRODUCT SPECIFICATIONS AND WARRANTY INFORMATION SEE: WWW.3MCONNECTOR.COM PN 248-4205-01

DESIGN REFERENCE				NEXT ASSEMBLY				A		37213		INITIAL RELEASE				ARM					
DISTRIBUTION CODES								REV		ECO		ISSUE DATE AND DESCRIPTION				DRFT		CHKD			
								DRFT		DATE				MFG				DATE			
								CHKD		DATE				APPVL				DATE			
DIVISION				DIVISION CODE						3M Center St. Paul, MN 55144		© 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.									
DO NOT SCALE DRAWING				SCALE 5 1														TOLERANCES EXCEPT AS NOTED			
				INCHES .0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002																	
								MILLIMETERS 0 ± 0 ± .00 ± .00 ± 000 ±													
THIRD ANGLE PROJECTION								TITLE		QFN TEST SOCKET, 0.4mm, 48 pos, EVEN ROW, 6X6 PKG, WITH TP											
INTERPRET PER ASME Y14.5 - 1994																					
MAX SURFACE ROUGHNESS								CAGE NUMBER		SIZE		DRAWING NO.				REV.					
125 ✓ ☐ ALL SURFACES ☒ MARKED ONLY								C		C		78-5100-2451-2				A					
				ANGLES ± 1°				MODEL		TEXTTOOL - QFN				DET. LISTS		☐ YES ☒ NO		SHT 1 OF 2			

3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS



RECOMMENDED IC (REF.)

DESIGN REFERENCE				NEXT ASSEMBLY				REV	ECO	ISSUE DATE AND DESCRIPTION				DRFT	CHKD
DISTRIBUTION CODES								DRFT		DATE		MFG		DATE	
								CHKD		DATE		APPVL		DATE	
DIVISION				DIVISION CODE				3M 3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.							
DO NOT SCALE DRAWING		SCALE 5 1		TOLERANCES EXCEPT AS NOTED											
				INCHES				TITLE QFN TEST SOCKET, 0.4mm, 48 pos, EVEN ROW, 6X6 PKG, WITH TP							
				.0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002											
THIRD ANGLE PROJECTION INTERPRET PER ASME Y14.5 - 1994				MILLIMETERS				CAGE NUMBER C DRAWING NO. 78-5100-2451-2 REV. A							
MAX SURFACE ROUGHNESS 125 ✓ ☐ ALL SURFACES ☒ MARKED ONLY				0 ± .1 .0 ± .02 .00 ± .005 .000 ± .0002											
				ANGLES ± 1°				MODEL TEXTTOOL - QFN		DET. LISTS ☐ YES ☒ NO		SHT 2 OF 2			