





### Features


- Universal AC input / Full range
- Withstand 300VAC surge input for 5 second
- No load power consumption<0.2W</li>
- · Miniature size and 1U low profile
- High operating temperature up to 70°C
- · Protections: Short circuit / Overload / Over voltage
- Cooling by free air convection
- · Compliance to IEC/EN 60335-1(PD3) and IEC/EN61558-1, -2-16 for household appliances
- Operating altitude up to 5000 meters (Note.8)
- · Withstand 5G vibration test
- · High efficiency, long life and high reliability
- LED indicator for power on
- Over voltage category III
- · 100% full load burn-in test
- 3 years warranty

# Description

### LRS-35 series is a 35W single-output enclosed type power supply with 30mm of low profile design. Adopting the full range 85~264VAC input, the entire series provides an output voltage line of 5V, 12V, 15V, 24V, 36V and 48V.

In addition to the high efficiency up to 89%, the design of metallic mesh case enhances the heat dissipation of LRS-35 that the whole series operates from -30 $^{\circ}$ C through 70 $^{\circ}$ C under air convection without a fan. Delivering an extremely low no load power consumption (less than 0.2W), it allows the end system to easily meet the worldwide energy requirement. LRS-35 has the complete protection functions and 5G antivibration capability; it is complied with the international safety regulations such as TUV EN60950-1, EN60335-1,EN61558-1/-2-16, UL60950-1 and GB4943. LRS-35 series serves as a high price-toperformance power supply solution for various industrial applications.

## Model Encoding



### Applications

- · Industrial automation machinery
- Industrial control system
- Mechanical and electrical equipment
- · Electronic instruments, equipments or apparatus
- Household appliances




#### **SPECIFICATION**

| MODEL                       |                              | LRS-35-5   | LRS-35-12    | LRS-35-15      | LRS-35-24    | LRS-35-36    | LRS-35-48    |  |  |
|-----------------------------|------------------------------|--|--------------|----------------|--------------|--------------|--------------|--|--|
| OUTPUT                      | DC VOLTAGE                   | 5V   | 12V          | 15V            | 24V          | 36V          | 48V          |  |  |
|                             | RATED CURRENT                | 7A   | 3A           | 2.4A           | 1.5A         | 1A           | 0.8A         |  |  |
|                             | CURRENT RANGE                | 0 ~ 7A   | 0 ~ 3A       | 0 ~ 2.4A       | 0 ~ 1.5A     | 0 ~ 1A       | 0 ~ 0.8A     |  |  |
|                             | RATED POWER                  | 35W  | 36W          | 36W            | 36W          | 36W          | 38.4W        |  |  |
|                             | RIPPLE & NOISE (max.) Note.2 | 80mVp-p  | 120mVp-p     | 120mVp-p       | 150mVp-p     | 200mVp-p     | 200mVp-p     |  |  |
|                             | VOLTAGE ADJ. RANGE           | 4.5 ~ 5.5V   | 10.2 ~ 13.8V | 13.5 ~ 18V     | 21.6 ~ 28.8V | 32.4 ~ 39.6V | 43.2 ~ 52.8V |  |  |
|                             | VOLTAGE TOLERANCE Note.3     | ±2.0%  | ±1.0%        | ±1.0%          | ±1.0%        | ±1.0%        | ±1.0%        |  |  |
|                             | LINE REGULATION Note.4       | ±0.5%  | ±0.5%        | ±0.5%          | 土0.5%        | ±0.5%        | ±0.5%        |  |  |
|                             | LOAD REGULATION Note.5       | ±1.0%  | ±0.5%        | ±0.5%          | ±0.5%        | ±0.5%        | ±0.5%        |  |  |
|                             | SETUP, RISE TIME             | 1000ms, 30ms/230VAC 2000ms,30ms/115VAC at full load  |              |                |              |              |              |  |  |
|                             | HOLD UP TIME (Typ.)          | 30ms/230VAC 12ms/115VAC at full load   |              |                |              |              |              |  |  |
| INPUT                       | VOLTAGE RANGE                | 85 ~ 264VAC 120 ~ 373VDC   |              |                |              |              |              |  |  |
|                             | FREQUENCY RANGE              | 47 ~ 63Hz  |              |                |              |              |              |  |  |
|                             | EFFICIENCY (Typ.)            | 82%  | 86%          | 86%            | 88%          | 88%          | 89%          |  |  |
|                             | AC CURRENT (Typ.)            | 0.7A/115VAC 0.42A/230VAC   |              |                |              |              |              |  |  |
|                             | INRUSH CURRENT (Typ.)        | COLD START 45A/230VAC  |              |                |              |              |              |  |  |
|                             | LEAKAGE CURRENT              | <0.75mA/240VAC   |              |                |              |              |              |  |  |
| PROTECTION                  |                              | 110 ~ 150% rated output power  |              |                |              |              |              |  |  |
|                             | OVER LOAD                    | Protection type: Hiccup mode, recovers automatically after fault condition is removed  |              |                |              |              |              |  |  |
|                             |                              | 5.75 ~ 6.9V  | 13.8 ~ 16.2V | 18.75 ~ 21.75V | 28.8 ~ 33.6V | 41.4 ~ 48.6V | 55.2 ~ 64.8V |  |  |
|                             | OVER VOLTAGE                 | Protection type : Shut down o/p voltage, re-power on to recover  |              |                |              |              |              |  |  |
| ENVIRONMENT                 | WORKING TEMP.                | -30 ~ +70°C (Refer to "Derating Curve")  |              |                |              |              |              |  |  |
|                             | WORKING HUMIDITY             | 20 ~ 90% RH non-condensing   |              |                |              |              |              |  |  |
|                             | STORAGE TEMP., HUMIDITY      | $-40 \sim +85$ °C , $10 \sim 95\%$ RH non-condensing   |              |                |              |              |              |  |  |
|                             | TEMP. COEFFICIENT            | ±0.03%/°C (0~50°C)   |              |                |              |              |              |  |  |
|                             | VIBRATION                    | 10 ~ 500Hz, 5G 10min./1cycle, 60min. each along X, Y, Z axes   |              |                |              |              |              |  |  |
|                             | OVER VOLTAGE CATEGORY        | III; According to EN61558, EN50178, EN60664-1, EN62477-1; altitude up to 2000 meters   |              |                |              |              |              |  |  |
| SAFETY &<br>EMC<br>(Note 9) | SAFETY STANDARDS             | UL60950-1, TUV EN60950-1, EN60335-1, EN61558-1/-2-16, CCC GB4943.1, BSMI CNS14336-1, EAC TP TC 004, AS/NZS 60950.1(by CB) approved |              |                |              |              |              |  |  |
|                             | WITHSTAND VOLTAGE            | I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.25KVAC   |              |                |              |              |              |  |  |
|                             | ISOLATION RESISTANCE         | I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C/ 70% RH  |              |                |              |              |              |  |  |
|                             | EMC EMISSION                 | Compliance to EN55032 (CISPR32) Class B, EN55014, EN61000-3-2,-3, GB/T 9254, BSMI CNS13438, EAC TP TC 020                          |              |                |              |              |              |  |  |
|                             | EMC IMMUNITY                 | Compliance to EN61000-4-2,3,4,5,6,8,11, EN61000-6-2 (EN50082-2), heavy industry level, criteria A, EAC TP TC 020                   |              |                |              |              |              |  |  |
| OTHERS                      | MTBF                         | 763.6K hrs min. MIL-HDBK-217F (25°C)   |              |                |              |              |              |  |  |
|                             | DIMENSION                    | 99*82*30mm (L*W*H)   |              |                |              |              |              |  |  |
|                             | PACKING                      | 0.23Kg; 60pcs/14.8Kg/0.88CUFT  |              |                |              |              |              |  |  |
| NOTE                        |                              |  |              |                |              |              |              |  |  |

### NOTE

- 1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25  $^{\circ}\text{C}$  of ambient temperature.
- 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor.
- 3. Tolerance: includes set up tolerance, line regulation and load regulation.
- 4. Line regulation is measured from low line to high line at rated load.
- 5. Load regulation is measured from 0% to 100% rated load.
- 6. Length of set up time is measured at cold first start. Turning ON/OFF the power supply very quickly may lead to increase of the set up time.
- 7. 5V when the load factor 0~50%, the switching power less is reduced by burst operation, which will cause ripple and ripple noise to go beyond the specifications.
- 8. The ambient temperature derating of 5°C/1000m is needed for operating altitude greater than 2000m(6500ft).
- 9. The power supply is considered a component which will be installed into a final equipment. All the EMC tests are been executed by mounting the unit on a 360mm\*360mm metal plate with 1mm of thickness. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com)









### ■ Mechanical Specification

Case No.239A Unit:mm





### Terminal Pin No. Assignment

| Pin No. | Assignment | Pin No. | Assignment   |
|---------|------------|---------|--------------|
| 1       | AC/L       | 4       | DC OUTPUT -V |
| 2       | AC/N       | 5       | DC OUTPUT +V |
| 3       | FG ≟       |         |              |

### **■** Installation Manual

Please refer to : http://www.meanwell.com/manual.html