


ITEM	DESCRIPTION
1	SCREW
2	COVER ASSEMBLY
3	INSERT ASSEMBLY
4	GASKET


C12207N22**

SERIES _____
C12= INTERNAL THREAD FORM B INDUSTRIAL
POLES _____
2= 2 POLE
THREAD SIZE _____
07= PG7, 09= PG9, M2=M12x1.5, M6=M16x1.5, M0= M20x1.5, 13= 1/2" NPTF
MATERIAL AND HOUSING COLOUR _____
G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK V0, T= TRANSPARENT
GROUND POSITION _____
0= UNMOUNTED, 2= H12, 6= H6

SCREW AND GASKET

- 1= NBR PROFILE GASKET & SCREW
- 2= NBR FLAT GASKET & SCREW
- 3= WHITE SILICONE PROFILE GASKET & SCREW
- 4= WHITE SILICONE FLAT GASKET & SCREW
- 5= NBR PROFILE GASKET, NO SCREW
- 6= NBR FLAT GASKET, NO SCREW
- A= NBR PROFILE GASKET & SCREW +2mm
- G= NO GASKET, STANDARD SCREW
- P= INTEGRATED NBR GASKET & IP67 SCREW ASSEMBLED

NON STANDARD COMPONENTS
AF= WITH SCREW MOUNTED
BS= FULLY UNMOUNTED
P7= IP67 COMPLIANT
2J= M3x31 INOX FIXING SCREW
14= PACKED IN NEUTRAL BAG
SA= SINGLE BAGGED
SA= UL LISTED



1. PLEASE SEE SHEET 2 FOR CURRENTLY CONFIGURED PART NUMBERS.
FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT
THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED.
2. EARTH POSITION SHOWN: H12
3. PRODUCT SPEC: SEE PS-121201-001, WITH EXCEPTION.
4. FOR PACKAGING SEE PACKAGING SPEC PK-121023-C12.
5. PART NO 1210230107 SHOWN FOR ILLUSTRATION PURPOSES ONLY

LAST INSPECTION NUMBER 2

UPDATED NOTE 3 EC NO: IPG2015-1871 TDWMB/CAFFEY 2015/04/27 CHKD: APPR:STR/GFFIN 2015/05/13	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
		 =0			DRAWN BY DSHEA	DATE 2011/05/19	TITLE C12 SERIES INTERNAL THREAD	MOLEX MOLEX INCORPORATED	SHEET NO. 1 OF 2	
		 =0	4 PLACES	± ---	± ---	CHECKED BY DMAHER				DATE 2011/05/27
			3 PLACES	± ---	± ---	APPROVED BY				DATE
			2 PLACES	± 0.10	± ---	EFOLAN				2011/06/08
			1 PLACE	± 0.2	± ---	MATERIAL NO.				
		ANGULAR ± ---°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 2		SD-121023-006		
						SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

SEE SHEET 1 EC NO: IPG2015-1871 DRAWN: B. CAFFEY 2015/04/27 CHKD: 2015/05/13 APPR: S. GRIFFIN 2015/05/13	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																							
				<table><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± 0.10</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± 0.2</td><td>± ---</td></tr></table>	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.10	± ---	1 PLACE	± 0.2	± ---	<table><tr><td>DRAWN BY</td><td>DATE</td></tr><tr><td>DSHEA</td><td>2011/05/19</td></tr><tr><td>CHECKED BY</td><td>DATE</td></tr><tr><td>DMAHER</td><td>2011/05/27</td></tr><tr><td>APPROVED BY</td><td>DATE</td></tr><tr><td>EFOLAN</td><td>2011/06/08</td></tr></table>	DRAWN BY	DATE	DSHEA	2011/05/19	CHECKED BY	DATE	DMAHER	2011/05/27	APPROVED BY	DATE	EFOLAN	2011/06/08	TITLE C12 SERIES INTERNAL THREAD		
		4 PLACES	± ---	± ---																												
		3 PLACES	± ---	± ---																												
		2 PLACES	± 0.10	± ---																												
1 PLACE	± 0.2	± ---																														
DRAWN BY	DATE																															
DSHEA	2011/05/19																															
CHECKED BY	DATE																															
DMAHER	2011/05/27																															
APPROVED BY	DATE																															
EFOLAN	2011/06/08																															
ANGULAR ± ---°		MOLEX INCORPORATED																														
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-121023-006		SHEET NO. 2 OF 2																										
		SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																												