



1.2 m | 4 ft High Performance, Super High XPD Parabolic Shielded Antenna, dual-polarized, 10.700–11.700 GHz, CPR90G, gray antenna, enhanced white radome with flash, standard pack—one-piece reflector

Product Classification

| | |
|---------------------|-------------------|
| Product Type | Microwave antenna |
|---------------------|-------------------|

General Specifications

| | |
|-------------------------------|-----------------------------------------------------------------------------------|
| Antenna Type | HSX - High Performance, Super High XPD Parabolic Shielded Antenna, dual-polarized |
| Diameter, nominal | 1.2 m 4 ft |
| Packing | Standard pack |
| Radome Color | White |
| Radome Material | Enhanced |
| Reflector Construction | One-piece reflector |
| Antenna Input | CPR90G |
| Antenna Color | Gray |
| Antenna Type | HSX - High Performance, Super High XPD Parabolic Shielded Antenna, dual-polarized |
| Diameter, nominal | 1.2 m 4 ft |
| Flash Included | Yes |
| Polarization | Dual |

Electrical Specifications

| | |
|---------------------------------------------------------|---------------------------------|
| Operating Frequency Band | 10.700 – 11.700 GHz |
| Beamwidth, Horizontal | 1.6 ° |
| Beamwidth, Vertical | 1.6 ° |
| Boresite Cross Polarization Discrimination (XPD) | 40 dB |
| Electrical Compliance | ETSI Class 3 US FCC Part 101A |
| Front-to-Back Ratio | 64 dB |
| Gain, Low Band | 39.8 dBi |
| Gain, Mid Band | 40.2 dBi |
| Gain, Top Band | 40.6 dBi |
| Operating Frequency Band | 10.700 – 11.700 GHz |

| | |
|---------------------------------------------------|-------------|
| Radiation Pattern Envelope Reference (RPE) | 2312 2314 |
| Return Loss | 26.4 dB |
| VSWR | 1.10 |


Mechanical Specifications

| | |
|--------------------------------------|--------------------|
| Fine Azimuth Adjustment | ±15° |
| Fine Elevation Adjustment | ±20° |
| Mounting Pipe Diameter | 115 mm 4.5 in |
| Net Weight | 69 kg 152 lb |
| Side Struts, Included | 1 inboard |
| Side Struts, Optional | 1 inboard |
| Wind Velocity Operational | 110 km/h 68 mph |
| Wind Velocity Survival Rating | 200 km/h 125 mph |

Wind Forces At Wind Velocity Survival Rating

| | |
|----------------------------------------------|----------------------|
| Angle α for MT Max | -130 ° |
| Axial Force (FA) | 3158 N 710 lbf |
| Side Force (FS) | 1546 N 348 lbf |
| Twisting Moment (MT) | 1072 N-m 791 ft lb |
| Weight with 1/2 in (12 mm) Radial Ice | 356 kg 784 lb |
| Zcg with 1/2 in (12 mm) Radial Ice | 524 mm 21 in |
| Zcg without Ice | 335 mm 13 in |


Wind Forces At Wind Velocity Survival Rating Image



Packed Dimensions

| | |
|-------------------------------------|---------------------|
| Gross Weight, Packed Antenna | 168.0 kg 370.4 lb |
| Height | 840.0 mm 33.1 in |
| Length | 1430.0 mm 56.3 in |
| Volume | 1.7 m ³ |
| Width | 1430.0 mm 56.3 in |

Antenna Dimensions And Mounting Information



| Dimensions in Inches (mm) | | | | | |
|---------------------------|-------------|------------|------------|------------|------------|
| Antenna Size, ft (m) | A | B | C | D | E |
| 4 (1.2) | 50.8 (1291) | 15.0 (382) | 29.5 (751) | 12.2 (310) | 11.6 (295) |

Regulatory Compliance/Certifications

Agency
ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



* Footnotes

Axial Force (FA)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Boresite Cross Polarization Discrimination (XPD)

The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.

Front-to-Back Ratio

Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$, across the

Gain, Mid Band

band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.

Operating Frequency Band

For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.

Packing

Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.

Radiation Pattern Envelope Reference (RPE)

Andrew standard packing is suitable for export. Antennas are shipped as standard in totally recyclable cardboard or wire-bound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.

Return Loss

Radiation patterns define an antenna's ability to discriminate against unwanted signals. Under still dry conditions, production antennas will not have any peak exceeding the current RPE by more than 3dB, maintaining an angular accuracy of +/-1° throughout

Side Force (FS)

The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.

Twisting Moment (MT)

Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

VSWR

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Wind Velocity Operational

Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.

Wind Velocity Survival Rating

The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of 0.3 x the 3 dB beam width of the antenna.

The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.