

TELECOMMUNICATION DRY COUPLING SURFACE MOUNT TRANSFORMER




MODEL NUMBER

TTC-8404

A. Electrical specifications (@ 25 ° C)



1. Pri source impedance; 600 Ω
2. Sec load impedance; 294 Ω
3. MAX output power; 3.6 dBm (2.3mW)
4. Frequency response; ± 0.15 dB, 300 Hz to 3.5 KHz
5. DC unbalance; 0 mA MAX
6. Return loss; 25 dB MIN @ 300 Hz to 3.5 KHz
7. Insertion loss; 3.3 dB ± 0.25 dB @ 1 KHz
8. Longitudinal balance;
60 dB MIN @ 200 Hz to 4 KHz
9. DC resistance;
(1-2) = 157 Ω $\pm 15\%$
(3-4) = 146 Ω $\pm 15\%$
10. Turns ratio;
(1-2) : (3-4) = 1 : 1.00 $\pm 2\%$
11. Dielectric strength;
1000 Vrms 1 minute @ Pri to Sec, Pri to Core
500 Vrms 1 minute @ Sec to Core
12. Total harmonic distortion;
-82 dB TYP @ 600 Hz, -10 dBm

Date code and
country of origin
farside

B. Marking; TTC-8404, TAMURA, date code and country of origin


C. Safety; CSA-C22.2 No. 950-M89 File No. 138028
UL1459, UL1950 File No. 138028

D. Schematic diagram

MOUNTING FOOTPRINT
(CIRCUIT BOARD CUTOUT REQUIRED)

E. Mechanical Specifications

All dimensions shown are nominal unless otherwise specified



PREPARED BY:

ENGINEER:
K. BrennanQUALITY CONTROL:
T. ShiozawaAPPROVED:
D. Kelley

D. Kelley

DRAWING CONTROL NO.
P-A1-11203
ACAD\TTC\A1112031.DWGREV
—MODEL DESCRIPTION
TELECOMMUNICATION SURFACE MOUNT
DRY COUPLING TRANSFORMERTAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624

MODEL SPECIFICATION

TTC-8404

DIM: mm(in) SCL: 4/1 SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.

TRCELECTRONICS, INC.
 "Authorized Distributor"
 135 Pasadena Ave.
 Lodi, NJ 07644 USA
 Tel: (973) 779-8282
 Fax: (973) 779-1490
 sales@trcelectronics.com
 http://www.trcelectronics.com