




FEATURES:

- Designed for Fluke, Amprobe, H-P, Tektronix and Wavetek DMM's with a safety style of sheathed banana plug.
- Probe body incorporates a two step mold process. First step is Polypropylene for probe rigidity. Second step is Santoprene® rubber for handling comfort, added insulation protection and wire strain relief.
- Probe test leads are designed with over-voltage spike protection of up to 6kV.
- Probe body and banana plug are molded directly to the wire for robust pull strength.
- Wire is a high strand count silicone wire for extreme flexibility and high temperature resistance.
- Stainless Steel tip features high conductivity for precision measurements.
- Banana plug spring is nickel-plated beryllium copper for long insertion life.

MATERIALS:

Probe Body: Outer Insulation - Santoprene® Rubber, Color: Gray

Inner Insulation – Polypropylene, Fire Retardant, Color: One Black, One Red

Tip: Stainless Steel

Wire: 18 AWG, 65 x 36 Tinned Copper Strand, Silicone Insulation, Length: 48" (122cm), O.D. .144" (3.66mm)

Banana Plug: Body – Brass, Nickel Plated

Spring – Beryllium Copper, Nickel Plated

Insulation – Polypropylene UL94 V-2, Color: One Black, One Red

RATINGS:

IEC 1010-2-031, Category III, P2 Compliant

Operating Voltage: 1000V

Current: 10 Amperes

ORDERING INFORMATION: Model 5898

Includes a set of one black and one red test lead

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA