



IPS Series

Industrial Pressure Transducer - Ceramic



- **Piezo-resistive thick film ceramic sensor**
- **Stainless steel body**
- **Accuracy $\leq \pm 0.25\%$ FS BFSL**
- **Various outputs including mV, Volts and mA.**
- **Pressure ranges from -1 to 400 bar**

The IPS series is suitable for use in a wide range of industrial applications. The probe uses a piezo-resistive ceramic sensor, giving excellent media compatibility within a stainless steel housing

The electronics incorporate a microprocessor based amplifier, requiring no adjusting and giving stable electronics, especially industrial applications..

Each device is temperature compensated, calibrated and supplied with a traceable serial number and calibration certificate.

Electrical Protection

Supply reverse polarity	No damage/no function
Electromagnetic compatibility	CE Compliant

Performance

Accuracy (Non-Linearity & Hysteresis)	$\leq \pm 0.25\%$ / FS (BFSL)	
Setting Errors (offsets)	2-wire	Zero & Full Scale, $\leq \pm 0.5\%$ / FS
	3-wire	Zero & Full Scale, $\leq \pm 0.5\%$ / FS
	4-wire	Zero & Full Scale, $\leq \pm 0.5\%$ / FS @ 10 Volts

Mechanical Stability

Shock	100g / 11s
Vibration	10g RMS (20 - 2000Hz)

Temperatures & Thermal Effects

Media Temperature	-40°C to +135°C
Ambient Temperature	-20°C to +80°C
Storage temperature	-40°C to +125°C
Compensated temperature range	+20°C to +80°C
Thermal Zero Shift (TZS)	$\leq \pm 0.04\%$ /FS/°C
Thermal Span Shift	$\leq \pm 0.015\%$ /°C

Material Specifications

Housing	303 Stainless Steel
"O" ring seals	Viton
Diaphragm	Ceramic Al ₂ O ₃ 96%
Media wetted parts	Housing & connection, "O" ring seal, diaphragm
Weight	Approx 100g
Installation position	Any
Operational Life	> 100x 10 ⁶ cycles
Insulation resistance	> 50MΩ at 50Vdc

Pressure Ranges and Passive mV/V Outputs

Nominal Pressure, Gauge,	bar	1	2	5	10	20	50	100	250	400
Compound range	bar	-1 to 0	-1 to 2	-1 to 5	-1 to 9	-1 to 19	-1 to 24			
Permissible Overpressure	bar	2	4	10	20	40	100	200	400	650
Burst Pressure	bar	4	5	12	25	50	120	250	500	650

Output Signals and Supply Voltages

Wire system	Output	Supply Voltage	Connection Pin Nos		
2-wire	4-20mA	9-32Vdc	+ve Supply Pin 1	-ve Supply Pin 2	Ground Earth Pin
3-wire	0-5Vdc	9-32Vdc	+ve Supply Pin 1	-ve Supply Pin 2	
			+ve Output Pin 3	Ground	Earth Pin
4-wire (amplified)	10mV/V (ratiometric)	3-12Vdc	+ve Supply Pin 1	-ve Supply Pin 2	
			+ve Output Pin 3	-ve Output	Earth Pin

Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969

Email:sales@cynergy3.com

ISO9001 CERTIFIED

www.cynergy3.com

IPS 2016

© 2016 Cynergy3 Components, All Rights Reserved. Specifications are subject to change without prior notice. Cynergy3 Components and the Cynergy3 Components logo are trademarks of Cynergy3 Components Limited.




IPS Series

Industrial Pressure Sensor - Ceramic

Part Number	Pressure Rating	Output
IPS-G1000-3	0 - 1 Bar G	0 - 100mV
IPS-G1000-5	0 - 1 Bar G	4 - 20mA
IPS-G1000-6	0 - 1 Bar G	0 - 5V
IPS-G6000-3	0 - 6 Bar G	0 - 100mV
IPS-G6000-5	0 - 6 Bar G	4 - 20mA
IPS-G6000-6	0 - 6 Bar G	0 - 5V
IPS-GM1P9-5	-1 to +9 Bar G	4 - 20mA
IPS-GM1P9-6	-1 to +9 Bar G	0 - 5V
IPS-G1002-3	0 - 10 Bar G	0 - 100mV
IPS-G1002-5	0 - 10 Bar G	4 - 20mA
IPS-G1002-6	0 - 10 Bar G	0 - 5V
IPS-G1602-3	0 - 16 Bar G	0 - 100mV
IPS-G1602-5	0 - 16 bar G	4-20mA
IPS-G1602-6	0 - 16 bar G	0-5V
IPS-C0184-5	-1 to +24 Bar G	4 - 20mA
IPS-C0184-6	-1 to +24 Bar G	0 - 5V
IPS-G2502-3	0 - 25 Bar G	0 - 100mV
IPS-G2502-5	0 - 25 Bar G	4 - 20mA
IPS-G2502-6	0 - 25 Bar G	0 - 5V
IPS-G4002-3	0 - 40 Bar G	0 - 100mV
IPS-G4002-5	0 - 40 Bar G	4 - 20mA
IPS-G4002-6	0 - 40 Bar G	0 - 5V
IPS-G1003-3	0 - 100 Bar G	0 - 100mV
IPS-G1003-5	0 - 100 Bar G	4 - 20mA
IPS-G1003-6	0 - 100 Bar G	0 - 5V
IPS-G2503-3	0 - 250 Bar G	0 - 100mV
IPS-G2503-5	0 - 250 Bar G	4 - 20mA
IPS-G2503-6	0 - 250 Bar G	0 - 5V
IPS-G4003-3	0 - 400 Bar G	0 - 100mV
IPS-G4003-5	0 - 400 Bar G	4 - 20mA
IPS-G4003-6	0 - 400 Bar G	0 - 5V

Mechanical Dimensions



Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969

Email: sales@cynergy3.com

ISO9001 CERTIFIED

www.cynergy3.com