


NOTE:
1. SUGGESTED MTG. HOLE = $\phi.160$




04

LEAD FINISH:	SOLDER
EYELET FINISH:	SILVER
CAPACITANCE	1750pF MIN.
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C: --- VDC 125°C: 200 VDC

D.C.R.=.01 Ohms MAX.

MIN. I.L. PER MIL-STD-220 @ 25 ϕ NO LOAD

FREQ. MHz	I.L. (db)
1	N/A
10	5
100	50
1 GHz	60
10GHz	70



MARKING:

PART: NONE

BAG: SCI

1214-029

DATE CODE

LOT NO.

QTY./BAG (200 MAX.)

	4	3	2	1	0	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	api  FAIRVIEW PENNSYLVANIA technologies corp.	
	CN #20899	CN 49738-ENG	CN 13179-CPD	CN 169482	CN 162125	CHANGE NOTICE	Fractions $\pm 1/64$		
							Dec. .xx $\pm$	Dwn. Kauffman	Description
							Dec. .xxx $\pm$.010	Date 7-29-16	SOLDER-IN FILTER
							Angles $\pm 0^{\circ} 30'$	Engr DEVINE	1214-029
							CODE IDENT. NO. OLSP2	Scale N.T.S.	