

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


0458301027

Status:

Contact Molex

Description:

1.20mm (.047") by 2.00mm (.079") Pitch HD Mezz™ Plug, 351 Circuits, 18.00mm (.708") Unmated Height, 27 Rows, Tin (Sn)/Lead (Pb) Plating



Series

image - Reference only

Documents:

Drawing (PDF)

Product Specification PS-45802-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

General

Product Family

Series

Application

Comments

PCB Headers

45830

Board-to-Board, Signal

1.20mm (.047") Pitch Pin-to-Pin and 2.00mm (.079") Pitch Row-to-Row

Product Name

HD Mezz™

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Robotic Placement

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

351

351

Black

100

No

94V-0

No

No

None

Yes

High Performance Alloy (HPA)

Gold

Tin

High Temperature Thermoplastic

27

Vertical

Yes

Yes

Tray

1.20mm (.047")

1.20mm (.047")

0.762µm (30µ")

2.540µm (100µ")

Yes

Yes

Vacuum Pick-Up Clip

Closed Ends

No

Yes

-55°C to +105°C

Surface Mount

Electrical

Current - Maximum per Contact

2A

EU RoHS

Not RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

45830Series

Mates With

45802 HD Mezz™ Receptacle

Voltage - Maximum	250V AC
-------------------	---------

Solder Process Data

Duration at Max. Process Temperature (seconds)	20
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	2
Process Temperature max. C	230
Replacement RoHS Compliant Part Number	0458301225

Material Info

Reference - Drawing Numbers

Product Specification	PS-45802-001
Sales Drawing	SD-45830-0001

This document was generated on 03/03/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION