



LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	OWN	APVD	
G	14		C2	REVISED PER ECO-11-004917	11MAR11	RK	HMR	



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED

- 1 STAMP AMP 16-14* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545
- 4 MEETS M7928/7-8, CLASS 1 & 2
- 5 MEETS M7928/7-8, CLASS 2
- 6 RECOMMENDED OPERATING TEM IS 170°C MAX
- 7 WIRE CROSS SECTIONAL AREA RANGE IS 1.04-2,62mm2 [2,050-5,180] CMA

5000	ON TAPE	5 2-320093-1
----	LOOSE PIECE	4 320093
QUANTITY	PACKAGING TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	TE Connectivity	
DIMENSIONS: mm[INCHES]		CHK DA PATTERSON 3-17-93		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JL MECKLEY 3-17-93	NAME TERMINAL, RING TONGUE, SOLISTRAND	
	0 PLC ± -	PRODUCT SPEC		
	1 PLC ± -	APPLICATION SPEC		
	2 PLC ± -	—		
MATERIAL	ANGLES ± ± -	—	SIZE	CAGE CODE
	FINISH	—	WEIGHT	DRAWING NO
2	3	CUSTOMER DRAWING	8:1	1 of 1
		SCALE	SHEET	REV
		8:1	1 of 1	C2