





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		N7	REVISED PER ECO-13-014668	17SEP2013	KH	MB

.160	4DB-P108-17	5.590	17	4-1437667-2
.160	4DB-P108-16	5.265	16	4-1437667-0
.160	4DB-P108-15	4.940	15	3-1437667-9
2 1 .160	4DB-P108-14-102	4.615	14	2-796658-5
2 .160	4DB-P108-14-102	4.615	14	2-796658-3
.160	4DB-P108-14	4.615	14	3-1437667-8
.160	4DB-P108-13	4.290	13	3-1437667-7
.160	4DB-P108-12	3.965	12	3-1437667-6
.160	4DB-P108-11	3.640	11	3-1437667-5
.160	4DB-P108-10	3.315	10	3-1437667-3
5 2 .160	4DB-P106-09-094	2.990	9	1-796658-7
.160	4DB-P108-09	2.990	9	3-1437667-2
6 1 OBSELETE	4DB-P108-08-091	2.665	8	1-796658-4
.160	4DB-P108-08	2.665	8	3-1437667-1
5 3 2 .160	4DB-P106-07-100	2.340	7	2-796658-2
.160	4DB-P106-07-093	2.340	7	1-796658-6
5 3 2 .160	4DB-P106-06-099	2.015	6	2-796658-1
6 1 OBSELETE	4DB-P108-06-090	2.015	6	1-796658-3
5 .200	4DB-P108-06	2.015	6	2-796658-6
.160	4DB-P108-06	2.015	6	2-1437667-9
5 3 2 .160	4DB-P106-05-098	1.690	5	2-796658-0
6 4 OBSELETE	4DB-P108-05-093	1.690	5	1-796658-5
.160	4DB-P108-05	1.690	5	2-1437667-8
5 3 2 .160	4DB-P106-04-097	1.365	4	1-796658-9
1 .160	4DB-P108-04-089	1.365	4	1-796658-2
.160	4DB-P108-04	1.365	4	2-1437667-6
5 3 2 .160	4DB-P106-03-096	1.040	3	1-796658-8
6 1 .160	4DB-P108-03-088	1.040	3	1-796658-1
.160	4DB-P108-03	1.040	3	2-1437667-5
7 5 .142	4DB-P108-02-143	.715	2	2-796658-8
5 .142	4DB-P108-02-142	.715	2	2-796658-7
.160	4DB-P108-02	.715	2	2-1437667-4



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .01
3 PLC ± .005
4 PLC ± -
ANGLES ± 1°

MATERIAL

-

DWN S WELDON 01MAY2003
CHK S YODER 5/1/03
APVD S YODER 5/1/03
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

CUSTOMER DRAWING

SCALE NTS

SHEET 1 OF 2

REV N7

TE Connectivity

NAME

ASSEMBLY, DUAL BARRIER
4DB-P108-XX

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2-1437667-4

-


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	—	SEE SHEET 1	—	—	—	

MATERIAL:
HOUSING: THERMOPLASTIC PA, UL94V-0, BLACK.
TERIMINAL: BRIGHT TIN PLATED, COPPER ALLOY.
SCREW: 6-32, STEEL, ZINC PLATED CLEAR CHROMATE.

ELECTRICAL:
UL CLASS C: 20A, 150V.
UL CLASS D: 10A, 300V.
CSA TYPE B: 20A, 300V.
CSA TYPE C: 20A, 300V.
CSA TYPE D: 10A, 300V.
CSA TYPE E: 20A, 300V.
WIRE RANGE: 12-22 AWG

MECHANICAL:
MAXIMUM TORQUE RATING: 7 IN-LBS.
RUNNING TORQUE: 0.5-3.5 IN-LBS UNLESS
OTHERWISE STATED.

- 1 SCREWS ARE BOTTOMED, NO THREAD INTERRUPT.
- 2 SCREWS ARE NICKEL PLATED BRASS.
- 3 SCREWS ARE CAPTIVE.
- 4 SEE FIGURE.
- 5 PRELIMINARY PART NUMBER.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 7 TERMINAL FINISH: MATTE TIN



.160	4DB-P108-04-SPCL	1.365	4	3-796658-0
.160	4DB-P108-03-SPCL	1.040	3	2-796658-9
.160	4DB-P108-30	9.815	30	5-1437667-5
.160	4DB-P108-29	9.490	29	796658-9
.160	4DB-P108-28	9.165	28	5-1437667-3
.160	4DB-P108-27	8.840	27	796658-8
.160	4DB-P108-26	8.515	26	5-1437667-2
.160	4DB-P108-25	8.190	25	796658-7
.160	4DB-P108-24	7.865	24	5-1437667-0
.160	4DB-P108-23	7.540	23	796658-6
.160	4DB-P108-22	7.215	22	4-1437667-8
.160	4DB-P108-21	6.890	21	796658-2
.160	4DB-P108-20	6.565	20	4-1437667-6
.160	4DB-P108-19	6.240	19	4-1437667-5
.160	4DB-P108-18	5.915	18	4-1437667-4
.160	4DB-P108-16-105	5.590	17	2-796628-4
DIM B	CATALOG NUMBER	DIM A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —
1 PLC ± —
2 PLC ± .01
3 PLC ± .005
4 PLC ± —
ANGLES ± 1°
FINISH —

MATERIAL

—

DWN S WELDON 01MAY2003
CHK S YODER 5/1/03
APVD S YODER 5/1/03
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity
NAME ASSEMBLY, DUAL BARRIER
4DB-P108-XX
SIZE A3 CAGE CODE 00779 DRAWING NO C-2-1437667-4 RESTRICTED TO —
CUSTOMER DRAWING SCALE NTS SHEET 2 OF 2 REV N7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4DB-P108-15](#) [4DB-P108-19](#) [4DB-P108-21](#) [4DB-P108-13](#) [4DB-P108-24](#) [4DB-P108-28](#) [4DB-P108-14](#) [4DB-P108-20](#)