



SiI9135/SiI9235A HDMI Receiver with Enhanced Audio and Deep Color Outputs

Data Brief

Document # SiI-DB-0206-F01

April, 2010

Copyright Notice

Copyright © 2008-2010 Silicon Image, Inc. All rights reserved. These materials contain proprietary and confidential information (including trade secrets, copyright, and other interests) of Silicon Image, Inc. You may not use these materials except only for your bona fide non-commercial evaluation of your potential purchase of products and/or services from Silicon Image or its affiliates, and/or only in connection with your purchase of products and/or services from Silicon Image or its affiliates, and only in accordance with the terms and conditions herein. You have no right to copy, modify, transfer, sublicense, publicly display, create derivative works of or distribute these materials, or otherwise make these materials available, in whole or in part, to any third party.

Patents

The subject matter described herein contains one or more inventions claimed in patents and / or patents pending owned by Silicon Image, Inc., including but not limited to the inventions claimed in US patents #6,914,637, #6,151,334, #6,026,124, #5,974,464 and #5,825,824.

Trademark Acknowledgment

Silicon Image™, VastLane™, SteelVine™, PinnaClear™, Simplay™, Simplay HD™, Satalink™, InstaPort™, TMDS™, and LiquidHD™ are trademarks or registered trademarks of Silicon Image, Inc. in the United States and other countries. HDMI®, the HDMI logo and High-Definition Multimedia Interface™ are trademarks or registered trademarks of, and are used under license from, HDMI Licensing, LLC. x.v.Color™ is a trademark of Sony Corporation.

Export Controlled Document

This document contains information subject to the Export Administration Regulations (EAR) and has a classification of EAR99 or is controlled for Anti-Terrorism (AT) purposes. Transfer of this information by any means to an EAR Country Group E:1 or foreign national thereof (whether in the U.S. or abroad) may require an export license or other approval from the U.S. Department of Commerce. For more information, contact the Silicon Image Director of Global Trade Compliance.

Further Information

To request other materials, detailed hardware and software guides, and additional information, contact your local Silicon Image, Inc. sales office or visit the Silicon Image, Inc. web site at www.siliconimage.com. Information about obtaining licenses required for using HDMI and HDCP technologies is available from www.hdmi.org and www.digital-cp.com.

© 2008-2010 Silicon Image, Inc. All rights reserved

Introduction

The SiI9135/SiI9235A HDMI Receiver with Enhanced Audio and Deep Color Outputs is a second-generation dual-input High Definition Multimedia Interface (HDMI) receiver. It is software-compatible with the SiI9133 receiver, but adds audio support for DTS-HD and Dolby TrueHD. Digital televisions that can display 10- or 12-bit color depth can now provide the highest quality protected digital audio and video over a single cable. The SiI9135 and SiI9135A devices, which are functionally identical, can receive Deep Color video up to 12-bit, 1080p @ 60 Hz. Backward compatibility with the DVI 1.0 specification allows HDMI systems to connect to existing DVI 1.0 hosts, such as HD set-top boxes and PCs. Silicon Image HDMI receivers use the latest generation Transition Minimized Differential Signaling (TMDS) core technology that runs at 25–225 MHz.

The chip comes pre-programmed with High-bandwidth Digital Content Protection (HDCP) keys for receiving protected audio and video content. This set of keys simplifies the manufacturing process and lowers costs while providing the highest level of HDCP key security.

The SiI9135/SiI9135A receiver can send and receive up to eight channels of uncompressed digital audio at 192 kHz and 2-channel digital audio up to 192 kHz. Compressed streams are also supported through either the S/PDIF port or over I²S for DTS-HD and Dolby TrueHD. An industry-standard I²S port allows direct connection to low-cost audio DACs at up to 192 kHz. An S/PDIF port supports up to 192 kHz audio. The device supports Super Audio Compact Disc (SACD) and provides Direct Stream Digital (DSD) ports that support 44.1 and 88.2-kHz one-bit audio.

A low-power standby feature of the SiI9135/SiI9135A receiver enables flexible power management.

Digital Video Interface

- Flexible support for many different standard- and high-definition video formats (36-bit RGB / YCbCr 4:4:4, 16/20/24-bit YCbCr 4:2:2, 8/10/12-bit YCbCr 4:2:2 (ITU BT.656))
- 12/15/18-bit Digital Multimedia Output (DMO) RGB/YCbCr 4:4:4 (clocked with rising and falling edges)
- Color Space Conversion for both RGB-to-YCbCr and YCbCr-to-RGB (both 601 and 709)
- True 12-bit accurate data using 14-bit processing
- Auto video mode configuration simplifies system firmware design

Digital Audio Interface

- DTS-HD and Dolby TrueHD high bit rate audio
- Four I²S inputs accept Dolby Digital, DVD-Audio input (2-channel 192 kHz and 8-channel 192 kHz)
- S/PDIF input supports PCM, Dolby Digital, DTS digital audio transmission (32–192 kHz Fs sample rate)
- IEC60958 or IEC61937 compatible
- Flexible, programmable I²S channel mapping

HDCP Decryption

- Pre-programmed HDCP keys provide the highest level of key security, simplify manufacturing, and lower cost
- Full support for HDCP repeaters (up to 16 attached downstream devices)

Package

- 20 mm x 20 mm 144-pin TQFP package with ePad™




Figure 1. Typical Application of SiI9135/SiI9135A Receiver

System Applications

The SiI9135/SiI9135A receiver is designed for AV receivers that require support for HDMI Deep Color and the latest audio technologies: DTS-HD and Dolby TrueHD. The receiver allows receiving 10/12-bit color depth up to 1080p resolutions. A single device provides two HDMI input ports. The video output goes to a video processor or HDMI transmitter. Besides DTS-HD and Dolby TrueHD, the device supports full surround sound audio including DVD-Audio and SACD. The audio output can go directly to an audio DAC or an audio digital signal processor for further processing.

Comparing the SiI9135/SiI9135A Receiver with the SiI9033 and SiI9133 Receivers

Table 1 summarizes the functional differences among the SiI9033, the SiI9133, and the SiI9135/SiI9135A receivers.

Table 1. Summary of New Features

Feature	SiI9033	SiI9133	SiI9135/SiI9135A
HDMI Input Connections			
TMDS Input Ports	2	2	2
Color Depth	8-bit	8/10/12-bit	8/10/12-bit
DDC Input Ports	2	2	2
Maximum TMDS Input Clock	165 MHz	225 MHz	225 MHz
Output Ports			
Digital Video Output Ports	1	1	1
Maximum Output Pixel Clock	165 MHz.	165 MHz.	165 MHz.
Maximum Output Bus Width	24	36	36
Analog Video Output Ports	0	0	0
S/PDIF Output Ports	1	1	1
I²S Output	8 channel	8 channel	8 channel
DSD Output	8 channel	8 channel	6 channel
Video Processing			
Color Space Converter	RGB to/from YcbCr	RGB to/from YcbCr	RGB to/from YcbCr
Pixel Clock Divider	0.25, 0.5	0.25, 0.5	0.25, 0.5
Digital Video Bus Mapping	swap Cb, Cr pins	swap Cb, Cr pins	swap Cb, Cr pins
Maximum Audio Sample Rate (Fs)			
2-channel (I²S or S/PDIF)	192 kHz	192 kHz	192 kHz
8-channel (I²S)	192 kHz	192 kHz	192 kHz
8-channel (DSD)	88.2 kHz	88.2 kHz	88.2 kHz (6 channel)
High Bit Rate Audio Support Compressed DTS-HD and Dolby True-HD	No	No	Yes
Other Features			
MCLK Generation	No external connection required.	No external Connection required	No external connection required.
HDCP Repeater Support	Yes	Yes	Yes
Interlaced Format Detection Pin	Yes	Yes	Yes
TMDS R_{EXT_SWING}	Not Used	Not Used	Not Used
Package	144-pin TQFP ePad	404-pin BGA w/Heat Slug	144-pin TQFP ePad

Pin Diagrams

Figure 2 shows the SiI9135/SiI9135A pin assignments of the receiver. Pin names are generalized by type for this document. The list below the diagram describes the purpose of each type. The package is a 20 mm x 20 mm 144-pin TQFP with an ePad.





Figure 2. Pin Diagram

Packaging

ePad Enhancement

The SiI9135/SiI9135A receiver is packaged in a 144-pin TQFP package with an ePad™. The ePad dimensions are shown in [Figure 3](#).



Silicon Image recommends that the ePad be soldered to the PCB and electrically grounded on the PCB. The ePad must not be connected to any other voltage level.

Figure 3. ePad Diagram

ePad Dimensions: Amkor and SPIL

Item	Description	Typ	Max
T1	ePad height	4.60	4.64
T2	ePad width	5.20	5.24

ePad Dimensions: ASE

Item	Description	Typ	Max
T1	ePad height	5.25	5.29
T2	ePad width	5.25	5.29

All dimensions are in millimeters.


The ePad is centered on the package center lines. The measurement tolerance is ± 0.04 mm for all manufacturers. The ePad tab dimensions may vary.

A clearance of at least 0.25 mm should be provided on the PCB between the edge of the ePad and the inner edges of the lead pads to avoid the possibility of electrical shorts.

PCB Layout Guidelines

PCB layout designers should refer to Silicon Image application note *PCB Layout Guidelines: Designing with Exposed Pads* for basic design guidelines when designing with thermally enhanced packages using the Exposed Pad.

144-pin TQFP Package Dimensions



JEDEC Package Code MS-026-AFB

Item	Description	Min	Typ	Max
A	Thickness	1.00	1.10	1.20
A1	Stand-off	0.05	0.10	0.15
A2	Body thickness	0.95	1.00	1.05
D	Footprint	22.00 BSC		
E	Footprint	22.00 BSC		
D1	Body size	20.00 BSC		
E1	Body size	20.00 BSC		
D2	Lead Row Width	17.5 BSC		
E2	Lead Row Width	17.5 BSC		

Item	Description	Min	Typ	Max
b	Lead width	0.17	0.22	0.27
C	Lead thickness	0.09	—	0.20
e	Lead pitch	0.50 BSC		
L	Lead foot length	0.45	0.60	0.75
L1	Total lead length	1.00 REF		
R1	Lead radius, inside	0.08	—	—
R2	Lead radius, outside	0.08	—	0.20
S	Lead horizontal run	0.20	—	—

Dimensions in millimeters.

Overall thickness A = A1 + A2.

Figure 4. Package Diagram

Marking Specification

Drawing is not to scale and pin count shown is representative. Refer to specifics in Figure 4 on page 5.




Figure 5. Marking Diagram

The universal package may be used in lead-free and ordinary process lines

Ordering Information

Production Part Numbers:

TMDS Input Clock Range	Part Number
25–225 MHz	SiI9135CTU
25–225 MHz	SiI9135ACTU

Disclaimers

These materials are provided on an “AS IS” basis. Silicon Image, Inc. and its affiliates disclaim all representations and warranties (express, implied, statutory or otherwise), including but not limited to: (i) all implied warranties of merchantability, fitness for a particular purpose, and/or non-infringement of third party rights; (ii) all warranties arising out of course-of-dealing, usage, and/or trade; and (iii) all warranties that the information or results provided in, or that may be obtained from use of, the materials are accurate, reliable, complete, up-to-date, or produce specific outcomes. Silicon Image, Inc. and its affiliates assume no liability or responsibility for any errors or omissions in these materials, makes no commitment or warranty to correct any such errors or omissions or update or keep current the information contained in these materials, and expressly disclaims all direct, indirect, special, incidental, consequential, reliance and punitive damages, including WITHOUT LIMITATION any loss of profits arising out of your access to, use or interpretation of, or actions taken or not taken based on the content of these materials.

Silicon Image, Inc. and its affiliates reserve the right, without notice, to periodically modify the information in these materials, and to add to, delete, and/or change any of this information.

Notwithstanding the foregoing, these materials shall not, in the absence of authorization under U.S. and local law and regulations, as required, be used by or exported or re-exported to (i) any U.S. sanctioned or embargoed country, or to nationals or residents of such countries; or (ii) any person, entity, organization or other party identified on the U.S. Department of Commerce's Denied Persons or Entity List, the U.S. Department of Treasury's Specially Designated Nationals or Blocked Persons List, or the Department of State's Debarred Parties List, as published and revised from time to time; (iii) any party engaged in nuclear, chemical/biological weapons or missile proliferation activities; or (iv) any party for use in the design, development, or production of rocket systems or unmanned air vehicles.

Products and Services

The products and services described in these materials, and any other information, services, designs, know-how and/or products provided by Silicon Image, Inc. and/or its affiliates are provided on as “AS IS” basis, except to the extent that Silicon Image, Inc. and/or its affiliates provides an applicable written limited warranty in its standard form license agreements, standard Terms and Conditions of Sale and Service or its other applicable standard form agreements, in which case such limited warranty shall apply and shall govern in lieu of all other warranties (express, statutory, or implied). EXCEPT FOR SUCH LIMITED WARRANTY, SILICON IMAGE, INC. AND ITS AFFILIATES DISCLAIM ALL REPRESENTATIONS AND WARRANTIES (EXPRESS, IMPLIED, STATUTORY OR OTHERWISE), REGARDING THE INFORMATION, SERVICES, DESIGNS, KNOW-HOW AND PRODUCTS PROVIDED BY SILICON IMAGE, INC. AND/OR ITS AFFILIATES, INCLUDING BUT NOT LIMITED TO, ALL IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND/OR NON-INFRINGEMENT OF THIRD PARTY RIGHTS. YOU ACKNOWLEDGE AND AGREE THAT SUCH INFORMATION, SERVICES, DESIGNS, KNOW-HOW AND PRODUCTS HAVE NOT BEEN DESIGNED, TESTED, OR MANUFACTURED FOR USE OR RESALE IN SYSTEMS WHERE THE FAILURE, MALFUNCTION, OR ANY INACCURACY OF THESE ITEMS CARRIES A RISK OF DEATH OR SERIOUS BODILY INJURY, INCLUDING, BUT NOT LIMITED TO, USE IN NUCLEAR FACILITIES, AIRCRAFT NAVIGATION OR COMMUNICATION, EMERGENCY SYSTEMS, OR OTHER SYSTEMS WITH A SIMILAR DEGREE OF POTENTIAL HAZARD. NO PERSON IS AUTHORIZED TO MAKE ANY OTHER WARRANTY OR REPRESENTATION CONCERNING THE PERFORMANCE OF THE INFORMATION, PRODUCTS, KNOW-HOW, DESIGNS OR SERVICES OTHER THAN AS PROVIDED IN THESE TERMS AND CONDITIONS.



1060 E. Arques Avenue
Sunnyvale, CA 94085
T 408.616.4000 F 408.830.9530
www.siliconimage.com