



The model 501 can be used for general purpose insulation tests that require voltages from 50V to 1000V only.

The Instrument is equipped with AC and DC measuring ranges up to 1000V. This is advantageous for testing for the absence of voltage and the discharge of capacitive devices under test.

The 501 features a quick testing signal lamp within the test probe that illuminates the work area. The signal lamp can also be used for quick Pass/Fail evaluations of insulation resistances. Minimum values for insulation resistances are present if the lamp lights up.

Comes equipped with built-in test probes, an alligator clip, a leatherette carrying case and batteries.

- Five Test Voltages: 50, 100, 250, 500, and 1000 VDC
- Voltage Measurement to 1000 V AC/DC
- Test Probe Signal Lamp Illuminates Work Area and Indicates Pass/Fail of Insulation Resistance
- Battery Powered with Battery Test and Battery Charge Indicator
- Rugged Tester Design for Industrial Applications with Leatherette Carrying Case

## Measuring Ranges

### INSULATION RESISTANCE

Measuring Range	Open-Circuit Voltage $U_o$	Internal Resistance $R_i$	Lamp in Test Prod (1) Lights for Resistance
0...50KΩ 20KΩ...1MΩ 200KΩ...20MΩ	60V	30KΩ 10KΩ 40KΩ	> 100KΩ
0...100KΩ 40KΩ...2MΩ 400KΩ...40MΩ	120V	60KΩ 20KΩ 80KΩ	> 200KΩ
0...250KΩ 100KΩ...5MΩ 1MΩ...100MΩ	300V	150KΩ 50KΩ 200KΩ	> 500KΩ
0...500KΩ 200KΩ...10MΩ 2MΩ...200MΩ	600V	300KΩ 100KΩ 400KΩ	> 1MΩ
0...1MΩ 400KΩ...20MΩ 4MΩ...400KΩ	1200V	600KΩ 200KΩ 800KΩ	> 2MΩ
0...4KΩ	9V	—	—

(1) Switching Accuracy

### DIRECT AND ALTERNATING CURRENT

Measuring Range	Frequency	Internal Resistance	Maximum Overload	Intrinsic Error (1)
0 to 1000V AC/DC	0 or 40 to 200Hz	900KΩ	1200V AC/DC Continuous	±2.5%

(1) Referring to scale length

## Ordering Information

ACCESSORIES	Catalog No.
501 Insulation Tester, 1000 V	12501



## Specifications

### REFERENCE CONDITIONS

Ambient Temperature: 73°F (23°C) ± 4°F (2°C)

Relative Humidity: 45 to 55%

Measurement Magnitude Frequency: 45-65 Hz (voltage measurements)

Line Voltage Waveform: Sine, deviation between effective and rectified value < .5%

Battery Voltage: 9V ± .5V

Operating Position: Horizontal

### ELECTROMAGNETIC COMPATIBILITY EMC

Interference Emission:

EN 50081-1: 1992

Interference Immunity:

EN 50082-1: 1992

### ELECTRICAL SAFETY

Designed to IEC 1010-1

Protection Class: II

Test Voltage: ≈ 5.55kV

Overvoltage Classification: II

Pollution Degree: 2

Protection: Housing IP52

### AMBIENT CONDITIONS

Operating Temp. Range: 32°F (0°C) to 104°F (40°C)

Storage Temp. Range: -4°F (-20°C) to 140°F (60°C) (without batteries)

Relative Humidity: Max. 45-55%, condensation must be avoided

### MECHANICAL DESIGN

Dimensions: W 6.50" (165mm) x

D 4.33" (110mm) x H 4.92" (125mm)

Weight: 3.5 lbs. (1.6kg) (with batteries)

### POWER SUPPLY

Standard or Storage Battery: 6 ea. 1.5V "D" size batteries

Working Range: 7V to 10V

Battery Service Life: Number of possible measurements with 1 set of "D" size batteries (with lamp in test prod switched off): at least 3,000 measurements of an insulation resistance of 1MΩ (Nominal Voltage of 1000 V, 5 sec. Measurement duration, switched off for 25 sec. etc.)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Simpson:](#)

[12501](#)