





**Sensitivity and image quality up, low energy consumption.
No ultra-small color board camera is so ideal
for so many applications.**

Panasonic announce the introduction of a new addition to our world-renown color board camera line-up. The GP-KX121 series combines high image quality and high sensitivity with an energy saving design. These incredibly versatile ultra-small, ultra-light cameras offer the highest cost-performance ever.


Key Features

- Ultra-small 22mm(H) x 26mm(W) package.
- Horizontal 500-pixel array in a 1/4-type CCD, integrated with single chip digital signal processing (DSP).
- 300 lines of horizontal resolution and high sensitivity and image quality in lighting as low as 5 lx at F2.0 lens.
- MCM PCB design offers ultra-compact thin size, light weight, and high durability.
- Options include two types of lenses, with 45° and 51° horizontal image angle.

Actual size



- | | | |
|--|---------------------------------------|-------------------------------------|
| • Notebook PCs | • Medical/Dental checks | • In-store and ATM surveillance |
| • Videophones | • Recording natural observations | • And these are just the beginning. |
| • Rear-view monitoring for automobiles | • and special monitoring applications | |



Notebook PCs



Videophones



Automobiles



Video Intercoms




ATMs

SPECIFICATIONS

TV Standard	NTSC		PAL
Model No.	GP-KX121P series		GP-KX121E series
Pick-up Device	1/4-type CCD with complimentary color filter		
Actual Number of Pixels	512H x 492V	512H x 582V	
Total Number of Pixels	542H x 492V	542H x 582V	
Imaging Area	3.68 mm (H) x 2.75 mm (V)	3.68 mm (H) x 2.74 mm (V)	
Pixel Dimensions	7.20 μm(H) x 5.60μm (V)	7.20 μm(H) x 4.70μm (V)	
Imaging System	Interline field memory 2-line simultaneous read-out		
Horizontal Scanning Frequency	15.734 kHz	15.625 kHz	
Vertical Scanning Frequency	59.94 Hz	60.00 Hz	
Number of Scanned Lines	525 lines	625 lines	
Frames per Second	30 frames	25 frames	
Synchronization	Internal synchronization		
Video Output	VBS 1 V(p-p) / 75 Ω composite signal		
Resolution	Horizontal	Min. 330 lines (center area)	
	Vertical	Min. 350 lines (center area)	Min. 400 lines (centre area)
S/N Ratio	46 dB (with AGC off, Weight on)		
Minimum Illumination	6 lx (at F2.8), 3 lx (at F2.0)		
AGC	ON fixed (0dB ~ +15dB)		
ELC	(1/60 ~ 1/96,000s)	(1/50 ~ 1/96,000s)	
White Balance	ATW (ON fixed)		
External Terminals	6-pin cable connector (1) Power input (2) GND (3) Video output (4) GND (5) I ² C SCL (6) I ² C SDA		
Power Supply Range	DC 4.8 ~ 5.5 V		
Power Consumption	125 mA (DC 5.0 V)		
Temperature Range	Operating (Actual use): -10°C ~ +50°C (PCB only) Guaranteed performance: +5°C ~ +35°C		
Humidity Range	Operating: 90% max. Storage: 95% max.		
Dimensions (GP-KX121/51)	26.8 mm (W) x 22 mm (H) x 29.3 mm (D) (including connector)		
Weight (GP-KX121/51)	approx. 11 g		

EXTERNAL TERMINALS: JST BM06B-SRSS-TB



OPTIONAL ACCESSORIES


Connector Cable (10 pcs per package)
Z-E498-01

Regulator Board (from 12V to 5V DC)
GP-PSB12E

CONFIGURATIONS

Model No.	Lens type	Horizontal field angle	Max. aperture	Focal length
GP-KX121P/E	without lens			
GP-KX121/45P/E	Pin-hole	45.0°	F2.8	4.6 mm
GP-KX121/51P/E	Standard	51.0°	F2.0	3.7 mm

APPEARANCE



PIN ASSIGNMENT

Pin Array		
Pin	Signal name	Explanation
1	DC	Power Input
2	GND	GND
3	VIDEO OUT	Video Output
4	GND	GND
5	SCL	OPEN
6	SDA	OPEN

- Weights and dimensions are approximate.
- Specifications are subject to change without notice.
- These products may be subject to export control regulations.

DISTRIBUTED BY: