



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: APSINT2012

### PowerVerter® APS INT Series 2000W Inverter/Charger with Auto-Transfer Switching and Hardwire Input/Output

#### Highlights



- 12V DC or 230V AC input; 230V, 50 Hz output (hardwired)
- 2000 watts continuous, 3000 watts OverPower and 4000 watts DoubleBoost inverter output (see specifications)
- 3 stage, selectable 15/60 amp wet/dry cell battery charger
- Auto Transfer Switching option for battery backup / UPS operation
- Reliability enhanced large-transformer design with protected DC and AC wiring terminals

#### Description

Tripp Lite's APSINT2012 DC-to-AC inverter with automatic line-to-battery transfer and integrated charging system serves as an extended run UPS, a standalone power source or an automotive inverter. Supplies up to 2000 watts of continuous 230V AC power from any 12V battery or automotive DC source. When hardwire AC input is energized, commercial power passes through to connected equipment and the battery set is recharged via 3 stage, selectable 15/60 amp charging system. In UPS mode, the APS system responds to blackouts and voltage fluctuations with a near instantaneous automatic transfer to battery-derived AC output. Includes a set of high current DC input terminals for simple installation (user supplies batteries and cabling - see owner's manual for recommendations). Passes sine wave utility or generator power during battery charging and UPS line power operation, plus efficient PWM sine wave AC output in inverter and UPS backup modes. Reliable large transformer design, with frequency control powers resistive electronic loads or large inductive motors, compressors and other items with high current needs on startup. Optional APSRM4 wired remote power switch with full status LEDs provides remote power inverter on/off switching and continuous status information (APSRM4 sold separate). Supports an unlimited amount of runtime with any number of user-supplied batteries connected. Highly adaptable to a variety of applications and site conditions with adjustable charger settings for wet/gel battery types and selectable line to battery power transfer voltages.

#### Applications

- Ideal for RVs, over-the-road trucking, conversion vans and fleet service vehicles; a standalone alternative power source for off-grid, alternative energy or export applications and as an uninterruptible power supply (UPS) for items compatible with a 20 millisecond transfer time. Moisture-resistant construction enables vehicular or marine operation in high humidity environments. NOTE: For sump pump applications, Tripp Lite recommends its "UT" Utility Truck Inverter/Chargers.

#### Package Includes

- APSINT2012 Inverter/Charger
- Instruction manual with warranty information

#### Features

- Supports 230V AC output from a 230V AC line power source or 12V DC battery source
- 20 millisecond automatic transfer between line and battery power supports UPS protection during blackouts and voltage fluctuations for equipment compatible with a one cycle transfer time
- Double Boost inverter output supports momentary startup loads up to 200% of the continuous rating for up to 10 seconds (see specification chart)
- OverPower inverter output supports longer duration overloads to 150% for 1-60 minutes under ideal battery and temperature conditions.
- 3 stage, 15/60 amp battery charger with adjustable settings for wet/gel battery types offers fast, reliable battery recharging
- 3 position operating mode switch supports "AUTO" mode to enable automatic transfer between DC and AC modes, CHARGE-ONLY to maintain a full battery charge when AC is present without auto transfer and SYSTEM OFF settings
- Set of six front panel LEDs display AC/DC operational modes, overload status, DC voltage level, shutdown status and system fault status
- Set of 4 configuration dipswitches support wet/gel battery charging profiles, adjustable 259/264V high voltage auto transfer during

overvoltages and selectable 144/163/182/201V AC low voltage auto transfer during brownouts

- Set of 4 additional configuration dip switches support 4 levels of charger limiting relative to output load size
- Resettable 10A charger AC input breaker and resettable 15A AC output breaker and automatic 2 speed cooling fan protect the inverter from load and temperature related failures
- Automatic overload and thermal shutoff safely turns off inverter as excessive loads or overheating conditions develop
- Front panel remote control connector enables remote off/on switching (requires APSRM4 switch accessory)

## Specifications

OVERVIEW	
Intended Application	Emergency Home Power
OUTPUT	
Frequency compatibility	50 Hz
Output watts	2000
Continuous output capacity (watts)	2000
Peak output capacity (watts)	4000
Output nominal voltage	230V
Output voltage regulation	LINE POWER (AC): Maintains 230V nominal sine wave output from line power source. INVERTER POWER (AC): Maintains PWM sine wave output voltage of 230 VAC (+/-5%).
Output frequency regulation	50 Hz (+/- 0.3 Hz)
Overload protection	Includes 10A input breaker dedicated to the charging system and 15A output breaker for AC output loads
Outlet quantity / type	Hardwire
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	DC INPUT: Requires 12VDC input source capable of delivering 192A for the required duration (when used at full continuous capacity - DC requirements increase during OverPower and DoubleBoost operation). For automotive applications, professional hardwire installation with 400A minimum battery system fusing is recommended.
Maximum input amps / watts	DC INPUT: Full continuous load - 192A at 12VDC. AC INPUT: 17 amps at 230VAC with full inverter and charger load (8.7A max charger-only / combined input load to support charger and AC output is automatically controllable to 66%-33%-0% based on AC output loading using the charger limiting set points - see manual for setting instructions)
Input connection type	DC INPUT: Set of 2 DC bolt-down terminals. AC INPUT: Hardwire via built in junction box with cover plate
Voltage compatibility (VAC)	230
Voltage compatibility (VDC)	12
Input frequency	50Hz
BATTERY	
Expandable battery runtime	Runtime is expandable with any number of user supplied wet or gel type batteries

DC system voltage (VDC)	12
Battery Pack Accessory (optional)	98-121 sealed lead acid battery (optional)
Battery recharge rate	Selectable 15 / 60 amp
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	3 position on/off/remote switch enables simple on/off power control plus "auto/remote" setting that enables distant on/off control of the inverter system when used in conjunction with optional <a href="#">APSRM4</a> accessory when used in inverter mode. In AC uninterruptible power mode, "auto/remote" setting enables automatic transfer from line power to battery power - to maintain continuous AC power to connected loads.
Front panel LEDs	Set of 6 LEDs offer continuous status information on load percentage (6 levels reported) and battery charge level (7 levels reported). See manual for sequences.
<b>PHYSICAL</b>	
Shipping weight (lbs)	46
Shipping weight (kg)	20.9
Cooling method	Multi-speed fan
Unit Dimensions (HWD/in)	7 x 8.5 x 14
Unit Dimensions (HWD/cm)	17.78 x 21.59 x 35.56
Shipping Dimensions (HWD/in)	13.25 x 15 x 21.13
Shipping Dimensions (HWD/cm)	33.66 x 38.1 x 53.66
Unit weight (lbs)	42
Unit weight (kg)	19.1
Material of construction	Polycarbonate
Style	Heavy-duty with built-in battery charger
Form factors supported	Mounting slots enable permanent placement of inverter on any horizontal surface (see manual for additional mounting information)
<b>ENVIRONMENTAL</b>	
Relative Humidity	0-95% non-condensing
<b>LINE / BATTERY TRANSFER</b>	
Transfer time from line power to battery mode	20 milliseconds (typical - compatible with many computers, servers and networking equipment - verify transfer time compatibility of loads for UPS applications)
Low voltage transfer to battery power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage drops to 144V (user adjustable to 163, 182, 201V - see manual)
High voltage transfer to battery power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage increases to 259V (user adjustable to 264 - see manual)

SPECIAL FEATURES	
Appearance	Black color
Load Sensing	Optional load sense function enables automatic inverter shutoff and startup as connected equipment is powered off and on. Front panel load sense potentiometer can be set to shutoff or turn on inverter power in response to loads of any level, up to 150 watts.
Remote control capability	Yes
WARRANTY	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

## Related Items

### Optional Products

Related Model	Description	Qty.
<a href="#">APSRM4</a>	Remote Control Module - for Tripp Lite Inverters and Inverter/Chargers	1
<a href="#">BP-260</a>	Ideal battery housing for use with Tripp Lite PowerVerter APS inverter/charger systems with a 12 or 24V DC system voltage.	1
<a href="#">98-121</a>	12V DC Sealed, Maintenance-Free Battery	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=1339](http://www.tripplite.com/en/products/model.cfm?txtModelID=1339).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[APS INT2012](#)