



PART NUMBER	REV	FIRST USED	TERMINATOR	FEED TYPE	DESCRIPTION
1528555-1	B	-	LEADMAKER	MECH POST FEED	CUTS CARRIER
1528555-2	B	-	BENCH	MECH PRE FEED	CUTS CARRIER
1528555-6	B	-	LEADMAKER	MECH POST FEED	CONTINUOUS CARRIER
7-1528555-1	B	-	LEADMAKER	MECH POST FEED	-1 AND SPARE PARTS
7-1528555-2	B	-	BENCH	MECH PRE FEED	-2 AND SPARE PARTS
7-1528555-6	B	-	LEADMAKER	MECH POST FEED	-6 AND SPARE PARTS
7-1528555-7	A	-	-	-	SPARE PARTS KIT

[illegible]

* WARNING:

ON INSTALLATION, SET WIRE DISC TO LARGEST WIRE SIZE SETTING. USE OF SETTINGS BELOW MIN REQUIRED CRIMP HEIGHT SETTING WILL CAUSE DAMAGE TO CRIMP TOOLING.



		B	REVISED ECR-10-016309
P	F	LTR	REVISION RECORD

[illegible]

DIMENSIONS: mm [INCHES]
DO NOT SCALE PRINT.
TOLERANCES UNLESS
OTHERWISE SPECIFIED:
1 PLC DEC $\pm$ -
2 PLC DEC $\pm$ -
3 PLC DEC $\pm$ -
ANGLES $\pm$ -
SURF TEXTURE: $\sqrt{\text{ }}$
REMOVE BURRS, BREAK
SHARP EDGES R0.38 MAX

MATL		HT TR		FIN	
16JUN05		APP 16JUN05		F.BACKHURST	
DR L.OFFHOUSE		REL 05-08-05		 Tyco Electronics 14000 SW 15th St. #200-3000 Fort Lauderdale, FL 33325	
CHK -		REWORK		WILFORD	
NAME		FINE ADJ		SIDE FD HD-1 APPL	
SCALE -		D DWS NO		1528555	
				SHEET 1 of 1	
				REV B	

	-	1	1	1	1	1	1	1528555	PRINT, APPLICATOR LOG SHEET	73
	-	1	1	1	1	1	1	1338705-3	DOCUMENTATION PACKAGE	72
										71
										70
										69
										68
	-	1	1	1	1	1	1	461264-5	PLATE, IDENTIFICATION	67
	-	2	2	2	2	2	2	21017-2	SCR,DRIVE(#2x.19)ID PLATE	66
										65
										64
	-	1	1	1	1	1	1	3-18031-0	SCR,SKT SET(M6X6)RAM	63
										62
	-	2	2	2	2	2	2	2-18032-5	SCR,SKT SET (M5X20)DRAG	61
	-	1	1	1	1	1	1	18024-7	SCR,BHC(M4X10)ANVIL	60
	-	1	1	1	1	1	1	5-18022-2	SCR,HEX(M4X8)FEED FINGER	59
										58
										57
	-	1	1	1	1	1	1	1338685-1	PAWL, FEED	56
										55
	-	4	4	4	4	4	4	18024-8	SCR,BHC(M4x12)SHEAR HOLDER	54
	-	2	2	2	2	2	2	1-18023-4	SCR,SHC(M4x20)TERM HLD DWN	53
	-	1	1	1	1	1	1	18030-1	NUT,HEX(M3)HOLD DOWN	52
	-	1	1	1	1	1	1	811242-5	BUMPER, HOLDDOWN	51
	-	1	1	1	1	1	1	690753-2	SPACER, TONKER	50
	-	1	1	1	1	1	1	18024-3	SCR,BHC(M3X10)CAM	49
	-	-	1	-	-	1	-	1338675-1	CAM, PRE FEED 30 & 40 mm ST	48
	-	1	-	1	1	-	1	1338676-1	CAM, POST FEED 30 & 40 mm ST	47
	-	1	1	1	1	1	1	1320999-3	APPLICATOR BASIC SUBASSY	46
	-	1	1	1	1	1	1	690191-1	PLUG, NYLON	45
	-	1	1	1	1	1	1	1338660-1	RAM	44
										43
										42
	-	1	1	1	1	1	1	2-18024-6	SCR,BHC(M8X25)RAM	41
										40
	-	1	1	1	1	1	1	690125-1	SHIM SUBASSY	39
	-	1	1	1	1	1	1	469367-9	SPACER, FINE ADJUST	38
	-	1	1	1	1	1	1	879103-2	FINE ADJUST HEAD SUBASSY	37
										36
										35
	-	1	1	1	1	1	1	2-1320934-7	SUPPORT, TERMINAL	34
	-	2	2	2	2	2	2	1-18024-0	SCR,BHC(M4X20)STRIP GUIDE	33
	-	1	1	1	1	1	1	18027-2	WASHER, FLAT(M4)	32
	-	1	1	1	1	1	1	1-18023-2	SCR,SKT CAP(M4X12)MOUNT BLOCK	31
	-	1	1	1	1	1	1	1320908-2	SPACER, STRIP GUIDE	30
	-	1	1	1	1	1	1	1633073-1	STRIP GUIDE PLATE ASSY	29
	-	1	1	1	1	1	1	1-455888-0	SPACER, FRONT SHEAR DEP	28
	-	2	2	2	2	2	2	1-22284-0	SPRING, DRAG	27
	-	1	1	1	1	1	1	356835-1	LEVER, DRAG RELEASE	26
	-	1	1	1	1	1	1	240792-1	DRAG, TERMINAL	25
	-	1	1	1	1	1	1	1320928-1	PLATE, STRIP GUIDE	24
	-	1	1	1	1	1	1	980371-4	SCR,SHC SHLD	23
	-	1	-	1	1	-	1	690472-2	STRIPPER	22
	-	1	1	1	1	1	1	1-18023-1	SCR,SHC(M4X10)STRIPPER	21
	-	4	4	4	4	4	4	18025-2	WASHER,LOCK(M4)STRIPPER	20
	-	-	1	-	-	1	-	690472-1	STRIPPER	19
										18
	-	1	-	-	1	-	-	1338684-1	HOLDER, SHEAR, FRONT (NO-CUT)	17
										16
										15
										14
										13
	-	1	1	1	1	1	1	3-22280-3	SPRING, SHEAR	12
	-	1	1	1	1	1	1	356885-4	STOP, SHEAR	11
	-	-	1	1	-	1	1	1320921-1	HOLDER, SHEAR, FRONT (CUT)	10
	-	1	1	1	1	1	1	454276-1	SHEAR, FLOAT (FRONT)	9
	1	2	2	2	1	1	1	4-1333206-0	ANVIL	8
	-	1	1	1	1	1	1	240641-4	SPACER, DEPRESSOR (REAR)	7
										6
	-	1	1	1	1	1	1	1-455889-4	DEPRESSOR, SHEAR (FRONT)	5
	-	1	1	1	1	1	1	238011-4	SPACER, BLOCK CRIMPER	4
	1	2	2	2	1	1	1	6-456134-5	CRIMPER, INSULATION	3
										2
	1	2	2	2	1	1	1	456407-5	CRIMPER, WIRE	1
-77	-76	-72	-71	-6	-2	-1		PART NO	DESCRIPTION	ITEM NO
								REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)		