




Wire Marker Sleeves

When ordering a colored sleeve, replace ** with the abbreviation of the desired color.

Example: Part Number 3PS-094-2-**-S in red would be ordered as 3PS-094-2-RD-S



3-To-1 Shrink Ratio Colored Two-Sided PermaSleeve Wire Markers

Part Number	Markers Per Box	Range of Wire Dia. Inch (mm) Min.-Max.	Approx. Wire Gauge	Marker Width Inch (mm) A	Marker Height Inch (mm) B	Vert Repeat Inch (mm) C	Suggested Ribbon	Diagram
2.000" Marker Width								
3PS-094-2-YL	2,500	0.023 (0.6)–0.080 (2.0)	28-18	2.000 (50.8)	0.182 (4.6)	0.500 (12.7)	R4300	Fig. 21
3PS-094-2-**-S	500	0.023 (0.6)–0.080 (2.0)	28-18	2.000 (50.8)	0.182 (4.6)	0.500 (12.7)	R4300	Fig. 21
3PS-125-2-YL	2,500	0.046 (1.2)–0.110 (2.8)	22-16	2.000 (50.8)	0.235 (6.0)	0.500 (12.7)	R4300	Fig. 21
3PS-125-2-**-S	500	0.046 (1.2)–0.110 (2.8)	22-16	2.000 (50.8)	0.235 (6.0)	0.500 (12.7)	R4300	Fig. 21
3PS-187-2-YL	2,500	0.062 (1.6)–0.150 (3.8)	18-12	2.000 (50.8)	0.335 (8.5)	0.625 (15.9)	R4300	Fig. 21
3PS-187-2-**-S	500	0.062 (1.6)–0.150 (3.8)	18-12	2.000 (50.8)	0.335 (8.5)	0.625 (16.0)	R4300	Fig. 21
3PS-250-2-YL	2,500	0.094 (2.4)–0.215 (5.5)	16-10	2.000 (50.8)	0.439 (11.2)	0.750 (19.1)	R4300	Fig. 21
3PS-250-2-**-S	500	0.094 (2.4)–0.215 (5.5)	16-10	2.000 (50.8)	0.439 (11.2)	0.750 (19.1)	R4300	Fig. 21
3PS-375-2-YL	1,000	0.125 (3.2)–0.320 (8.1)	12-6	2.000 (50.8)	0.645 (16.4)	1.000 (25.4)	R4300	Fig. 21
3PS-375-2-**-S	250	0.125 (3.2)–0.320 (8.1)	12-6	2.000 (50.8)	0.645 (16.4)	1.000 (25.4)	R4300	Fig. 21
3PS-500-2-YL	500	0.187 (4.8)–0.450 (11.4)	8-1	2.000 (50.8)	0.851 (21.6)	1.250 (31.8)	R4300	Fig. 21
3PS-500-2-**-S	250	0.187 (4.8)–0.450 (11.4)	8-1	2.000 (50.8)	0.851 (21.6)	1.250 (31.8)	R4300	Fig. 21
3PS-750-2-YL	250	0.250 (6.4)–0.700 (17.8)	6- 4/0	2.000 (50.8)	1.250 (31.8)	1.625 (41.3)	R4300	Fig. 21
3PS-750-2-**-S	100	0.250 (6.4)–0.700 (17.8)	6- 4/0	2.000 (50.8)	1.250 (31.8)	1.625 (41.3)	R4300	Fig. 21

2-To-1 Shrink Ratio Colored Two-Sided PermaSleeve Wire Markers

Part Number	Markers Per Box	Range of Wire Dia. Inch (mm) Min.-Max.	Approx. Wire Gauge	Marker Width Inch (mm) A	Marker Height Inch (mm) B	Vert Repeat Inch (mm) C	Suggested Ribbon	Diagram
3PS-1000-2-**-S	100	0.450 (11.4)–0.950 (24.1)	1-500	2.000 (50.8)	1.660 (42.2)	2.000 (50.8)	R4300	Fig. 21

2-To-1 Shrink Ratio Colored Polyolefin (B-341) One-Sided Printable Sleeve Markers

Part Number	Markers Per Box	Range of Wire Dia. Inch (mm) Min.-Max.	Approx. Wire Gauge	Marker Width Inch (mm) A	Marker Height Inch (mm) B	Vert Repeat Inch (mm) C	Suggested Ribbon	Diagram
2.000" Marker Width								
PS-1000-2-YL	250	0.450 (11.4)–0.950 (24.1)	1-500	2.000 (50.8)	1.660 (42.2)	2.000 (50.8)	R4300	Fig. 21
PS-1000-2-BK-S	100	0.450 (11.4)–0.950 (24.1)	1-500	2.000 (50.8)	1.660 (42.2)	2.000 (50.8)	R4502-SV	Fig. 21



Keep In Mind

Sleeves may be perforated for shorter marker lengths. Sleeves may be perforated in halves, thirds, or fourths. Options are 2, 3, 4.

Approximate wire gauge based on National Electric Code insulation measurement of THHN wire.