




SECTION B-B'



SECTION A-A'




ISO VIEW

NOTES

1. MATERIAL : BRASS(C2600), 0.4mm THICKNESS
2. FINISH : 0.8 -1.8 μ TIN PLATING OVERALL
0.3-0.8 μ m COPPER PLATING
3. APPLICABLE SOCKET
P21/7W : 49454,104035,104036,104037,104038,104039
WY21W, W21W : 104133, 104134
4. APPLICABLE WIRE SEAL : 49454-9002
5. APPLICABLE BULB : P27/7W, W21W, WY21W

<TABLE1>

NO.	MATERIAL NO.	ORDER NO.	TYPE	DIMENSIONS			WIRE RANGE
				W2	H2	R2	
1	498699702	49869-9702	SEALED	5.55	5.35	1.75	AVS 0.5~0.85mm ²
2	498699102	49869-9102	UNSEALED	4.2	4.1	1.2	AVS(AVSS) 0.5~0.85mm ²



CHANGED DIMENSION
EC NO: KTR2012-0050
DRAWN: HIMOON 2012/01/17
CHKD:
APPR: JHBAE 2012/05/04

QUALITY SYMBOLS
▽=0
C=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± 0	± ---
2 PLACES	± 0.20	± ---
1 PLACE	± 0.25	± ---
ANGULAR ± 1 °		

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY
DRAWN BY
SMKIM
DATE
2009/03/16
CHECKED BY
BCY00N
DATE
2009/03/16
APPROVED BY
EHJUNG
DATE
2009/03/16

SCALE
5:1
DESIGN UNITS
METRIC
THIRD ANGLE
PROJECTION

SINGLE CONTACT TERMINAL
FOR S8 & T20 SOCKET



MOLEX INCORPORATED

MATERIAL NO.
SEE TABLE1
DOCUMENT NO.
SD-49869-001
SHEET NO.
1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[49869-9702](#)