

KVR16R11D4K4/64

64GB (16GB 2G x 72-Bit x 4 pcs.) PC3-12800
CL11 Registered w/Parity 240-Pin DIMM Kit

DESCRIPTION

ValueRAM's KVR16R11D4K4/64 is a kit of four 2G x 72-bit (16GB) DDR3-1600 CL11 SDRAM (Synchronous DRAM), registered w/parity, 2Rx4 ECC memory modules, based on thirty-six 1G x 4-bit FBGA components per module. Total kit capacity is 64GB. The SPDs are programmed to JEDEC standard latency DDR3-1600 timing of 11-11-11 at 1.5V. Each 240-pin DIMM uses gold contact fingers. The electrical and mechanical specifications are as follows:

FEATURES



- JEDEC standard 1.5V (1.425V ~1.575V) Power Supply
- VDDQ = 1.5V (1.425V ~ 1.575V)
- 800MHz fCK for 1600Mb/sec/pin
- 8 independent internal bank
- Programmable CAS Latency: 11, 10, 9, 8, 7, 6
- Programmable Additive Latency: 0, CL - 2, or CL - 1 clock
- 8-bit pre-fetch
- Burst Length: 8 (Interleave without any limit, sequential with starting address "000" only), 4 with tCCD = 4 which does not allow seamless read or write [either on the fly using A12 or MRS]
- Bi-directional Differential Data Strobe
- Internal(self) calibration : Internal self calibration through ZQ pin (RZQ : 240 ohm $\pm$ 1%)
- On Die Termination using ODT pin
- On-DIMM thermal sensor (Grade B)
- Average Refresh Period 7.8us at lower than TCASE 85°C, 3.9us at 85°C < TCASE $\leq$ 95°C
- Asynchronous Reset
- PCB : Height 1.180" (30.00mm), double sided component

SPECIFICATIONS


CL(IDD)	11 cycles
Row Cycle Time (tRCmin)	48.125ns (min.)
Refresh to Active/Refresh Command Time (tRFCmin)	260ns (min.)
Row Active Time (tRASmin)	35ns (min.)
Maximum Operating Power	6.681 W* (per module)
UL Rating	94 V - 0
Operating Temperature	0° C to 85° C
Storage Temperature	-55° C to +100° C

*Power will vary depending on the SDRAM and Register/PLL used.


Continued >>

MODULE DIMENSIONS:


Detail of Contacts A





Detail of Contacts B



Detail of Contacts C




Detail of Contacts D

**Side****Note:**

1. ± 0.13 tolerance on all dimensions unless otherwise stated.

Units: millimeters

HEAT SPREADER DIMENSIONS:**Note:**

1. ± 0.13 tolerance on all dimensions unless otherwise stated.
2. In order to uninstall FDHS, please contact sales administrator.

Units: millimeters